## SIEMENS

## Data sheet

## 3LD3310-0TK05



Load disconnector 3LD3, lu 40 A Main switch 3-pole Rated operating capacity at AC-23 A at 400 V 18.5 kW Installation in distribution boards, Basic switch without Knob-operated mechanism

| Model   |                         |  |
|---|-------------------------|--|
| product brand name  | SENTRON                 |  |
| product designation   | 3LD Switch disconnector |  |
| design of the product   | Switch                  |  |
| display version / for switch position indicator manual operation                                      | 1 ON - 0 OFF            |  |
| design of the actuating element   | Without handle          |  |
| design of handle  | without                 |  |
| General technical data  |                         |  |
| number of poles   | 3                       |  |
| number of poles / note  | 3                       |  |
| type of device  | fixed mounting          |  |
| type of switch  | DIN-rail mounting       |  |
| mechanical service life (switching cycles) / typical  | 100 000                 |  |
| electrical endurance (switching cycles)   |                         |  |
| • at AC-23 A / at 690 V   | 6 000                   |  |
| l2t value / with closed switch / at 690 V / for combination<br>switch + gG fuse / maximum             | 15 kA2.s                |  |
| let-through I2t value / with closed switch / at 440 V / for<br>combination switch + gG fuse / maximum | 15 kA2.s                |  |
| operating frequency / maximum   | 50 1/h                  |  |
| Voltage   |                         |  |
| insulation voltage / rated value  | 690 V                   |  |
| surge voltage resistance / rated value  | 6 kV                    |  |
| Protection class  |                         |  |
| protection class IP   | IP20                    |  |
| protection class IP / on the front  | IP20                    |  |
| Dissipation   |                         |  |
| power loss [W]  |                         |  |
| <ul> <li>for rated value of the current / at AC / in hot<br/>operating state / per pole</li> </ul>    | 2.5 W                   |  |
| <ul> <li>per conductor / typical</li> </ul>   | 2 W                     |  |
| Current   |                         |  |
| operational current   |                         |  |
| <ul> <li>at 40 °C / rated value</li> </ul>  | 40 A                    |  |
| • at 45 °C / rated value  | 40 A                    |  |
| • at 50 °C / rated value  | 40 A                    |  |
| • at 55 °C / rated value  | 40 A                    |  |
| • at AC / rated value   | 40 A                    |  |
| <ul> <li>at AC-23 A / at 400 V / rated value</li> </ul>   | 36 A                    |  |

| • at AC-21 / at 690 V / rated value   | 40 A         |
|---|--------------|
| • at AC-21 A / at 240 V / rated value   | 40 A         |
| • at AC-21 A / at 440 V / rated value   | 40 A         |
| operational current / of upstream fuse / rated value                                      | 40 A         |
| let-through current / with closed switch  |              |
| <ul> <li>at 440 V / for combination switch + gG fuse /<br/>maximum</li> </ul>             | 5 kA         |
| <ul> <li>at 690 V / for combination switch + gG fuse /<br/>maximum permissible</li> </ul> | 5 kA         |
| Main circuit  |              |
| operating power   |              |
| • at AC-23 A / at 240 V / rated value   | 7.5 kW       |
| <ul> <li>at AC-23 A / at 400 V / rated value</li> </ul>                                   | 19 kW        |
| <ul> <li>at AC-23 A / at 440 V / rated value</li> </ul>                                   | 15 kW        |
| <ul> <li>at AC-23 A / at 690 V / rated value</li> </ul>                                   | 15 kW        |
| <ul> <li>at AC-3 / at 240 V / rated value</li> </ul>                                      | 7.5 kW       |
| <ul> <li>at AC-3 / at 400 V / rated value</li> </ul>                                      | 12 kW        |
| <ul> <li>at AC-3 / at 690 V / rated value</li> </ul>                                      | 11.5 kW      |
| operational current / rated value   | 40 A         |
| Auxiliary circuit   |              |
| number of CO contacts / for auxiliary contacts  | 0            |
| number of NC contacts / for auxiliary contacts  | 0            |
| number of NO contacts / for auxiliary contacts  | 0            |
| operating voltage / of auxiliary contacts / at AC / maximum                               | 500 V        |
| continuous current / of the auxiliary contact / rated value                               | 10 A         |
| insulation voltage / of the auxiliary switch / rated value                                | 500 V        |
| Suitability   |              |
| suitability for use   |              |
| main switch   | Yes          |
| switch disconnector   | Yes          |
| EMERGENCY OFF switch  | Yes          |
| safety switch   | Yes          |
| maintenance/repair switch   | Yes          |
| Product details   |              |
| product feature   |              |
| can be locked into OFF position   | No           |
| special product feature   | Basic Switch |
| product extension / optional  |              |
| motor drive   | No           |
| voltage trigger   | No           |
| Short circuit   |              |
| conditional short-circuit current / with line-side fuse                                   |              |
| protection  |              |
| <ul> <li>at 440 V / by gG fuse / rated value</li> </ul>                                   | 10 kA        |
| • at 690 V / by gG fuse / rated value   | 6 kA         |
| according UL  |              |
| operational current / at AC / according to UL 508/UL 60947-4-1 / rated value              | 40 A         |
| operating voltage / at AC / at 50/60 Hz / according to UL 508/UL 60947-4-1 / rated value  | 600 V        |
| active power [hp] / at AC / at 480 V / according to UL<br>508/UL 60947-4-1 / rated value  | 20           |
| active power [hp] / at AC / at 600 V / according to UL<br>508/UL 60947-4-1 / rated value  | 20           |
| short-time withstand current (SCCR) / at 600 V / according to UL 508/UL 60947-4-1         | 5 kA         |
| continuous current / of upstream fuse / according to UL / rated value                     | 50 A         |
| type of fuse / according to UL  | RK5          |
| Number  |              |
| number of connectable NC contacts / for auxiliary contacts                                | 2            |
|   |              |

| 4<br>0                              |
|-------------------------------------|
|                                     |
| 0                                   |
|                                     |
|                                     |
|                                     |
|                                     |
| 6                                   |
| 14                                  |
|                                     |
| 1x (2.5 to 16 mm <sup>2</sup> )     |
| 1x (2.516 mm²)                      |
| 1x (2.5 to 16 mm <sup>2</sup> )     |
|                                     |
| 2x (0.75 2.5 mm²), 1x 4 mm²         |
| 2x (0.75 1.5 mm²), 1x 2.5 mm²       |
| 2x (0.75 2.5 mm²), 1x 4 mm²         |
|                                     |
| box terminal                        |
| Box terminals                       |
|                                     |
|                                     |
| fuse gL/gG: 40 A                    |
| fuse gL/gG: 10 A                    |
|                                     |
| 60 mm                               |
| 36 mm                               |
| 64 mm                               |
| Built-in unit fixed-mounted version |
|                                     |
| No                                  |
| No                                  |
| Yes                                 |
| 200 g                               |
|                                     |
|                                     |
| -25 °C                              |
| 55 °C                               |
| -25 °C                              |
| Declaration of Conformity           |
|                                     |

## other

**Miscellaneous** 

Subject to change without notice © Copyright Siemens Information- and Downloadcenter (Catalogs, Brochures,...) http://www.siemens.com/lowvoltage/catalogs Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3LD3310-0TK05 Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/en/ps/3LD3310-0TK05 Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...) http://www.automation.siemens.com/bilddb/cax\_en.aspx?mlfb=3LD3310-0TK05 CAx-Online-Generator http://www.siemens.com/cax Tender specifications

http://www.siemens.com/specifications

Ø