





XKB



Specifications:


- Voltage rating: 250V AC/DC
- Current rating: 2.5-1.0A AC/DC
- Withstanding voltage: 800V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥1000MΩ
- Contact resistance: ≤10mΩ
- After environmental testing: ≤20mΩ






6P~14P Without Guideway
16P~40P With Guideway
Scale: 1/0.5

X2006 W V - 2*XX -4T SN
① ② ③ ④ ⑤ ⑥

- ① XKB Series No.
- ② Category: W-WAFER
- ③ Welding Board Angle: V-180°
- ④ Row No.-pin No.: 2*XX-04P~20P
- ⑤ Material: 4T-PA4T 94V-0
- ⑥ Plating Category : SN-Bright Tin Plating



Recommended P.C.B Layout
General Tolerance ±0.05



Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2*04	6.00	10.00	2*13	24.00	28.00
2*05	8.00	12.00	2*14	26.00	30.00
2*06	10.00	14.00	2*15	28.00	34.00
2*07	12.00	16.00	2*16	30.00	36.00
2*08	14.00	18.00	2*17	32.00	38.00
2*09	16.00	20.00	2*18	34.00	40.00
2*10	18.00	22.00	2*19	36.00	42.00
2*11	20.00	24.00	2*20	38.00	44.00
2*12	22.00	26.00			

Part No	Material	Suitable XKB Terminal	Suitable XKB Terminal
X2006W-2xXX-4TSN	PA4T UL 94V-0	X2006T	X2006H

广东星坤科技股份有限公司

日期
文件工程章

www.helloxkb.com

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE:
DWN	DATE	VIEW:	X2006W-2xXX-4TSN
CHKD	DATE	UNIT: mm/in	PART NO.:
APPD	DATE	SIZE: A4	DWG NO.:
			WEIGHT
XKB INDUSTRIAL PRECISION CO., LIMITED			SHEET
			REVISION
			1/1
			A0