SIEMENS

Data sheet 3RV2031-4XA10



Circuit breaker size S2 for motor protection, CLASS 10 A-release 49...59 A N-release 845 A screw terminal Standard switching capacity

product brand name	SIRIUS	
product designation	Circuit breaker	
design of the product	For motor protection	
product type designation	3RV2	
General technical data		
size of the circuit-breaker	S2	
size of contactor can be combined company-specific	S2	
product extension auxiliary switch	Yes	
power loss [W] for rated value of the current		
 at AC in hot operating state 	26 W	
at AC in hot operating state per pole	8.7 W	
insulation voltage with degree of pollution 3 at AC rated value	690 V	
surge voltage resistance rated value	6 kV	
shock resistance according to IEC 60068-2-27	25g / 11 ms Sinus	
mechanical service life (switching cycles)		
 of the main contacts typical 	20 000	
of auxiliary contacts typical	20 000	
electrical endurance (switching cycles) typical	20 000	
type of protection according to ATEX directive 2014/34/EU	Ex II (2) GD	
certificate of suitability according to ATEX directive 2014/34/EU	DMT 02 ATEX F 001	
reference code according to IEC 81346-2	Q	
Substance Prohibitance (Date)	04/10/2015	
Ambient conditions		
installation altitude at height above sea level maximum	2 000 m	
ambient temperature		
 during operation 	-20 +60 °C	
 during storage 	-50 +80 °C	
during transport	-50 +80 °C	
relative humidity during operation	10 95 %	
Main circuit		
number of poles for main current circuit	3	
adjustable current response value current of the current-dependent overload release	49 59 A	
operating voltage		
• rated value	20 690 V	
 at AC-3 rated value maximum 	690 V	
 at AC-3e rated value maximum 	690 V	

execution frequency rated value	50 60 Hz
operating frequency rated value	
operational current rated value operational current	59 A
at AC-3 at 400 V rated value	59 A
at AC-3 at 400 V rated value at AC-3e at 400 V rated value	59 A
operating power	39 A
• at AC-3	
— at 230 V rated value	15 kW
— at 400 V rated value	30 kW
— at 500 V rated value	37 kW
— at 690 V rated value	55 kW
• at AC-3e	OO RVV
— at 230 V rated value	15 kW
— at 400 V rated value	30 kW
— at 500 V rated value	37 kW
— at 690 V rated value	55 kW
operating frequency	33 RVV
• at AC-3 maximum	15 1/h
at AC-3 maximum at AC-3e maximum	15 1/h
Protective and monitoring functions	
product function	
ground fault detection	No
phase failure detection	Yes
trip class	CLASS 10
design of the overload release	thermal
breaking capacity maximum short-circuit current (Icu)	tioma
at AC at 240 V rated value	65 kA
at AC at 400 V rated value	65 kA
at AC at 500 V rated value	8 kA
at AC at 690 V rated value	4 kA
breaking capacity operating short-circuit current (Ics)	
at AC	
• at 240 V rated value	100 kA
 at 400 V rated value 	30 kA
• at 500 V rated value	4 kA
at 690 V rated value	2 kA
response value current of instantaneous short-circuit trip unit	845 A
UL/CSA ratings	
full-load current (FLA) for 3-phase AC motor	
• at 480 V rated value	59 A
at 600 V rated value	59 A
yielded mechanical performance [hp]	
 for single-phase AC motor 	
— at 110/120 V rated value	5 hp
— at 230 V rated value	10 hp
• for 3-phase AC motor	
— at 220/230 V rated value	20 hp
— at 460/480 V rated value	40 hp
— at 575/600 V rated value	50 hp
Short-circuit protection	
product function short circuit protection	Yes
design of the short-circuit trip	magnetic
design of the fuse link for IT network for short-circuit protection of the main circuit	
• at 240 V	none required
• at 400 V	160
• at 500 V	125
• at 690 V	100
Installation/ mounting/ dimensions	
motanation/ mounting/ difficultions	

mounting position	any
fastening method	screw and snap-on mounting onto 35 mm standard mounting rail
Table Millian Control	according to DIN EN 60715
height	140 mm
width	55 mm
depth	149 mm
required spacing	
 for grounded parts at 400 V 	
— downwards	50 mm
— upwards	50 mm
— at the side	10 mm
 for live parts at 400 V 	
— downwards	50 mm
— upwards	50 mm
— at the side	10 mm
 for grounded parts at 500 V 	
— downwards	50 mm
— upwards	50 mm
— at the side	10 mm
• for live parts at 500 V	
— downwards	50 mm
— upwards	50 mm
— at the side	10 mm
 for grounded parts at 690 V 	
— downwards	50 mm
— upwards	50 mm
— at the side	10 mm
 for live parts at 690 V 	
— downwards	50 mm
— upwards	50 mm
— at the side	10 mm
Connections/ Terminals	
type of electrical connection	
for main current circuit	screw-type terminals
arrangement of electrical connectors for main current circuit	Top and bottom
type of connectable conductor cross-sections	
• for main contacts	
— solid or stranded	2x (1 35 mm²), 1x (1 50 mm²)
finely stranded with core end processing	2x (1 25 mm²), 1x (1 35 mm²)
at AWG cables for main contacts	2x (18 2), 1x (18 1)
tightening torque	
for main contacts with screw-type terminals	3 4.5 N·m
design of screwdriver shaft	Diameter 5 to 6 mm
size of the screwdriver tip	Pozidriv size 2
design of the thread of the connection screw	
• for main contacts	M6
Safety related data	
B10 value	
with high demand rate according to SN 31920	5 000
proportion of dangerous failures	
with low demand rate according to SN 31920	50 %
with high demand rate according to SN 31920 with high demand rate according to SN 31920	50 %
failure rate [FIT]	
with low demand rate according to SN 31920	50 FIT
with low demand rate according to SN 31920	10 y
T1 value for proof test interval or convice life according to	10 y
T1 value for proof test interval or service life according to IEC 61508	
	IP20
Protection class IP on the front according to IEC	IP20 finger-safe, for vertical contact from the front

General Product Approval



Confirmation





<u>KC</u>



For use in hazardous locations

Declaration of Conformity

Test Certificates







Type Test Certificates/Test Report

Special Test Certificate

Marine / Shipping













Marine / Shipping

other

Railway



Confirmation



Confirmation

Vibration and Shock

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RV2031-4XA10

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RV2031-4XA10

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3RV2031-4XA10

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RV2031-4XA10&lang=en

Characteristic: Tripping characteristics, I2t, Let-through current

https://support.industry.siemens.com/cs/ww/en/ps/3RV2031-4XA10/char

Further characteristics (e.g. electrical endurance, switching frequency) http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RV2031-4XA10&objecttype=14&gridview=view1

last modified:

6/25/2022

