SIEMENS

Data sheet 3RV2411-0HA15



Circuit breaker size S00 for transformer protection A-release 0.55...0.8 A N-release 16 A screw terminal Standard switching capacity with transverse auxiliary switches 1 NO+1 NC

product brand name	SIRIUS
product designation	Circuit breaker
design of the product	For transformer protection
product type designation	3RV2
General technical data	
size of the circuit-breaker	S00
size of contactor can be combined company-specific	S00, S0
product extension auxiliary switch	Yes
power loss [W] for rated value of the current	
 at AC in hot operating state 	7.25 W
at AC in hot operating state per pole	2.4 W
insulation voltage with degree of pollution 3 at AC rated value	690 V
surge voltage resistance rated value	6 kV
shock resistance according to IEC 60068-2-27	25g / 11 ms
mechanical service life (switching cycles)	
 of the main contacts typical 	100 000
of auxiliary contacts typical	100 000
electrical endurance (switching cycles) typical	100 000
reference code according to IEC 81346-2	Q
Substance Prohibitance (Date)	10/01/2009
Ambient conditions	
installation altitude at height above sea level maximum	2 000 m
ambient temperature	
 during operation 	-20 +60 °C
during storage	-50 +80 °C
during transport	-50 +80 °C
relative humidity during operation	10 95 %
Main circuit	
number of poles for main current circuit	3
adjustable current response value current of the current-dependent overload release	0.55 0.8 A
operating voltage	
rated value	20 690 V
 at AC-3 rated value maximum 	690 V
at AC-3e rated value maximum	690 V
operating frequency rated value	50 60 Hz
operational current rated value	0.8 A
operational current	
 at AC-3 at 400 V rated value 	0.8 A

at AC-3e at 400 V rated value	0.8 A
operating power	
• at AC-3	
— at 230 V rated value	0.1 kW
— at 400 V rated value	0.2 kW
— at 500 V rated value	0.3 kW
— at 690 V rated value	0.4 kW
• at AC-3e	
— at 230 V rated value	0.1 kW
— at 400 V rated value	0.2 kW
— at 500 V rated value	0.3 kW
— at 690 V rated value	0.4 kW
operating frequency	
• at AC-3 maximum	15 1/h
at AC-3e maximum	15 1/h
Auxiliary circuit	10 1/11
	hanavana
design of the auxiliary switch	transverse
number of NC contacts for auxiliary contacts	1
number of NO contacts for auxiliary contacts	1
number of CO contacts for auxiliary contacts	0
operational current of auxiliary contacts at AC-15	
• at 24 V	2 A
● at 120 V	0.5 A
● at 125 V	0.5 A
• at 230 V	0.5 A
operational current of auxiliary contacts at DC-13	
• at 24 V	1 A
● at 60 V	0.15 A
Protective and monitoring functions	
product function	
 ground fault detection 	No
 phase failure detection 	Yes
trip class	CLASS 10
design of the overload release	thermal
breaking capacity maximum short-circuit current (Icu)	
 at AC at 240 V rated value 	100 kA
 at AC at 400 V rated value 	100 kA
 at AC at 500 V rated value 	100 kA
at AC at 690 V rated value	100 kA
breaking capacity operating short-circuit current (lcs) at AC	
• at 240 V rated value	100 kA
• at 400 V rated value	100 kA
• at 500 V rated value	100 kA
• at 690 V rated value	100 kA
response value current of instantaneous short-circuit trip unit	16 A
UL/CSA ratings	
full-load current (FLA) for 3-phase AC motor	
• at 480 V rated value	0.8 A
at 600 V rated value	0.8 A
contact rating of auxiliary contacts according to UL	C300 / R300
Short-circuit protection	
	Yes
product function short circuit protection	
design of the short-circuit trip	magnetic
 design of the fuse link for short-circuit protection of the auxiliary switch required 	Fuse gL/gG: 10 A, miniature circuit breaker C 6 A (short-circuit current lk < 400 A)
	וא סטדי או
design of the fuse link for IT network for short-circuit protection of the main circuit	

● at 690 V	gL/gG 6 A
Installation/ mounting/ dimensions	
mounting position	any
fastening method	screw and snap-on mounting onto 35 mm standard mounting rail according to DIN EN 60715
height	97 mm
width	45 mm
depth	97 mm
required spacing	
 for grounded parts at 400 V 	
— downwards	30 mm
— upwards	30 mm
— at the side	9 mm
for live parts at 400 V	
— downwards	30 mm
— upwards	30 mm
— at the side	9 mm
 for grounded parts at 500 V 	
— downwards	30 mm
— upwards	30 mm
— at the side	9 mm
 for live parts at 500 V 	
— downwards	30 mm
— upwards	30 mm
— at the side	9 mm
• for grounded parts at 690 V	
— downwards	50 mm
— upwards	50 mm
— backwards	0 mm
— at the side	30 mm
— forwards	0 mm
• for live parts at 690 V	
— downwards	50 mm
— upwards	50 mm
— backwards	0 mm
— at the side	30 mm
— forwards	0 mm
Connections/ Terminals	
type of electrical connection	
for main current circuit for auxiliary and control circuit	screw-type terminals
for auxiliary and control circuit	screw-type terminals
arrangement of electrical connectors for main current circuit	Top and bottom
type of connectable conductor cross-sections	
for main contacts	0.40750533.0.43
— solid or stranded	2x (0,75 2,5 mm²), 2x 4 mm²
— finely stranded with core end processing	2x (0.5 1.5 mm²), 2x (0.75 2.5 mm²)
at AWG cables for main contacts	2x (18 14), 2x 12
type of connectable conductor cross-sections	
for auxiliary contacts colid or stranded	2v (0.5
— solid or stranded	2x (0.5 1.5 mm²), 2x (0.75 2.5 mm²)
— finely stranded with core end processing	2x (0.5 1.5 mm²), 2x (0.75 2.5 mm²)
at AWG cables for auxiliary contacts tightening torque	2x (20 16), 2x (18 14)
tightening torque	0.8 1.2 N·m
for main contacts with screw-type terminals for auxiliary contacts with screw type terminals	0.8 1.2 N·m 0.8 1.2 N·m
for auxiliary contacts with screw-type terminals design of screwdriver shaft	Diameter 5 to 6 mm
design of screwdriver shaft size of the screwdriver tip	Pozidriv size 2
design of the thread of the connection screw	I OZIGITY SIZE Z
• for main contacts	M3
♥ 101 IIIaiii Contacts	IVIO

of the auxiliary and control contacts	M3
Safety related data	
B10 value	
 with high demand rate according to SN 31920 	5 000
proportion of dangerous failures	
 with low demand rate according to SN 31920 	50 %
 with high demand rate according to SN 31920 	50 %
failure rate [FIT]	
 with low demand rate according to SN 31920 	50 FIT
T1 value for proof test interval or service life according to IEC 61508	10 y
protection class IP on the front according to IEC 60529	IP20
touch protection on the front according to IEC 60529	finger-safe, for vertical contact from the front
display version for switching status	Handle
Contification	

Certificates/ approvals

General Product Approval

Declaration of Conformity





Confirmation





Declaration of Conformity

Test Certificates

Marine / Shipping



Special Test Certificate Type Test Certificates/Test Report







Marine / Shipping

other









Confirmation



Railway

Confirmation Vibration and Shock

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RV2411-0HA15

Cax online generator

 $\underline{\text{http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en\&mlfb=3RV2411-0HA15}}$

 ${\bf Service \& Support~(Manuals,~Certificates,~Characteristics,~FAQs,...)}$

https://support.industry.siemens.com/cs/ww/en/ps/3RV2411-0HA15

 $Image\ database\ (product\ images,\ 2D\ dimension\ drawings,\ 3D\ models,\ device\ circuit\ diagrams,\ EPLAN\ macros,\ ...)$

 $\underline{\text{http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RV2411-0HA15\&lang=en}}$

Characteristic: Tripping characteristics, I2t, Let-through current

https://support.industry.siemens.com/cs/ww/en/ps/3RV2411-0HA15/char Further characteristics (e.g. electrical endurance, switching frequency)

last modified:	6/25/2022 🗗