SIEMENS

Data sheet 3RV2311-0EC10



Circuit breaker size S00 for starter combination Rated current 0.4 A N-release $5.2~\mathrm{A}$ screw terminal Standard switching capacity

product brand name	SIRIUS
product designation	Circuit breaker
design of the product	For starter combinations
product type designation	3RV2
General technical data	
size of the circuit-breaker	S00
size of contactor can be combined company-specific	S00, S0
product extension auxiliary switch	Yes
power loss [W] for rated value of the current	
 at AC in hot operating state 	5.5 W
at AC in hot operating state per pole	1.8 W
insulation voltage with degree of pollution 3 at AC rated value	690 V
surge voltage resistance rated value	6 kV
shock resistance according to IEC 60068-2-27	25g / 11 ms
mechanical service life (switching cycles)	
 of the main contacts typical 	100 000
of auxiliary contacts typical	100 000
electrical endurance (switching cycles) typical	100 000
reference code according to IEC 81346-2	Q
Substance Prohibitance (Date)	10/01/2009
Ambient conditions	
installation altitude at height above sea level maximum	2 000 m
ambient temperature	
during operation	-20 +60 °C
 during storage 	-50 +80 °C
during transport	-50 +80 °C
relative humidity during operation	10 95 %
Main circuit	
number of poles for main current circuit	3
operating voltage	
rated value	20 690 V
 at AC-3 rated value maximum 	690 V
 at AC-3e rated value maximum 	690 V
operating frequency rated value	50 60 Hz
operational current rated value	0.4 A
operational current	
 at AC-3 at 400 V rated value 	0.4 A
 at AC-3e at 400 V rated value 	0.4 A

operating power	
• at AC-3	
— at 230 V rated value	0.1 kW
— at 400 V rated value	0.1 kW
— at 500 V rated value	0.1 kW
— at 690 V rated value	0.2 kW
• at AC-3e	
— at 230 V rated value	0.1 kW
— at 400 V rated value	0.1 kW
— at 500 V rated value	0.1 kW
— at 690 V rated value	0.2 kW
operating frequency	
at AC-3 maximum	15 1/h
at AC-3e maximum	15 1/h
Auxiliary circuit	
number of NC contacts for auxiliary contacts	0
number of NO contacts for auxiliary contacts	0
number of CO contacts for auxiliary contacts	0
Protective and monitoring functions	
product function	
ground fault detection	No
phase failure detection	No
breaking capacity maximum short-circuit current (Icu)	
at AC at 240 V rated value	100 kA
 at AC at 400 V rated value 	100 kA
 at AC at 500 V rated value 	100 kA
 at AC at 690 V rated value 	100 kA
breaking capacity operating short-circuit current (lcs) at AC	
at 240 V rated value	100 kA
 at 400 V rated value 	100 kA
 at 500 V rated value 	100 kA
 at 690 V rated value 	100 kA
response value current of instantaneous short-circuit trip unit	5.2 A
UL/CSA ratings	
full-load current (FLA) for 3-phase AC motor	
 at 480 V rated value 	0.4 A
 at 600 V rated value 	0.4 A
Short-circuit protection	
product function short circuit protection	Yes
design of the short-circuit trip	magnetic
Installation/ mounting/ dimensions	
mounting position	any
fastening method	screw and snap-on mounting onto 35 mm standard mounting rail
	according to DIN EN 60715
height	97 mm
width	45 mm
depth	97 mm
required spacing	
 for grounded parts at 400 V 	
— downwards	30 mm
— upwards	30 mm
— at the side	9 mm
 for live parts at 400 V 	
— downwards	30 mm
— upwards	30 mm
— at the side	9 mm
 for grounded parts at 500 V 	
— downwards	30 mm

	00
— upwards	30 mm
— at the side	9 mm
 for live parts at 500 V 	
— downwards	30 mm
— upwards	30 mm
— at the side	9 mm
 for grounded parts at 690 V 	
— downwards	50 mm
— upwards	50 mm
— backwards	0 mm
— at the side	30 mm
— forwards	0 mm
 for live parts at 690 V 	
— downwards	50 mm
— upwards	50 mm
— backwards	0 mm
— at the side	30 mm
— forwards	0 mm
Connections/ Terminals	
type of electrical connection	
for main current circuit	screw-type terminals
arrangement of electrical connectors for main current circuit	Top and bottom
type of connectable conductor cross-sections	
for main contacts	
— solid or stranded	2x (0,75 2,5 mm²), 2x 4 mm²
— finely stranded with core end processing	2x (0.5 1.5 mm²), 2x (0.75 2.5 mm²)
at AWG cables for main contacts	2x (18 14), 2x 12
tightening torque	
for main contacts with screw-type terminals	0.8 1.2 N·m
design of screwdriver shaft	Diameter 5 to 6 mm
size of the screwdriver tip	Pozidriv size 2
design of the thread of the connection screw	
for main contacts	M3
Safety related data	
B10 value	
with high demand rate according to SN 31920	5 000
proportion of dangerous failures	
with low demand rate according to SN 31920	50 %
with high demand rate according to SN 31920 with high demand rate according to SN 31920	50 %
failure rate [FIT]	
with low demand rate according to SN 31920	50 FIT
T1 value for proof test interval or service life according to	10 y
IEC 61508	
protection class IP on the front according to IEC 60529	IP20
touch protection on the front according to IEC 60529	finger-safe, for vertical contact from the front
display version for switching status	Handle
Certificates/ approvals	
General Product Approval	

General Product Approva





Confirmation



<u>KC</u>



Declaration of Conformity Test Certificates Marine / Shipping





Type Test Certificates/Test Report

Special Test Certificate





Marine / Shipping

other











Confirmation

other

Railway



Confirmation

Vibration and Shock

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RV2311-0EC10

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RV2311-0EC10

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3RV2311-0EC10

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RV2311-0EC10&lang=en

Characteristic: Tripping characteristics, I2t, Let-through current

https://support.industry.siemens.com/cs/ww/en/ps/3RV2311-0EC10/char

Further characteristics (e.g. electrical endurance, switching frequency)

http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RV2311-0EC10&objecttype=14&gridview=view1

last modified:

6/25/2022

