


RECOMMENDED PCB LAYOUT
G1-GN pin is defined as GND



NOTES:

1. MATERIAL:

- 1.1 Insulator: High Temperature Thermoplastic, UL94V-0; Color Black.
- 1.2 Terminal: Copper Alloy.
- 1.3 Shell: Stainless Steel.

2. PLATING:

- 2.1 Contact: Plated 50u" Ni Overall Contact Au 1u"
- 2.2 Shell: Plated 50u" Ni Overall, PAD Au 1u"

3. SPECIALITY:

- 2.1 Current Rating :0.5mA AC/DC max.
- 2.2 Voltage Rating :125V AC/DC
- 2.3 Ambient Temperature Range :-20°C~+60°C
- 2.4 Storage Temperature Range :-40°C~+70°C
- 2.5 Ambient Humidity Range :95% R.H. Max.
- 2.6 Contact Resistance:100mΩ max.
- 2.7 Insulation Resistance:1000MΩ min./500VDC
- 2.8 Mating Cycles:10,000 Insertions
- 2.9 Reflow peak temp.: 260°C ±5°C, 3~5 S
- 2.10 Mating Cycles:3,000 Insertions Min

new		2015/5/3	A	瀚源	
ECN BO.		DESCRIPTION.	DATE.		REV.
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALE: 1/2	SCALE: 3:1
Mikey	Tom	Jerry	PART NAME	NANO-1151	UNLESS OTHERWISE SPECIFIED, TOLERANCE: X. ±0.25 X.x ±0.20 X.xx ±0.15 ANGULAIR ±3
			MODEL NAME	NANO-1151	
			3RD ANGLE PROJ	HanElectricity Co.,LTD	