SIEMENS

Data sheet

3RV2331-4BC10



Circuit breaker size S2 for starter combination Rated current 20 A Nrelease 260 A screw terminal Standard switching capacity

product brand name	SIRIUS
product designation	Circuit breaker
design of the product	For starter combinations
product type designation	3RV2
General technical data	
size of the circuit-breaker	S2
size of contactor can be combined company-specific	S2
product extension auxiliary switch	Yes
power loss [W] for rated value of the current	
 at AC in hot operating state 	14.5 W
 at AC in hot operating state per pole 	4.8 W
insulation voltage with degree of pollution 3 at AC rated value	690 V
surge voltage resistance rated value	6 kV
shock resistance according to IEC 60068-2-27	25g / 11 ms Sinus
mechanical service life (switching cycles)	
 of the main contacts typical 	50 000
 of auxiliary contacts typical 	50 000
electrical endurance (switching cycles) typical	50 000
reference code according to IEC 81346-2	Q
Substance Prohibitance (Date)	10/15/2014
Ambient conditions	
installation altitude at height above sea level maximum	2 000 m
ambient temperature	
 during operation 	-20 +60 °C
 during storage 	-50 +80 °C
 during transport 	-50 +80 °C
relative humidity during operation	10 95 %
Main circuit	
number of poles for main current circuit	3
operating voltage	
 rated value 	20 690 V
 at AC-3 rated value maximum 	690 V
 at AC-3e rated value maximum 	690 V
operating frequency rated value	50 60 Hz
operational current rated value	20 A
operational current	
 at AC-3 at 400 V rated value 	20 A
 at AC-3e at 400 V rated value 	20 A

operating power	
• at AC-3	
— at 230 V rated value	5.5 kW
— at 400 V rated value	7.5 kW
— at 500 V rated value	11 kW
— at 690 V rated value	15 kW
• at AC-3e	
— at 230 V rated value	5.5 kW
— at 400 V rated value	7.5 kW
— at 500 V rated value	11 kW
— at 690 V rated value	15 kW
operating frequency	
 at AC-3 maximum 	15 1/h
• at AC-3e maximum	15 1/h
Auxiliary circuit	
number of NC contacts for auxiliary contacts	0
number of NO contacts for auxiliary contacts	0
Protective and monitoring functions	
product function	
 ground fault detection 	No
phase failure detection	No
breaking capacity maximum short-circuit current (Icu)	
 at AC at 240 V rated value 	100 kA
 at AC at 400 V rated value 	65 kA
 at AC at 500 V rated value 	12 kA
 at AC at 690 V rated value 	5 kA
breaking capacity operating short-circuit current (lcs)	
at AC	
 at 240 V rated value 	100 kA
 at 400 V rated value 	30 kA
 at 500 V rated value 	6 kA
at 690 V rated value	3 kA
response value current of instantaneous short-circuit trip unit	260 A
UL/CSA ratings	
full-load current (FLA) for 3-phase AC motor	
 at 480 V rated value 	20 A
at 600 V rated value	20 A
yielded mechanical performance [hp]	
 for single-phase AC motor 	
— at 110/120 V rated value	1.5 hp
— at 230 V rated value	3 hp
 for 3-phase AC motor 	
— at 200/208 V rated value	7.5 hp
— at 220/230 V rated value	7.5 hp
— at 460/480 V rated value	15 hp
— at 575/600 V rated value	20 hp
Short-circuit protection	
product function short circuit protection	Yes
design of the short-circuit trip	magnetic
design of the fuse link for IT network for short-circuit protection of the main circuit	
• at 240 V	none required
● at 400 V	100
● at 500 V	80
● at 690 V	63
Installation/ mounting/ dimensions	
mounting position	any
fastening method	screw and snap-on mounting onto 35 mm standard mounting rail according to DIN EN 60715

height	140 mm
width	55 mm
depth	149 mm
required spacing	
 for grounded parts at 400 V 	
— downwards	50 mm
— upwards	50 mm
— at the side	10 mm
 for live parts at 400 V 	
 Of the parts at 400 V — downwards 	50 mm
	50 mm
— upwards	
— at the side	10 mm
for grounded parts at 500 V	50
— downwards	50 mm
— upwards	50 mm
— at the side	10 mm
 for live parts at 500 V 	
— downwards	50 mm
— upwards	50 mm
— at the side	10 mm
 for grounded parts at 690 V 	
— downwards	50 mm
— upwards	50 mm
— backwards	0 mm
— at the side	10 mm
— forwards	0 mm
 for live parts at 690 V 	
— downwards	50 mm
— upwards	50 mm
— backwards	0 mm
— at the side	10 mm
— forwards	0 mm
Connections/ Terminals	
type of electrical connection	
for main current circuit	screw-type terminals
arrangement of electrical connectors for main current circuit	Top and bottom
type of connectable conductor cross-sections	
 for main contacts 	
— solid or stranded	2x (1 25 mm²), 1x (1 35 mm²)
 finely stranded with core end processing 	2x (1 16 mm²), 1x (1 25 mm²)
at AWG cables for main contacts	2x (18 3), 1x (18 2)
tightening torque	
for main contacts with screw-type terminals	3 4.5 N·m
design of screwdriver shaft	Diameter 5 to 6 mm
size of the screwdriver tip	Pozidriv size 2
design of the thread of the connection screw	
for main contacts	M6
Safety related data	
B10 value	
with high demand rate according to SN 31920	5 000
proportion of dangerous failures	
with low demand rate according to SN 31920	50 %
 with high demand rate according to SN 31920 with high demand rate according to SN 31920 	50 %
failure rate [FIT]	00 /0
	50 FIT
with low demand rate according to SN 31920 T1 value for proof test interval or service life according to	
IEC 61508	10 y
protection class IP on the front according to IEC 60529	IP20
touch protection on the front according to IEC 60529	finger-safe, for vertical contact from the front

display version for sw	vitching status	Hand	dle			
Certificates/ approval	•					
General Product Ap	oproval					
(S) M	Confirmation			<u>KC</u>	EHC	
Declaration of Conf	formity	Test Certificates		Marine / Shipping		
C C EG-Konf.	UK CA	<u>Type Test Certific-</u> ates/Test Report	<u>Special Test Certific-</u> <u>ate</u>	ABS	BUREAU VERITAS	
Marine / Shipping					other	
	Lloyd's Register us	PRS	RINA	RMRS	<u>Confirmation</u>	
other	Railway					
	<u>Confirmation</u>	Vibration and Shock				
Further information Information- and Downloadcenter (Catalogs, Brochures,)						
https://www.siemens.com/ic10 Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RV2331-4BC10 Cax online generator http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RV2331-4BC10 Service&Support (Manuals, Certificates, Characteristics, FAQs,) https://support.industry.siemens.com/cs/ww/en/ps/3RV2331-4BC10 Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros,) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RV2331-4BC10⟨=en Characteristic: Tripping characteristics, I ² t, Let-through current https://support.industry.siemens.com/cs/ww/en/ps/3RV2331-4BC10/char Further characteristics (e.g. electrical endurance, switching frequency) http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RV2331-4BC10&objecttype=14&gridview=view1						

last modified:

6/25/2022 🖸