

SMBJ5.0(C)A~SMBJ440(C)A

600W Surface Mount Transient Voltage Suppressors

Features

- ◆ Optimized for LAN protection applications
- ◆ Ideal for ESD protection of data lines in accordance with IEC 1000-4-2(IEC801-2)
- ◆ Ideal for EFT protection of data lines in accordance with IEC 1000-4-4(IEC801-2)
- ◆ Plastic package has Underwriters Laboratory Flammability Classification 94V-0
- ◆ Glass passivated junction chip
- ◆ 600w peak pulse power capability
- ◆ Excellent clamping capability
- ◆ Low incremental surge resistance
- ◆ Fast response time: typically less than 1.0ps from 0v to V_{BR} min
- ◆ High temperature soldering guaranteed:
260°C/10S at terminals

Mechanical Data

Case : Molded plastic body


Terminals : Solder plated, solderable per MIL-STD-750, Method 2026

Polarity : Polarity symbol marking on body

Mounting Position : Any

Weight : 0.0035 ounce, 0.098 grams

DO-214AA/SMB



Uni-Polar

Bi-Polar



Dimensions in inches and (millimeters)

Maximum Ratings And Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified.

Parameter	SYMBOLS	VALUE	UNITS
Peak pulse power dissipation with a 10/1000 μ s wavetorm(NOTE 1,2,FIG.1)	P _{PPM}	Minimum 600	Watts
Peak forward surge current (Note 1,2,3)	I _{FSM}	100.0	Amps
Peak pulse current with a 10/1000 μ s waveform(NOTE 1)	I _{PPM}	See Table 1	Amps
Steady state power dissipation (Note 3)	P _{M(AV)}	5.0	Watts
Maximum instantaneous forward voltage at 50A(Note 3,4) unidirectional only	V _F	3.5/5.0	Volts
Operating junction and storage temperature range	T _{STG} , T _J	-55 to + 150	°C

Notes:1.Non-repetitive current pulse,per Fig.3 and derated above T_A=25°C per Fig.2

2.Mounted on 5.0mm copper pads to each terminal

3.Measured on 8.3ms single half sine-wine.For uni-directional devices only.

4.V_F=3.5V on SMB-5.0 thru SMB-220 devices and V_F=5.0V on SMB-220 thru SMB-440 devices

Type		Peak Pulse Power	Stand-off Voltage	Maximum Reverse Current at VR	Breakdown Voltage at IT		Test Current	Maximum Peak Pulse Current	Maximum Clamping Voltage at Ipp
Uni-Polar	Bi-Polar	PPP	V(R)	IR	V (BR) (V)		IT	Ipp	Vc
		(W)	(V)	(μ A)	Min.	Max.			
SMBJ5.0A	SMBJ5.0CA	600	5	800	6.4	7	10	65.3	9.2
SMBJ6.0A	SMBJ6.0CA	600	6	800	6.67	7.37	10	58.3	10.3
SMBJ6.5A	SMBJ6.5CA	600	6.5	500	7.22	7.98	10	53.6	11.2
SMBJ7.0A	SMBJ7.0CA	600	7	200	7.78	8.6	10	50.0	12.0
SMBJ7.5A	SMBJ7.5CA	600	7.5	100	8.33	9.21	1	46.6	12.9
SMBJ8.0A	SMBJ8.0CA	600	8	50	8.89	9.83	1	44.2	13.6
SMBJ8.5A	SMBJ8.5CA	600	8.5	20	9.44	10.4	1	41.7	14.4
SMBJ9.0A	SMBJ9.0CA	600	9	10	10	11.1	1	39.0	15.4
SMBJ10A	SMBJ10CA	600	10	5	11.1	12.3	1	35.3	17.0
SMBJ11A	SMBJ11CA	600	11	1	12.2	13.5	1	33.0	18.2
SMBJ12A	SMBJ12CA	600	12	1	13.3	14.7	1	30.2	19.9
SMBJ13A	SMBJ13CA	600	13	1	14.4	15.9	1	28.0	21.5
SMBJ14A	SMBJ14CA	600	14	1	15.6	17.2	1	25.9	23.2
SMBJ15A	SMBJ15CA	600	15	1	16.7	18.5	1	24.6	24.4
SMBJ16A	SMBJ16CA	600	16	1	17.8	19.7	1	23.1	26.0
SMBJ17A	SMBJ17CA	600	17	1	18.9	20.9	1	21.8	27.6
SMBJ18A	SMBJ18CA	600	18	1	20	22.1	1	20.6	29.2
SMBJ20A	SMBJ20CA	600	20	1	22.2	24.5	1	18.6	32.4
SMBJ22A	SMBJ22CA	600	22	1	24.4	26.9	1	16.9	35.5
SMBJ24A	SMBJ24CA	600	24	1	26.7	29.5	1	15.5	38.9
SMBJ26A	SMBJ26CA	600	26	1	28.9	31.9	1	14.3	42.1
SMBJ28A	SMBJ28CA	600	28	1	31.1	34.4	1	13.3	45.4
SMBJ30A	SMBJ30CA	600	30	1	33.3	36.8	1	12.4	48.4
SMBJ33A	SMBJ33CA	600	33	1	36.7	40.6	1	11.3	53.3
SMBJ36A	SMBJ36CA	600	36	1	40	44.2	1	10.4	58.1
SMBJ40A	SMBJ40CA	600	40	1	44.4	49.1	1	9.3	64.5
SMBJ43A	SMBJ43CA	600	43	1	47.8	52.8	1	8.7	69.4
SMBJ45A	SMBJ45CA	600	45	1	50	55.3	1	8.3	72.7
SMBJ48A	SMBJ48CA	600	48	1	53.3	58.9	1	7.8	77.4
SMBJ51A	SMBJ51CA	600	51	1	56.7	62.7	1	7.3	82.4
SMBJ54A	SMBJ54CA	600	54	1	60	66.3	1	6.9	87.1
SMBJ58A	SMBJ58CA	600	58	1	64.4	71.2	1	6.5	93.6
SMBJ60A	SMBJ60CA	600	60	1	66.7	73.7	1	6.2	96.8
SMBJ64A	SMBJ64CA	600	64	1	71.1	78.6	1	5.9	103
SMBJ70A	SMBJ70CA	600	70	1	77.8	86	1	5.3	113
SMBJ75A	SMBJ75CA	600	75	1	83.3	92.1	1	5.0	121
SMBJ78A	SMBJ78CA	600	78	1	86.7	95.8	1	4.8	126
SMBJ85A	SMBJ85CA	600	85	1	94.4	104	1	4.4	137
SMBJ90A	SMBJ90CA	600	90	1	100	111	1	4.1	146
SMBJ100A	SMBJ100CA	600	100	1	111	123	1	3.7	162
SMBJ110A	SMBJ110CA	600	110	1	122	135	1	3.4	177
SMBJ120A	SMBJ120CA	600	120	1	133	147	1	3.1	193
SMBJ130A	SMBJ130CA	600	130	1	144	159	1	2.9	209
SMBJ150A	SMBJ150CA	600	150	1	167	185	1	2.5	243
SMBJ160A	SMBJ160CA	600	160	1	178	197	1	2.3	259
SMBJ170A	SMBJ170CA	600	170	1	189	209	1	2.2	275
SMBJ180A	SMBJ180CA	600	180	1	201	222	1	2.1	292
SMBJ188A	SMBJ188CA	600	188	1	209	231	1	2.0	304
SMBJ200A	SMBJ200CA	600	200	1	224	247	1	1.9	324
SMBJ220A	SMBJ220CA	600	220	1	246	272	1	1.7	356
SMBJ250A	SMBJ250CA	600	250	1	279	309	1	1.5	405
SMBJ300A	SMBJ300CA	600	300	1	335	371	1	1.3	486
SMBJ350A	SMBJ350CA	600	350	1	391	432	1	1.1	567
SMBJ400A	SMBJ400CA	600	400	1	447	494	1	0.9	648
SMBJ440A	SMBJ440CA	600	440	1	492	543	1	0.9	713

Ratings And Characteristic Curves

Fig1. Peak Pulse Power Rating Curve




Fig2. Pulse Derating Curve




Fig3. Clamping Power Pulse Waveform




Fig4. Maximum Non-Repetitive Forward Surge Current Unidirectional Only




Fig5. Typical Junction Capacitance

