


**SOD-123**

**Marking: S8**
**特征 Features**

- 大电流承受能力。High Current Capability
- 正向压降低。Low Forward Voltage Drop

**机械数据 Mechanical Data**





- 封装: SOD-123 封装 SOD-123 Small Outline Plastic Package
- 极性: 色环端为负极 Polarity: Color band denotes cathode end
- 环氧树脂 UL 易燃等级 Epoxy UL: 94V-0
- 安装位置: 任意 Mounting Position: Any

**极限值和温度特性(TA = 25°C 除非另有规定)**
**Maximum Ratings & Thermal Characteristics (Ratings at 25°C ambient temperature unless otherwise specified.)**

参数 Parameters	符号 Symbol	BAT43W			单位 Unit
最大可重复峰值反向电压 Maximum repetitive peak reverse voltage	VRRM	40			V
最大均方根电压 Maximum RMS voltage	VRMS	28			V
最大直流阻断电压 Maximum DC blocking voltage	VDC	40			V
最大正向平均整流电流 Maximum average forward rectified current	IFM	350			mA
峰值正向浪涌电流 8.3ms 单一正弦半波 Peak forward surge current 8.3 ms single half sine-wave	IFSM	2			A
功率消耗 Power Dissipation	PD	400			mW
典型热阻 T Typical thermal resistance	RθJA	250			°C/W
工作结温 Operating junction temperature	Tj	125			°C
存储温度 Storage temperature range	TSTG	-50-+150			°C


**电特性 (TA = 25°C 除非另有规定)**
**Electrical Characteristics (Ratings at 25°C ambient temperature unless otherwise specified).**

参数 Parameters	符号 Symbol	测试条件 Test conditions	BAT43W			单位 Unit
最大正向电压 Maximum forward voltage	VF	IF = 20mA IF = 200mA	0.370 0.600			V
最大反向电压 Maximum reverse breakdown voltage	VR	IR=100uA	40	30	20	V
最大反向电流 Maximum reverse current	IR	VR=30V <b>BAT43W</b>	5.0			uA
典型结电容 Type junction capacitance	Cj	VR =0V, f = 1MHz	50			pF
反向恢复时间 Reverse recovery time	Trr	IF=IR=200mA, Irr=0.1xIR,RL=100 Ω	10			ns

**特性曲线 Characteristic Curves**


**SOD-123 PACKAGE OUTLINE**

Plastic surface mounted package




SYMBOL	DIMENSIONS	
	MIN.	MAX.
A	1.050	1.250
A1	0.000	0.100
A2	1.050	1.150
b	0.450	0.650
c	0.080	0.150
D	1.500	1.700
E	2.600	2.800
E1	3.550	3.850
L	0.500REF	
L1	0.250	0.450
$\theta$	0°	8°

**焊盘设计参考**

Precautions: PCB Design

Recommended land dimensions for SOD-123 diode. Electrode patterns for PCBs



技术要求:

- 中心距: 3.24
  - 脚 宽: 0.55
  - 焊盘宽: 1.00
  - 脚 长: 0.50
  - 焊盘长: 0.80
- 1, 塑封体尺寸: 2.70 X 1.60
  - 2: 未注公差为:  $\pm 0.05$
  - 3, 所有单位: mm