

APPROVAL SHEET

 Customer Name :
 Customer P/N :

 Frequency : 32.768000 KHz

 Aker Approved P/N : D31N-032768-B-AL-02

 Aker MPN : D31N-032768-B-AL-02

 REVISION : A0

 ISSUED DATE : 2022/8/25

APPROVED	CHECKED	PREPARED
Evrnest		Kiku
APPROVED BY CUST	OMER	

AKER TECHNOLOGY CO., LTD.

ADDRESS: NO 11-3, Jianguo Rd., Tanzi Dist., Taichung City 427, Taiwan.

TEL: 886-4-25335978 FAX: 886-4-25336011

Web: www.aker.com.tw MSL:Level 1

RoHS compliant



Aker Approved P/N	:	D31N-032768-B-AL-02	
APPROVED	:	Earnest	SHEET: 1 of 4
PREPARED	:	Kiku	REV . : A0
			Confidential

Date	Reviser	Revise contents
2022/8/25	Kiku	Initial Released



	Aker Approved P/N	:	D31N-032768-B-AL-02
--	-------------------	---	---------------------

APPROVED : Earnest SHEET : 2 of 4

PREPARED : Kiku REV . : A0

Confidential

TUNING FORK CRYSTAL SPECIFICATION

1. ELECTRICAL CHARACTERISTICS

Measurement temperature: 25±2°C

Item	Symbol	Rating	Note
Storage temperature range	T_stg	-55~+125°C	
Maximum drive level	DL max.	1.0 μW max.	


Operating temperature range	T_use	-40∼+85°C	
Drive level	DL	$0.1~\muW$ typ.	

	Item	Symbol	Specification	Condition
1	Nominal frequency	f_nom	32.768 kHz	
2	Frequency tolerance	f_tol	± 20 × 10 ⁻⁶	
3	Load capacitance	CL	6.0 pF	
4	Motional resistance	R ₁	70 kΩ max.	Measured with ATI 4192A Impedance analyzer OSC LEVEL = 0.1V
5	Motional capacitance	C ₁	3 fF typ.	
6	Shunt capacitance	C ₀	1 pF typ.	Measured with ATI 4192A Impedance analyzer OSC LEVEL = 0.1V
7	Turnover temperature	Ti	25 ± 5°C	Measure this coefficient at 5 points of -40°C, -20°C, 25°C, 60°C, 85°C
8	Parabolic coefficient	В	$(-0.03\pm10\%) \times 10^{-6}$ /°C ²	using C-MOS circuit.
9	Frequency aging	f_age	± 3 × 10 ⁻⁶ /year	25±3°C, First year
10	Insulation resistance	IR	500 M Ω min.	Measured with ATI 4329A Insulation Resistance Meter Apply DC100V




Aker Approved P/N:		D31N-032768-B-AL-02	
APPROVED	:	Earnest	SHEET: 3 of 4
PREPARED	:	Kiku	REV . : A0
			Confidential


2. INTERNAL CONNECTION:



3. RECOMMENDED SOLDERING PATTERN: (Unit: mm)



4. SOLDERING REFLOW PROFILE:




Please kindly be noted that AKER DO NOT guarantee parts quality which involves human security application.




Aker Approved P/N:	D31N-0327	68-B-AL-02
APPROVED :	Earnest	SHEET: 4 of 4
PREPARED :	Kiku	REV . : A0

Confidential

5. DIMENSIONS: (Unit: mm)







- *1 Product name
- *2 Type of product
- *3 Specification
- *4 CL (6pF:A, 7pF:B, 9pF:J, 12.5pF:F)
- *5 Year of production (Last digit of year)
- *6,7 Week of production (01 ~ 52)