# MSKSEMI 美森科













TV

TSS

MOV

GDT

PIFD

ESD9X5.0ST5G-MS

**Product specification** 





#### **Features**

- 80W peak pulse power per line (tP = 8/20μs)
- SOD-923 package
- Replacement for MLV(0402)
- Bidirectional configurations
- Response time is typically < 1ns</li>
- Low clamping voltage
- RoHS compliant
- Transient protection for data lines to IEC61000-4-2(ESD) ±30KV(air), ±30KV(contact);
  IEC61000-4-4 (EFT) 40A (5/50ns)

## **Mechanical Characteristics**

- Lead finish:100% matte Sn(Tin)
- Mounting position: Any
- Qualified max reflow temperature:260C
- Device meets MSL 1 requirements
- Pure tin plating: 7 ~ 17 um
- Pin flatness:≤3mil

## **Applications**

- Cellular phones
- Portable devices
- Digital cameras
- Power supplies


#### **Reference News**

PACKAGE OUTLINE	Pin Configuration	Marking
WHEEL CONTROL OF THE PARTY OF T		В
SOD-923		



## **Electronics Parameter**

Symbol	Parameter		
VRWM	Peak Reverse Working Voltage		
I <sub>R</sub>	Reverse Leakage Current @ V <sub>RWM</sub>		
V <sub>BR</sub>	Breakdown Voltage @ I⊤		
lτ	Test Current		
<b>I</b> PP	Maximum Reverse Peak Pulse Current		
Vc	Clamping Voltage @ I <sub>PP</sub>		
P <sub>PP</sub>	Peak Pulse Power		
Cı	Junction Capacitance		
lF	Forward Current		
V <sub>F</sub>	Forward Voltage @ I <sub>F</sub>		



# Electrical characteristics per line@25C (unless otherwise specified)

Parameter	Symbol	Conditions	Min.	Тур.	Max.	Units
Peak Reverse Working Voltage	VRWM				5	V
Breakdown Voltage	V <sub>BR</sub>	I <sub>t</sub> = 1mA	5.6	6.7	7.8	V
Reverse Leakage Current	I <sub>R</sub>	V <sub>RWM</sub> = 5V T=25C			1.0	uA
Maximum Reverse Peak Pulse Current	<b>I</b> PP			5		А
Clamping Voltage	Vc	I <sub>PP</sub> =1A			8	V
Clamping Voltage	Vc	I <sub>PP</sub> =3A			13	V
Clamping Voltage	Vc	I <sub>PP</sub> =5A			15	V
Junction Capacitance	Cj	V <sub>R</sub> =0V f = 1MHz		12	15	pF

# Absolute maximum rating@25℃


Rating	Symbol	Value	Units
Peak Pulse Power (t <sub>p</sub> =8/20µs)	$P_pp$	80	W
Operating Temperature	TJ	-55 to + 150	°C
Storage Temperature	Тѕтс	-55 to + 150	$^{\circ}$



## **Typical Characteristics**



Fig 1.Pulse Waveform






Fig 3.Typical Breakdown Voltage vs. Temperature




Fig 4. Typical Leakage Current vs. Temperature




Fig 5. Clamping voltage vs. Peak pulse current






Fig 6. Non-Repetitive Peak Pulse Power vs. Pulse time



### **Solder Reflow Recommendation**

Peak Temp=257 °C, Ramp Rate=0.802deg. °C/sec




#### **PCB** Design


For TVS diodes a low-ohmic and low-inductive path to chassis earth is absolutely mandatory in order to achieve good ESD protection. Novices in the area of ESD protection should take following suggestions to heart:

- Do not use stubs, but place the cathode of the TVS diode directly on the signal trace.
- Do not make false economies and save copper for the ground connection.
- Place via holes to ground as close as possible to the anode of the TVS diode.
- Use as many via holes as possible for the ground connection.
- Keep the length of via holes in mind! The longer the more inductance they will have.




## PACKAGE MECHANICAL DATA





		Millimeters			Inches		
Dim	Min	Nom	Max	Min	Nom	Max	
Α	0.36	0.40	0.43	0.014	0.016	0.017	
b	0. 15	0.20	0.25	0.006	0.008	0.010	
С	0.07	0. 12	0. 17	0.003	0.005	0.007	
D	0.75	0.80	0.85	0.030	0.031	0.033	
E	0.55	0.60	0.65	0.022	0.024	0.026	
HE	0.95	1.00	1.05	0.037	0.039	0.041	
L	0.05	0. 10	0. 15	0.002	0.004	0.006	

# **Suggested Pad Layout**



#### Note:

- 1. Controlling dimension: in millimeters.
- 2.General tolerance:±0.05mm.
- 3. The pad layout is for reference purposes only.

## **REEL SPECIFICATION**

P/N	PKG	QTY	
ESD9X5.0ST5G-MS	SOD-923	8000	



## **Attention**

- Any and all MSKSEMI Semiconductor products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your MSKSEMI Semiconductor representative nearest you before using any MSKSEMI Semiconductor products described or contained herein in such applications.
- MSKSEMI Semiconductor assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specificationsof any andall MSKSEMI Semiconductor products described or contained herein.
- Specifications of any and all MSKSEMI Semiconductor products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer'sproducts or equipment.
- MSKSEMI Semiconductor. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with someprobability. It is possiblethat these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits anderror prevention circuitsfor safedesign, redundant design, and structural design.
- In the event that any or all MSKSEMI Semiconductor products (including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from theauthorities concerned in accordance with the above law.
- No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of MSKSEMI Semiconductor.
- Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production. MSKSEMI Semiconductor believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. Whendesigning equipment, referto the "Delivery Specification" for the MSKSEMI Semiconductor productthat you intend to use.