

规格说明:Specifications:

电气特性:Electrical:

- 1. 额定电流: Current Rating  
1.5A/contact terminal
- 2. 额定电压: Voltage Rating  
30V DC
- 3. 接触阻抗: Contact Resistance  
30 milliohms MAX
- 4. 耐电压: Dielectric Withstanding Voitage:  
500 V AC AT Sea Level
- 5. 绝缘阻抗: Lnsulation Resistance:  
1000MEGA ohms MIN

物理性能:Mechanical:





- 1. 插拔力: Cnncetor Mate and Unmate Force  
Mate force:3.57kgf(MAX)  
Unmate force:1.02kgf(MIN)
- 2. 端子保持力: Terminal Retenion  
1.2kgf(MIN)

原材料:Matorial:

- 1. 塑胶:Housing:  
Hing Temperature Tnermaplastics,  
UI 94V-0 PBT White/Black
- 2. 端子:Contact:Copper Alloy C2680
- 3. 外壳:Shell: Copper Alloy C2680/SPCC

电镀:Finish:

- 1. 端子:Contact: Piated Gold in Mating Area;  
Tin On Solder Talls
- 2. 外壳:Shell:  
Nickel Plating



PCB LAYOUT

04XN-1XVZ14-S1

- 1:SPCC 5:BRASS
- S:Scrolls F:Flat
- 1:Au 1U"
- 6:Au 30U"
- B:Black O: Orange
- G: Green W: White BL:Blue
- 1:PBT
- 2:PA6T
- 3:PA9T
- 4:LCP

new		2015/5/3	A	瀚源	
ECN BO.		DESCRIPTION.	DATE.		REV.
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALT: 1/2	SCALE: 3:1
Mikey	Tom	Jerry	PART NAME 04XN-1XVZ14-S1	UNLESS OTHERWISE SPECIFIED, TOLERANCE: X. ±0.25 X.x ±0.20 X.xx ±0.15 ANGULAIR ±3	FILE.NO.
			MODEL NAME 04XN-1XVZ14-S1		
3RD ANGLE PROJ			HanElectricity Co.,LTD		