



P.C.B LAYOUT

04XN-1XVC10-F1

- 1:Au 1U"
- 6:Au 30U"
- 1:SPCC 5:BRASS
- S:Scrolls F:Flat
- B:Black O: Orange
- G: Green W: White BL:Blue
- 1:PBT
- 2:PA6T
- 3:PA9T
- 4:LCP

规格说明:Specifications:

电气特性:Electrical:

- 1.额定电流: Current Rating
1.5A/contact terminal
- 2.额定电压: Voltage Rating
30V DC
- 3.接触阻抗:Contact Resistance
30 milliohms MAX
- 4.耐电压:Dielectnic Withstanding Voitage:
500 V AC AT Sea Levol
- 5.绝缘阻抗:Insulation Resistance:
1000MEGA ohms MIN

物理性能:Mechanical:

- 1.插拔力: Cnnector Mate and Unmate Force
Mate force:3.57kgf(MAX)
Unmate force:1.02kgf(MIN)
- 2.端子保持力: Terminal Retenion
1.2kgf(MIN)

原材料:Matorial:

- 1.塑胶:Housing:
Hing Temperature Tnermaplastics,
UI 94V-0 LCP Black
- 2.端子:Contact:Copper Alloy C2680
- 3.外壳:Shell: SPCC

电镀:Finish:

- 1.端子:Contact: Plated Gold in Mating Area;
Tin On Solder Talls
- 2.外壳:Shell:
Nickel Plating

| | | | | | |
|----------------|---------|----------|---|--|------------|
| new | | 2015/5/3 | A | 瀚源 | |
| ECN BO. | | DATE. | REV. | | |
| DESIGNED | CHECKED | APPROVAL | DRAWING NUMBER | SCALT: 1/2 | SCALE: 3:1 |
| Mikey | Tom | Jerry | PART NAME 04XN-1XVC10-F1 MODEL NAME 04XN-1XVC10-F1 | UNLESS OTHERWISE SPECIFIED, TOLERANCE: X. ±0.25 X.x ±0.20 X.xx ±0.15 ANGULAIR ±3 | FILE.NO. |
| 3RD ANGLE PROJ | | | HanElectricity Co.,LTD | | |