

DESCRIPTION

The PSM712-LF-T7 transient voltage suppressor (TVS) diode is designed for asymmetrical (12V to -7V) protection in multi-point data

transmission standard RS-485 applications. The

PSM712-LF-T7 may be used to protect devices from transient voltages resulting from electrostatic discharge (ESD), electrical fast transients (FET), and lightning.

The PSM712-LF-T7 features 400 Watts ($t_p=8/20\mu s$) of power handling capability to accommodate the higher transient voltage levels which may be expected in extended common mode applications. This provides higher equipment reliability and eliminates the “guess work” required when using zener diodes that are not rated to handle such transient conditions.

The integrated design aids in reducing voltage over-shoot associated with trace inductance. The low clamping voltage of the PSM712-LF-T7 minimizes the stress on the protected transceiver.

The SOT-23 package allows flexibility in the design of “crowded” circuit boards.

ORDERING INFORMATION

- ✧ Device: PSM712-LF-T7
- ✧ Package: SOT-23
- ✧ Marking: 712
- ✧ Material: Halogen free
- ✧ Packing: Tape & Reel
- Quantity per reel: 3,000pcs

APPLICATIONS

- ✧ Protection of RS-485 transceivers with extended

common-mode range


- ✧ Security systems
- ✧ Automatic Teller Machines
- ✧ HFC systems
- ✧ Networks

FEATURES


- ✧ 400 watts peak pulse power ($t_p=8/20\mu s$)
- ✧ Transient protection for asymmetrical data lines to IEC 61000-4-2 (ESD) $\pm 15kV$ (air), $\pm 8kV$ (contact) IEC 61000-4-4 (FET) 40A (5/50ns) IEC 61000-4-5 (Lightning) 12A (8/20 μs)
- ✧ Protects two +12V to -7V lines
- ✧ Low capacitance
- ✧ Low leakage current
- ✧ Low clamping voltage
- ✧ Solid-state silicon avalanche technology
- ✧ RoHS compliant

MACHANICAL DATA

- ✧ SOT-23 package
- ✧ Flammability Rating: UL 94V-0
- ✧ Terminal: Matte tin plated.
- ✧ Packaging: Tape and Reel
- ✧ High temperature soldering guaranteed: 260°C/10s
- ✧ Reel size: 7 inch








SOT-23 top view



Schematic diagram

ABSOLUTE MAXIMUM RATING			
Symbol	Parameter	Value	Units
P _{PP}	Peak Pulse Power (8/20μs)	400	W
I _{PP}	Peak Pulse Current (8/20μs)	17	A
V _{ESD}	ESD per IEC 61000-4-2 (Air) ESD per IEC 61000-4-2 (Contact)	±15 ±8	kV
T _{OPT}	Operating Temperature	-55/+150	°C
T _{STG}	Storage Temperature	-55/+150	°C

ELECTRICAL CHARACTERISTICS (T _{amb} =25°C)									
Symbol	Parameter	Test Condition	Pin 1 to 3 and Pin 2 to 3 (12V) TVS			Pin 3 to 1 and Pin 3 to 2 (7V) TVS			Units
			Min	Typ	Max	Min	Typ	Max	
V _{RWM}	Reverse Working Voltage	Pin 3 to 1 or Pin 2 to 1			12			7	V
V _{BR}	Reverse Breakdown Voltage	I _T = 1mA	13.3			7.5			V
I _R	Reverse Leakage Current	V _R = V _{RWM}			1			20	μA
V _{C1}	Clamping Voltage 1	I _{PP} = 5A, t _p = 8/20μs			20			10	V
V _{C2}	Clamping Voltage 2	I _{PP} = 17A, t _p = 8/20μs			26			12	V
C _{J1}	Junction Capacitance 1	V _R = 0V, f = 1MHz			75			75	pF
C _{J2}	Junction Capacitance 2	V _R = V _{RWM} , f = 1MHz		45			45		pF

ELECTRICAL CHARACTERISTICS CURVE
Non-Repetitive Peak Pulse Power vs. Pulse Time

Power Derating Curve

Pulse Waveform

Clamping Voltage vs. Peak Pulse Current

Capacitance vs. Reverse Voltage


Package Outline

SOT-23

Dimensions in mm

