



SPECIFICATIONS



Current Rating: 1.5 Amps
 Insulation Resistance: 1000M Ω Min
 Contact Resistance: 20m Ω Max
 Withstanding Voltage: AC 500V
 Operation Temperature: -40°to+105°
 Contact Material: Brass
 Standard: PA6T
 Insulator Material: Polyester(UL 94V-0)
 Contact Plating: Gold Flash
 Max.Processing Temp: 240°C for30-60seconds
 (260°C for 5 seconds)

P/N	PIN	DIM.A	DIM.B
FH2.0-09-01PZD	1	0.00	2.00
FH2.0-09-02PZD	2	2.00	4.00
FH2.0-09-03PZD	3	4.00	6.00
FH2.0-09-04PZD	4	6.00	8.00
FH2.0-09-05PZD	5	8.00	10.00
FH2.0-09-06PZD	6	10.00	12.00
FH2.0-09-07PZD	7	12.00	14.00
FH2.0-09-08PZD	8	14.00	16.00
FH2.0-09-09PZD	9	16.00	18.00
.....
FH2.0-09-40PZD	40	(PIN-1)x2.0	(PIN)x2.0



PART NUMBER DESCRIPTION:

FH2.0-09-NPZD



RECOMMEND P.C.B LAYOUT
 PCB TOLERANCE:±0.05 (TOP VIEW)

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE:2.0FH H6.35 1xnPin 180度 Y型 PC2.8 6T
			PAR FH2.0-09-NPZD
DECIMALS:	ANGLES:		DWN
X.±0.30	X°±5'		CHKD
X.X±0.20	X.X°±1'	APVD	
X.XX±0.10	X.XX°±0.5'	CUSTOMER COPY	SCALE N:A UNIT:MM
		SIZE:A4	UNIT:MM
		SHEET:1F1	REV:A