kHz RANGE CRYSTAL UNIT

C - TYPE C - 2 TYPE/C - 4 TYPE

 $\begin{array}{lll} \bullet \mbox{Frequency range} & : & 32.768 \mbox{ kHz} \ (20 \mbox{ kHz} {\sim} 120 \mbox{ kHz}) \\ \bullet \mbox{Thickness} & : & \phi \mbox{ 1.2 mm} \mbox{ } {\sim} \phi \mbox{ 2.0 mm} \mbox{ Max}. \\ \end{array}$

•Overtone order : Fundamental

•Applications : Clock and Microcomputer



Specifications for C-TYPE (characteristics)

Item	Symbol	C-002RX	C-004R	C-005R	Conditions / Remarks
Nominal frequency range	f_nom	32.768 kHz			
Storage temperature	T_stg	-20 °C to +70 °C			Storage as single product.
Operating temperature	T_use	-10 °C to +60 °C			
Level of drive	DL	1.0 μW Max.			
Frequency tolerance (standard)	f_tol	±20 × 10 ⁻⁶			+25 °C, DL=0.1 μW
Turnover temperature	Ti	+25 °C ± 5 °C			
Parabolic coefficient	В	−0.04 × 10 ⁻⁶ / °C ² Max.			
Load capacitance	CL	6 pF to ∞			Please specify
Motional resistance (ESR)	R1	50, 60 kΩ Max. (30 kΩ Typ.)	50 kΩ Max. (30 kΩ Typ.)	50 kΩ Max. (37 kΩ Typ.)	
Motional capacitance	C1	2.0 fF	2.0 fF	1.9 fF Typ.	
Shunt capacitance	C ₀	0.85 pF	0.85 pF	0.75 pF Typ.	
Frequency aging	f_age	±3 × 10 ⁻⁶ / year Max.			+25 °C, First year

Specifications for C-2 TYPE C-4 TYPE (characteristics)

Item	Symbol	C-2 TYPE	C-4 TYPE	Conditions / Remarks	
Nominal frequency range	f_nom	20 kHz to 120 kHz	32 kHz to 120 kHz	Please contact us about available frequencies.	
Storage temperature	T_stg	-20 °C to	+70 °C	Storage as single product.	
Operating temperature	T_use	-10 °C to +60 °C			
Level of drive	DL	1.0 μW	Max.		
Frequency tolerance (standard)	f_tol	±20 × 10 ⁶ ,±50 × 10 ⁶ ,±100 × 10 ⁶ ±50 × 10 ⁻⁶ ,±100 × 10 ⁻⁶		+25 °C, DL=0.1 μW	
Turnover temperature	Ti	+25 °C ± 5 °C			
Parabolic coefficient	В	-0.04 × 10 ⁻⁶ / °C ² Max.			
Load capacitance	CL	6 pF to ∞		Please specify	
Motional resistance (ESR)	R1	As per table below			
Motional capacitance	C1	4.0 fF to			
Shunt capacitance	Co	2.0 pF to			
Frequency aging	f_age	±5 × 10 ⁻⁶ / y	+25 °C, First year		

Motional resistance C-2 TYPE

Frequency	20 kHz≦f_nom<31.2 kHz	31.2 kHz≦f_nom<40 kHz	40 kHz≦f_nom<90 kHz	90 kHz≦f_nom≦120 kHz
Motional resistance	55 kΩ Max.	35 kΩ Max.	20 kΩ Max.	12 kΩ Max.


Motional resistance C-4 TYPE

Frequency	32 kHz≦f_nom<38 kHz	38 kHz≦f_nom<60 kHz	60 kHz≦f_nom<74 kHz	74 kHz≦f_nom≦100 kHz	100 kHz <f_nom≦120 khz<="" th=""></f_nom≦120>
Motional resistance	55 kΩ Max.	30 kΩ Max.	25 kΩ Max.	22 kΩ Max.	15 kΩ Max.

①Model ②Frequency ③Load capacitance(pF) ④Frequency tolerance(× 10⁻⁶, +25 °C)

External dimentions





Model	L ₁	L ₂	D ₁	D ₂	В
C-002RX C-2 TYPE	6.0 Max.	4.0 Min.	ф 2.0 Max.	φ 0.2	0.7
C-004R C-4 TYPE	5.0 Max.	4.0 Min.	ф 1.5 Max.	ф 0.18	0.5
C-005R	4.6 Max.	4.0 Min.	φ 1.2 Max.	φ 0.15	0.3

PROMOTION OF ENVIRONMENTAL MANAGEMENT SYSTEM CONFORMING TO INTERNATIONAL STANDARDS

At Seiko Epson, all environmental initiatives operate under the Plan-Do-Check-Action (PDCA) cycle designed to achieve continuous improvements. The environmental management system (EMS) operates under the ISO 14001 environmental management standard.

All of our major manufacturing and non-manufacturing sites, in Japan and overseas, completed the acquisition of ISO 14001 certification.

ISO 14000 is an international standard for environmental management that was established by the International Standards Organization in 1996 against the background of growing concern regarding global warming, destruction of the ozone layer, and global deforestation.

WORKING FOR HIGH QUALITY

In order provide high quality and reliable products and services than meet customer needs,

Seiko Epson made early efforts towards obtaining ISO9000 series certification and has acquired ISO9001 for all business establishments in Japan and abroad. We have also acquired ISO/TS 16949 certification that is requested strongly by major automotive manufacturers as standard.

ISO/TS16949 is the international standard that added the sector-specific supplemental requirements for automotive industry based on ISO9001.

Explanation of the mark that are using it for the catalog



►Pb free.



- ▶ Complies with EU RoHS directive.
 - *About the products without the Pb-free mark.

 Contains Pb in products exempted by EU RoHS directive.

 (Contains Pb in sealing glass, high melting temperature type solder or other.)



▶ Designed for automotive applications such as Car Multimedia, Body Electronics, Remote Keyless Entry etc.



▶ Designed for automotive applications related to driving safety (Engine Control Unit, Air Bag, ESC etc.).

Notice

- This material is subject to change without notice.
- Any part of this material may not be reproduced or duplicated in any form or any means without the written permission of Seiko Epson.
- The information about applied circuitry, software, usage, etc. written in this material is intended for reference only. Seiko Epson does not assume any liability for the occurrence of infringing on any patent or copyright of a third party. This material does not authorize the licensing for any patent or intellectual copyrights.
- When exporting the products or technology described in this material, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations.
- You are requested not to use the products (and any technical information furnished, if any) for the development and/or manufacture of
 weapon of mass destruction or for other military purposes. You are also requested that you would not make the products available to
 any third party who may use the products for such prohibited purposes.
- These products are intended for general use in electronic equipment. When using them in specific applications that require extremely high reliability, such as the applications stated below, you must obtain permission from Seiko Epson in advance.
 - / Space equipment (artificial satellites, rockets, etc.) / Transportation vehicles and related (automobiles, aircraft, trains, vessels, etc.) / Medical instruments to sustain life / Submarine transmitters / Power stations and related / Fire work equipment and security equipment / traffic control equipment / and others requiring equivalent reliability.
- · All brands or product names mentioned herein are trademarks and/or registered trademarks of their respective.