

Surface Mount Superfast Recovery Rectifier

Reverse Voltage – 50 to 600 V

Forward Current – 1 A

FEATURES

- For surface mounted applications
- Low profile package
- Glass Passivated Chip Junction
- Superfast reverse recovery time
- Lead free in comply with EU RoHS 2011/65/EU directives

MECHANICAL DATA

- Case: SMA
- Terminals: Solderable per MIL-STD-750, Method 2026
- Approx. Weight: 0.055g / 0.002oz

PINNING

PIN	DESCRIPTION
1	Cathode
2	Anode



Top View

Marking Code: ES1A~ES1J: ES1A~ES1J
Simplified outline SMA and symbol

Absolute Maximum Ratings and Characteristics

Ratings at 25 °C ambient temperature unless otherwise specified. Single phase, half wave, 60 Hz, resistive or inductive load.
For capacitive load, derate current by 20%.

Parameter	Symbols	ES1A	ES1B	ES1C	ES1D	ES1E	ES1G	ES1J	Units		
Maximum Repetitive Peak Reverse Voltage	V _{RRM}	50	100	150	200	300	400	600	V		
Maximum RMS voltage	V _{RMS}	35	70	105	140	210	280	420	V		
Maximum DC Blocking Voltage	V _{DC}	50	100	150	200	300	400	600	V		
Maximum Average Forward Rectified Current at T _L = 100 °C	I _{F(AV)}	1						A			
Peak Forward Surge Current 8.3 ms Single Half Sine Wave Superimposed on Rated Load (JEDEC Method)	I _{FSM}	30						A			
Maximum Forward Voltage at 1 A	V _F	1			1.25		1.70	V			
Maximum DC Reverse Current Ta = 25 °C at Rated DC Blocking Voltage Ta = 125 °C	I _R	5 100						μA			
Typical Junction Capacitance at V _R =4V, f=1MHz	C _j	15						pF			
Maximum Reverse Recovery Time ⁽¹⁾	t _{rr}	35						ns			
Typical Thermal Resistance ⁽²⁾	R _{θJA}	110						°C/W			
Operating and Storage Temperature Range	T _j , T _{stg}	-55 ~ +150						°C			

(1) Measured with I_F = 0.5 A, I_R = 1 A, I_{rr} = 0.25 A.

(2) P.C.B. mounted with 1.0 X 1.0" (2.54 X 2.54 cm) copper pad areas.

Fig.1 Reverse Recovery Time Characteristic And Test Circuit Diagram





Fig.2 Maximum Average Forward Current Rating




Fig.4 Typical Forward Characteristics




Fig.3 Typical Reverse Characteristics




Fig.5 Typical Junction Capacitance






Fig.6 Maximum Non-Repetitive Peak Forward Surge Current




PACKAGE OUTLINE

Plastic surface mounted package; 2 leads

SMA



The recommended mounting pad size



Marking

Type number	Marking code
ES1A	ES1A
ES1B	ES1B
ES1C	ES1C
ES1D	ES1D
ES1E	ES1E
ES1G	ES1G
ES1J	ES1J