



CUSTOMER		CUSTOMER'S P/S	
ISSUE DATE	2021.02.17	OUR P/N	XRCD105-4R7M

1. 外观尺寸图 DIMENSIONS



www.yushitong.com.cn

2. 接线图 CONNECTION (BOTTOM VIEW)




3. 绕线规格 WINDING SPEC

端子 TERMINZL	线 WIRE	圈数 TURNS	绕线方式 WINDING METHOD
S---F	Φ0.45	9TS (REF)	CLOSED

4. 电气特性 ELECTRONICS CHARACTERISTIC

客户代码 Part No.	厂方代码 OUR Part No.	电感量 Inductance at 100kHz	直流电阻 D. C. R max.	定格电流 I. D. C max.	标识 Marking	规格代码 Sample No.
	XRCD105-4R7M	4.7uH±20%	0.032 Ω	5A	4R7	—

5. 推荐回流焊温度曲线



备注:

OPERATING TEMP. :-40℃~+85℃

INDUCTANCE DROP=35% TYP. AT IDC.

制作 DRW	审核 CHK	确认 APPD	东莞市祥如电子有限公司
彭丽粉 2021.02.17	梁何娟 2021.02.17	刘俊丰 2021.02.17	

试产（样）报告

(TEST REPORT)

MODEL NO: 产品型号:	XRCD105-4R7M	EVALUATED Q' TY: 试样数:	10PCS
--------------------	--------------	--------------------------	-------

WATERIAL CODE: 磁材型号规格:	SMD 1050	TESTED DATE: 试制日期:	2021.02.17
---------------------------	----------	-----------------------	------------


(DATA)	LOTS 序号	SPC 规格	100KHz/0.25V L(uH)	DCR(Ω)						
			4R7uH±20%	MAX 0.032 Ω						
	1		4.78	0.031						
	2		4.76	0.031						
	3		4.80	0.032						
	4		4.75	0.031						
	5		4.73	0.032						
	6		4.76	0.031						
	7		4.75	0.032						
	8		4.75	0.032						
	9		4.78	0.030						
	10		4.73	0.030						
	11									
	12									
	13									
	14									
	15									

(DATA)
试样情况记录

REMARK: HM2801A HM2770A HP4342A VR-114 VR115
 备注:
 外观: OK

RESULTS: 判定: <input checked="" type="checkbox"/> 合格 (PASSED) <input checked="" type="checkbox"/> ROHS <input type="checkbox"/> 不合格, 改良后 (FAILED) 参照 (REF) _____	制样员DRW 彭丽粉 2021.02.17	东莞市祥如电子有限公司
---	-------------------------------------	-------------

包装



包装方式

LEADER部	SEAL TAPE 尺寸	10cm以上
	START CARRIER TAPE尺寸	20cm以上
	TRATLER部尺寸	10cm以上
	数量	1000pcs

