



产品规格书

CUSTOMER		CUSTOMER'S P/S	
ISSUE DATE	2023.06.09	OUR P/N	XRCD75-4R7M

1. 外观尺寸图 DIMENSIONS



2. 接线图 CONNECTION (BOTTOM VIEW)




3. 绕线规格 WINDING SPEC

端子 TERMINZL	线 WIRE	圈数 TURNS	绕线方式 WINDING METHOD
S---F	$\Phi 0.4$	10.5TS (REF)	CLOSED

4. 电气特性 ELECTRONICS CHARACTERISTIC

客户代码 Part No.	厂方代码 OUR Part No.	电感量 Inductance at 1kHz	直流电阻 D.C.R max.	定格电流 I.D.C max.	标识 Marking	规格代码 Sample No.
	XRCD75-4R7M	$4.7 \mu\text{H} \pm 20\%$	0.05Ω	3.6A	4R7	—

5. 推荐回流焊温度曲线



备注:

OPERATING TEMP. : $-40^\circ\text{C} \sim +85^\circ\text{C}$

INDUCTANCE DROP=35% TYP. AT IDC.

制作 DRW	审核 CHK	确认 APPD	东莞市祥如电子有限公司
陈泽伟	刘嘉伟	黄振伟	

2023. 06. 09	2023. 06. 09		
--------------	--------------	--	--

试产（样）报告

(TEST REPORT)

MODEL NO: 产品型号:	XRCD75-4R7M	EVALUATED Q' TY: 试样数:	10PCS
--------------------	-------------	--------------------------	-------

WATERIAL CODE: 磁材型号规格:	SMD 7850	TESTED DATE: 试制日期:	2023. 06. 09
---------------------------	----------	-----------------------	--------------


LOTS 序号	SPC 规格	1KHz/0.25V L(uH)	DCR(Ω)							
		4.7uH±20%	MAX 0.05Ω							
1		4.66	0.031							
2		4.53	0.030							
3		4.66	0.031							
4		4.56	0.030							
5		4.96	0.032							
6		4.74	0.031							
7		5.03	0.031							
8		4.64	0.031							
9		4.50	0.030							
10		4.49	0.029							
11										
12										
13										
14										
15										

(DATA) 试样情况记录

REMARK:	HM2801A HM2770A HP4342A VR-114 VR115
备注:	用100KHz 0.25V全检
外观:	OK

RESULTS: 判定: <input checked="" type="checkbox"/> 合格 (PASSED) <input checked="" type="checkbox"/> ROHS <input type="checkbox"/> 不合格, 改良后 (FAILED) 参照 (REF) _____	制样员DRW	东莞市祥如电子有限公司
	刘福田 2023. 06. 09	

包装



包装方式

LEADER部	SEAL TAPE 尺寸	10cm以上
	START CARRIER TAPE尺寸	20cm以上
	TRATLER部尺寸	10cm以上
	数量	1000pcs

