



BZT585B2V4T - BZT585B43T

SURFACE MOUNT PRECISION ZENER DIODE

Features

- ±2.0% Tolerance on Breakdown Voltage
- Small, Low Profile Surface Mount Package
- Flat Lead Package Design for Low Profile and High Power Dissipation
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- Qualified to AEC-Q101 Standards for High Reliability

Mechanical Data

- Case: SOD523
- Case Material: Molded Plastic, "Green" Molding Compound.
 UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminal Connections: Cathode Band
- Terminals: Finish Matte Tin annealed over Alloy 42 leadframe.
 Solderable per MIL-STD-202, Method 208 63
- Weight: 0.001 grams (approximate)



Top View

Ordering Information (Note 4)

Part Number	Case	Packaging
(Type Number)-7* (Note 4)	SOD523	3000/Tape & Reel

^{*}Add "-7" to the appropriate type number in Electrical Characteristics Table, example: 6.2V Zener = BZT585B6V2T-7.

Notes:

- $1.\ No\ purposely\ added\ lead.\ Fully\ EU\ Directive\ 2002/95/EC\ (RoHS)\ \&\ 2011/65/EU\ (RoHS\ 2)\ compliant.$
- 2. See http://www.diodes.com/quality/lead_free.html for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at http://www.diodes.com/products/packages.html.

Marking Information



xx = Product Type Marking Code (See Electrical Characteristics Table)



Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Single phase, half wave, 60Hz, resistive or inductive load.

For capacitance load, derate current by 20%.

Charac	teristic	Symbol	Value	Unit
Forward Voltage	@ I _F = 10mA @ I _F = 100mA	V _F	0.9 1.1	V
Continuous Forward Current		l _F	200	mA

Thermal Characteristics

Characteristic	Symbol	Value	Unit
Power Dissipation (Note 5)	P_{D}	350	mW
Thermal Resistance, Junction to Ambient Air (Note 5)	$R_{ heta JA}$	357	°C/W
Operating and Storage Temperature Range	$T_{J_i} T_{STG}$	-65 to +150	°C

Note:

Electrical Characteristics (@TA = +25°C, unless otherwise specified.)


Type	Marking Codes	Zener Voltage Range (Note 6)			Maximum Zener Impedance (Note 7)		Temperature Coefficient	Total Capacitance	Rev Cur	mum erse rent te 6)		
Number		Vz @ IzT		I _{ZT}	Z _{ZT} @	Z _{ZK} @	I _{ZK}	TC @ I _{ZT}	$C_T @ f = 1MHz,$ $V_R = 0V$	I _R	@ V _R	
		Nom (V)	Min (V)	Max (V)	mA	٥	2	mA	Typical (mV/°C)	Max (pF)	μΑ	V
BZT585B2V4T	3C	2.4	2.35	2.45	5	100	400	1	-1.3	450	50	1
BZT585B2V7T	3E	2.7	2.65	2.75	5	100	450	1	-1.4	440	20	1
BZT585B3V3T	3H	3.3	3.23	3.37	5	95	500	1	-1.8	410	5	1
BZT585B3V6T	3J	3.6	3.53	3.67	5	90	500	1	-1.9	390	5	1
BZT585B3V9T	3K	3.9	3.82	3.98	5	90	500	1	-1.9	370	3	1
BZT585B4V3T	3L	4.3	4.21	4.39	5	90	600	1	-1.7	350	3	1
BZT585B4V7T	3M	4.7	4.61	4.79	5	80	500	1	-1.2	325	3	2
BZT585B5V1T	3N	5.1	5.00	5.20	5	60	480	1	-0.5	300	2	2
BZT585B5V6T	3P	5.6	5.49	5.71	5	40	400	1	1.0	275	1	2
BZT585B6V2T	3S	6.2	6.08	6.32	5	10	150	1	2.2	250	3	4
BZT585B6V8T	3T	6.8	6.66	6.94	5	15	80	1	3.0	215	2	4
BZT585B7V5T	3U	7.5	7.35	7.65	5	10	80	1	3.8	170	1	5
BZT585B8V2T	3V	8.2	8.04	8.36	5	10	80	1	4.7	150	0.7	5
BZT585B9V1T	3X	9.1	8.92	9.28	5	10	100	1	5.8	120	0.5	6
BZT585B10T	3Y	10	9.80	10.20	5	10	150	1	7.0	110	0.2	7
BZT585B11T	3Z	11	10.78	11.22	5	10	150	1	8.2	110	0.1	8
BZT585B12T	4A	12	11.76	12.24	5	10	150	1	9.5	105	0.1	8
BZT585B13T	4B	13	12.74	13.26	5	10	170	1	10.7	105	0.1	8
BZT585B15T	4D	15	14.70	15.30	5	15	200	1	13.2	100	0.05	10.5
BZT585B16T	4E	16	15.68	16.32	5	40	200	1	14.4	90	0.05	11.2
BZT585B18T	4F	18	17.64	18.36	5	45	225	1	16.9	80	0.05	12.6
BZT585B20T	4G	20	19.60	20.40	5	55	225	1	19.4	70	0.05	14.0
BZT585B22T	4H	22	21.56	22.44	5	55	250	1	21.9	60	0.05	15.4
BZT585B24T	4J	24	23.52	24.48	5	70	250	1	24.4	55	0.05	16.8
BZT585B27T	4K	27	26.46	27.54	2	80	300	0.5	25.4	50	0.05	18.9
BZT585B30T	4M	30	29.40	30.60	2	80	300	0.5	31.1	50	0.05	21.0
BZT585B33T	4N	33	32.34	33.66	2	80	325	0.5	36.7	45	0.05	23.1
BZT585B36T	4P	36	35.28	36.72	2	90	350	0.5	42.4	45	0.05	25.2
BZT585B39T	4R	39	38.22	39.78	2	130	350	0.5	48.1	45	0.05	27.3
BZT585B43T	4S	43	42.14	43.86	2	150	375	0.5	55.7	40	0.05	30.1


Notes: 6. Short duration pulse test used to minimize self-heating effect.


7. f = 1kHz.


^{5.} Device mounted on FR-4 PCB with minimum recommended pad layout, as shown in Diodes Incorporated's Suggested Pad Layout document, which can be found on our website at http://www.diodes.com.












Package Outline Dimensions

Please see AP02002 at http://www.diodes.com/datasheets/ap02002.pdf for latest version.

Figure 3 Typical Zener Breakdown Characteristics




SOD523						
Dim	Min	Max				
Α	0.25	0.35				
В	0.70	0.90				
С	1.50	1.70				
H	1.10	1.30				
K	0.55	0.65				
L 0.10 0.30						
М	0.10	0.12				
All Dimensions in mm						



Suggested Pad Layout

Please see AP02001 at http://www.diodes.com/datasheets/ap02001.pdf for latest version.



Dimensions	Value (in mm)
G	0.80
Х	0.60
X1	2.00
Υ	0.70

IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2014, Diodes Incorporated

www.diodes.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Diodes Incorporated:

BZT585B6V8T-7 BZT585B39T-7 BZT585B9V1T-7 BZT585B18T-7 BZT585B24T-7 BZT585B36T-7 BZT585B6V2T-7 BZT585B4V7T-7 BZT585B3V9T-7 BZT585B16T-7 BZT585B2V7T-7 BZT585B12T-7 BZT585B11T-7 BZT585B3V6T-7 BZT585B4V3T-7 BZT585B15T-7 BZT585B7V5T-7 BZT585B3V3T-7 BZT585B2V4T-7 BZT585B10T-7 BZT585B13T-7 BZT585B43T-7 BZT585B8V2T-7 BZT585B2V4T-7 BZT585B3V3T-7 BZT585B3V3T-7