



DUAL NPN PRE-BIASED TRANSISTORS IN SOT363

Features

- Epitaxial Planar Die Construction
- Complementary PNP Types Available (DDA)
- · Built-In Biasing Resistors
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen- and Antimony-Free. "Green" Device (Note 3)
- The DDC(XXXX)UQs are suitable for automotive applications requiring specific change control; these parts are AEC-Q101 qualified, PPAP capable, and manufactured in IATF 16949 certified facilities.

https://www.diodes.com/quality/product-definitions/

Part Number	R1 (NOM)	R2 (NOM)
DDC124EU	22kΩ	22kΩ
DDC144EU	47kΩ	47kΩ
DDC114YU	10kΩ	47kΩ
DDC123JU	2.2kΩ	47kΩ
DDC114EU	10kΩ	10kΩ
DDC143ZU	4.7kΩ	47kΩ
DDC115EU	100kΩ	100kΩ

SOT363





Top View

Mechanical Data

- Case: SOT363
- Case Material: Molded Plastic, "Green" Molding Compound.
 UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208 ³
- Weight: 0.006 grams (Approximate)

Part Number	R1 Only
DDC113TU	1kΩ
DDC143TU	4.7kΩ
DDC114TU	10kO





Device Schematic

Ordering Information (Notes 4 & 5)

Part Number	Status	Compliance	Marking	Reel Size (inches)	Tape Width (mm)	Quantity per Reel
DDC124EU-7-F	Active	Standard	N17	7	8	3,000
DDC124EUQ-7-F	NRND (Use ADC124EUQ)	Automotive	N17	7	8	3,000
DDC144EU-7-F	Active	Standard	N20	7	8	3,000
DDC114YU-7-F	Active	Standard	N14	7	8	3,000
DDC114YUQ-7-F	NRND (Use ADC114YUQ)	Automotive	N14	7	8	3,000
DDC114YUQ-13-F	NRND (Use ADC114YUQ)	Automotive	N14	13	8	10,000
DDC123JU-7-F	Active	Standard	N06	7	8	3,000
DDC114EU-7-F	Active	Standard	N13	7	8	3,000
DDC114EUQ-7-F	NRND (Use ADC114EUQ)	Automotive	N13	7	8	3,000
DDC114EUQ-13-F	NRND (Use ADC114EUQ)	Automotive	N13	13	8	10,000
DDC113TU-7-F	Active	Standard	N01	7	8	3,000
DDC143TU-7-F	Active	Standard	N07	7	8	3,000
DDC114TU-7-F	Active	Standard	N12	7	8	3,000
DDC114TUQ-7-F	Active	Automotive	N12	7	8	3,000
DDC143ZU-7-F	Active	Standard	N03	7	8	3,000
DDC115EU-7-F	Active	Standard	N02	7	8	3,000


Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.
- 5. NRND = Not Recommended for New Design.



Marking Information

SOT363



NXX = Product Type Marking Code (See Ordering Information)

YM = Date Code Marking

Y = Year (ex: H = 2020)

M = Month (ex: 9 = September)

Date Code Kev

Year	2002		2020	2021	2022	2023	2024	2025	2026	2027	2028	2029
Code	0		Н	- 1	J	K	L	М	N	0	Р	R
Month	Jan	Feb	Mar	Apr	May	Jun	Jul	Aug	Sep	Oct	Nov	Dec

Absolute Maximum Ratings (@ TA = +25°C, unless otherwise specified.)

Charac	teristic	Symbol	Value	Unit
Supply Voltage, <pin: (1)="" (6)="" a<="" td="" to=""><td>nd (3) to (4)></td><td>V_{CC}</td><td>50</td><td>V</td></pin:>	nd (3) to (4)>	V _{CC}	50	V
Input Voltage, <pin: (1)="" (2)="" (4)="" (5)="" and="" to=""></pin:>	DDC124EU DDC144EU DDC114YU DDC123JU DDC114EU DDC113TU DDC143TU DDC114TU DDC143ZU DDC114EU	Vin	-10 to +40 -10 to +40 -6 to +40 -5 to +12 -10 to +40 -5V max -5V max -5V max -5V max -10 to +40	V
Output Current	DDC124EU DDC144EU DDC114YU DDC123JU DDC114EU DDC113TU DDC143TU DDC114TU DDC143ZU DDC115EU	lo	30 30 70 100 50 100 100 100 100 20	mA
Output Current	•	I _{C(MAX)}	100	mA

Thermal Characteristics (@ T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Power Dissipation (Notes 6 & 7)	P _D	200	mW
Thermal Resistance, Junction to Ambient Air (Note 6)	R _{θJA}	625	°C/W
Operating and Storage Temperature Range	T _J , T _{STG}	-55 to +150	°C

Notes: 6. Mounted on FR-4 PC Board with minimum recommended pad layout.

7. 150mW per element must not be exceeded.



Electrical Characteristics (@ T_A = +25°C, unless otherwise specified.) For R1 Only Devices: DDC113TU & DDC143TU & DDC114TU

Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition
Collector-Base Breakdown Voltage	BV _{CBO}	50	_		V	$I_C = 50\mu A$
Collector-Emitter Breakdown Voltage	BV _{CEO}	50	_		V	I _C = 1mA
Emitter-Base Breakdown Voltage	BV _{EBO}	5			V	$I_{E} = 50\mu A$
Collector Cutoff Current	I _{CBO}		_	0.5	μΑ	V _{CB} = 50V
Emitter Cutoff Current	I _{EBO}			0.5	μΑ	V _{EB} = 4V
Collector-Emitter Saturation Voltage	V _{CE(sat)}			0.3	٧	I _C /I _B = 2.5mA / 0.25mA DDC143TU I _C /I _B = 1mA / 0.1mA DDC114TU I _C /I _B = 10mA / 1mA DDC113TU
DC Current Transfer Ratio	h _{FE}	100	250	600		$I_C = 1mA$, $V_{CE} = 5V$
Input Resistor (R ₁) Tolerance	ΔR_1	-30	_	+30	%	_
Gain-Bandwidth Product (Note 8)	f⊤		250	_	MHz	$V_{CE} = 10V$, $I_{E} = -5mA$, $f = 100MHz$


Electrical Characteristics (@ T_A = +25°C, unless otherwise specified.)
For R1, R2 Devices: DDC124EU& DDC144EU& DDC114YU& DDC123JU& DDC114EU& DDC143ZU& DDC115EU

Characteristi	ic	Symbol	Min	Тур	Max	Unit	Test Condition
	DDC124EU DDC144EU DDC114YU DDC123JU DDC114EU DDC143ZU DDC115EU	V _I (OFF)	0.5 0.5 0.3 0.5 0.5 0.5	1.1 1.1 — — 1.1 —	_		V _{CC} = 5V, I _O = 100μA
Input Voltage	DDC124EU DDC144EU DDC114YU DDC123JU DDC114EU DDC143ZU DDC115EU	V _{I(ON)}		1.9 1.9 — 1.9 —	3.0 3.0 1.4 1.1 3.0 1.3 3	V	$V_O = 0.3V$, $I_O = 5mA$ $V_O = 0.3V$, $I_O = 2mA$ $V_O = 0.3V$, $I_O = 1mA$ $V_O = 0.3V$, $I_O = 5mA$ $V_O = 0.3V$, $I_O = 10mA$ $V_O = 0.3V$, $I_O = 5mA$ $V_O = 0.3V$, $I_O = 1mA$
Output Voltage	DDC124EU DDC144EU DDC114YU DDC123JU DDC114EU DDC143ZU DDC115EU	V _{O(ON)}		0.1	0.3	V	I _O /I _L = 10mA / 0.5mA I _O /I _L = 10mA / 0.5mA I _O /I _L = 5mA / 0.25mA I _O /I _L = 5mA / 0.25mA I _O /I _L = 10mA / 0.5mA I _O /I _L = 5mA / 0.25mA I _O /I _L = 10mA / 0.5mA
Input Current	DDC124EU DDC144EU DDC114YU DDC123JU DDC114EU DDC143ZU DDC115EU	lį			0.36 0.18 0.88 3.6 0.88 1.8 0.15		V _I = 5V
Output Current		I _{O(OFF)}	_	_	0.5	μΑ	$V_{CC} = 50V, V_{I} = 0V$
DC Current Gain	DDC124EU DDC144EU DDC114YU DDC114YUQ DDC123JU DDC114EU DDC143ZU DDC115EU	Gı	56 68 68 80 80 30 80	_	_	_	V _O = 5V, I _O = 5mA V _O = 5V, I _O = 5mA V _O = 5V, I _O = 10mA V _O = 5V, I _O = 5mA V _O = 5V, I _O = 10mA V _O = 5V, I _O = 5mA V _O = 5V, I _O = 10mA V _O = 5V, I _O = 5mA
Input Resistor (R ₁) Tolerance		ΔR_1	-30	_	+30	%	_
Resistance Ratio Tolerance		$\Delta(R_2/R_1)$	-20		+20	%	_
Gain-Bandwidth Product (Note 8)		f _T	_	250	_	MHz	V _{CE} = 10V, I _E = 5mA, f = 100MHz

Note: 8. Transistor - for reference only.




Typical Curves - DDC123JU (@ T_A = +25°C, unless otherwise specified.)







Typical Curves - DDC114YU (@ T_A = +25°C, unless otherwise specified.)







Typical Curves – DDC124EU (@ T_A = +25°C, unless otherwise specified.)













Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT363






SOT363							
Dim	Min Max Typ						
A1	0.00	0.10	0.05				
A2	0.90	1.00	0.95				
b	0.10	0.30	0.25				
С	0.10	0.22	0.11				
D	1.80	2.20	2.15				
Е	2.00	2.20	2.10				
E1	1.15	1.35	1.30				
е	C	0.650 BSC					
F	0.40	0.45	0.425				
L	0.25	0.40	0.30				
а	0°	8°	-				
All	Dimen	sions	in mm				

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT363



Dimensions	Value
Dillielisions	(in mm)
С	0.650
G	1.300
X	0.420
Y	0.600
Y1	2.500



IMPORTANT NOTICE

- 1. DIODES INCORPORATED AND ITS SUBSIDIARIES ("DIODES") MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- 2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes products. Diodes products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of the Diodes products for their intended applications, (c) ensuring their applications, which incorporate Diodes products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- 3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
- 4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- 5. Diodes products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- 6. Diodes products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- 7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- 8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

Copyright © 2020 Diodes Incorporated

www.diodes.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Diodes Incorporated:

DDC124EU-7-F DDC114YU-7-F DDC144EU-7-F DDC114TU-7-F DDC123JU-7-F DDC143TU-7-F DDC114EU-7-F DDC113TU-7-F DDC115EU-7-F DDC143ZU-7-F DDC114EUQ-13-F DDC114EUQ-7-F DDC114YUQ-7-F DDC114YUQ-7-F