

FEATURES

- Average Forward Current:I_{F(AV)}=2A
- Polarity: Color band denotes cathode



Package Marking and Ordering Information

Product ID	Pack	Marking	Qty(PCS)			
K22-K210	SOD-123F	K2 ★	3000			





★:From 2-10

MAXIMUM RATINGS (Ta=25 unless otherwise noted)

Rating 25°C ambient temperature unless otherwies specified. Single phase half wave, 60Hz, resistive or inductive load. For capacitive load, derate current by 20%.

·										
TYPE NUMBER		K22	K23	K24	K25	K26	K28	K29	K210	UNITS
Maximum Recurrent Peak Reverse Voltage		20	30	40	50	60	80	90	100	V
Maximum RMS Voltage		14	21	28	35	42	56	63	70	V
Maximum DC Blocking Voltage		20	30	40	50	60	80	90	100	V
Maximum Average Forward Rectified Current										
See Fig. 1			2.0							
Peak Forward Surge Current, 8.3 ms single half sine-wave										
superimposed on rated load (JEDEC method)			50							
Maximum Instantaneous Forward Voltage at 2.0A			0.55		0.70		0.85			V
Maximum DC Reverse Current	Ta=25°C		0.1 0.02					mA		
at Rated DC Blocking Voltage	Ta=100°C		5					2		mA
Typical Junction Capacitance (Note1)			170							
Typical Thermal Resistance R JA (Note 2)			80							
Operating Temperature Range T _J			-65 —+150							°C
Storage Temperature Range Tsтg			-65—+150							

NOTES:

- 1. Measured at 1MHz and applied reverse voltage of 4.0V D.C.
- 2. Thermal Resistance Junction to Ambient.



Typical Characteristics

FIG.1-TYPICAL FORWARD CURRENT DERATING CURVE





FIG.3-MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT






FIG.2-TYPICAL FORWARD






FIG.5 - TYPICAL REVERSE



SOD-123F Package Outline Dimensions





Attention

- Any and all HUA XUAN YANG ELECTRONICS products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your HUA XUAN YANG ELECTRONICS representative nearest you before using any HUA XUAN YANG ELECTRONICS products described or contained herein in such applications.
- HUA XUAN YANG ELECTRONICS assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein.
- Specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- HUA XUAN YANG ELECTRONICS CO.,LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- In the event that any or all HUA XUAN YANG ELECTRONICS products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of HUA XUAN YANG ELECTRONICS CO.,LTD.
- Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production.

 HUA XUAN YANG ELECTRONICS believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the HUA XUAN YANG ELECTRONICS product that you intend to use.