



- 技术参数 SPECIFICATIONS:
- ◆ 材质(Material): 磷铜phosphor bronze
 - ◆ 材料厚度(Thickness): 0.12mm
 - ◆ 适用线规(Wire Range): AWG 28#~32#
 - ◆ 产品工艺(Plating Process): 先冲后镀
- Electroplating after completion of production
- ◆ 表面处理(Surface): 镀锡Tin Plated
 - ◆ 包装数量(Qty/reel): 220000pcs



SECT: A-A

SECT: B-B

SECT: C-C

APPROVALS		DATE	DRAWING NO.	
DRAWN	G.M.Chen	2015/5/22	X1001-T-PN	
CHECKED			TITLE: 1.25mm Crimp Style Connectors	
APPROVALS			PART NO.	SHEET 1 OF 1
TOLERANCES ARE		ANGLE	SCALE: 1:1	PROJ.
30 ^{±0.15}	±0.30	±2°		
10 ^{±0.30}	±0.20			
5 ^{±0.10}	±0.15			
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.
	A		NEW	

DEALON 德之隆
ELECTRONICS CO.,LTD