


## Features

- Protects One Data or Power Line
- Low Clamping Voltage
- Ultra Low Leakage: nA Level
- Moisture Sensitivity Level 1
- Halogen Free. "Green" Device (Note 1)
- Epoxy Meets UL 94 V-0 Flammability Rating
- Lead Free Finish/RoHS Compliant ("P" Suffix Designates RoHS Compliant. See Ordering Information)

## **Maximum Ratings**


- Operating Junction Temperature Range: -55°C to +125°C
- Storage Temperature Range: -55°C to +150°C




IEC61000-4-2(ESD)	Air Contact	±30KV ±30KV
IEC61000-4-4 (EFT) @5/50ns		40A
IEC61000-4-5(Surge) @8/20us	I <sub>PP</sub>	10A
Peak pulse power(tp=8/20us)	P <sub>PP</sub>	300W

Note: 1. Halogen free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.


### **Circuit and Pin Schematic**








	DIMENSIONS				
DIM INCHES		MM		NOTE	
Divi	MIN	MAX	MIN	MAX	NOTE
Α	0.018	0.022	0.45	0.55	
В	0.000	0.002	0.00	0.05	
С	0.005	0.007	0.12	0.18	
D	0.037	0.041	0.95	1.05	
E	0.022	0.026	0.55	0.65	
F	0.0	026	0.6	650	TYP.
G	0.018	0.022	0.45	0.55	
Н	0.003	0.007	0.07	0.17	
L	0.008	0.012	0.20	0.30	





## ELECTRICAL CHARACTERISTICS (T<sub>A</sub> = 25°C unless otherwise noted)

Symbol	Parameter	
V <sub>RWM</sub>	Peak Reverse Working Voltage	
I <sub>R</sub>	Reverse Leakage Current @ $V_{RWM}$	
V <sub>BR</sub>	Breakdown Voltage @ $I_T$	
Ι <sub>Τ</sub>	Test Current	
I <sub>PP</sub>	Maximum Reverse Peak Pulse Current	
V <sub>C</sub>	Clamping Voltage @ IPP	
P <sub>PP</sub>	Peak Pulse Power	
CJ	Junction Capacitance	
١ <sub>F</sub>	Forward Current	
VF	Forward Voltage @ I <sub>F</sub>	





## Electrical Characteristics per line @ 25°C (Unless Otherwise Specified)

Parameter	Symbol	Conditions	Min.	Тур.	Max.	Units
Reverse Stand-Off Voltage	V <sub>RWM</sub>				15	V
Reverse Breakdown Voltage	V <sub>BR</sub>	I <sub>T</sub> =1mA	16.7		20	V
Reverse Leakage Current	I <sub>R</sub>	V <sub>RWM</sub> =15V			0.5	μA
Forward Voltage	V <sub>F</sub>	I <sub>F</sub> =10mA		0.8	1.2	V
Clamping Voltage	V <sub>c</sub>	I <sub>PP</sub> =1A, t <sub>P</sub> =8/20μs			22	V
Clamping Voltage	V <sub>c</sub>	I <sub>PP</sub> =10A, t <sub>P</sub> =8/20μs			30	V
Junction Capacitance	CJ	V <sub>R</sub> = 0V, f = 1MHz		65		pF



# **Curve Characteristics**










Fig. 2 - Pulse Derating Curve 120 100 Percent of Rated Power (%) 80 60 40 20 0 L 0 25 50 75 100 125 150 Ambient Temperature (°C)







## **Ordering Information**

Device	Packing
Part Number-TP	Tape&Reel: 10Kpcs/Reel

#### \*\*\*IMPORTANT NOTICE\*\*\*

*Micro Commercial Components Corp.* reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. *Micro Commercial Components Corp*. does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold *Micro Commercial Components Corp*. and all the companies whose products are represented on our website, harmless against all damages. *Micro Commercial Components Corp*. products are sold subject to the general terms and conditions of commercial sale, as published at

https://www.mccsemi.com/Home/TermsAndConditions.

### \*\*\*LIFE SUPPORT\*\*\*

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

#### \*\*\*CUSTOMER AWARENESS\*\*\*

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources**. MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.