





RECOMMENDED PCB LAYOUT  
GENERAL TOLERANCE±0.05



Specifications :


- Voltage rating: 50 V AC / DC
- Current rating: 2A AC / DC
- Withstanding voltage: 500V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: 100MΩ Min
- Contact resistance: 20mΩ Max
- After environmental testing : 20mΩ Max

X1203 WRS-XX- 6TV01  
① ②③④ ⑤ ⑥ ⑦

- ① Series No.
- ② Category : W-WAFER
- ③ Welding Board Angle : R-Stright 90°
- ④ Welding way: S-SMT
- ⑤ Row No.-Pin No.: XX-02P~03P
- ⑥ Material : N0-PA6T 94V-0
- ⑦ Plating Category: V01-All Gold Flash

X1203WRS-XX-6TV0	N0-PA6T 94V-0	Phosphor Bronze	Gold Flash	X1203H
PART NO	Material	Material(pin)	Finish(pin)	Suitable XKB Housing

Poles	Dimensions(mm)				
	A	B	C	D	E
02	1.20	2.70	4.20	3.20	1.50
03	2.40	3.90	5.40	4.40	1.50



剖面 A-A

广东星坤科技股份有限公司

日期

文件工程章

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

DSND	SCALE: N/A	MODEL TYPE: X1203WRS-XX-6TV01
DWN	VIEW:	PART NO.:
CHKD	UNIT: mm/in	DWG NO.:
APPD	SIZE: A4	X-X1203WRS-XX-6TV01
XKB INDUSTRIAL PRECISION CO., LIMITED		WEIGHT
		SHEET
		REVISION
		1/1
		A0