




### Specifications:

- Voltage rating: 250V AC/DC
- Current rating: 2.5-1.0A AC/DC
- Withstanding voltage: 800V AC/minute
- Temperature range: -25 °C ~ +85 °C
- Insulation resistance: ≥1000MΩ
- Contact resistance: ≤10mΩ
- After environmental testing: ≤20mΩ


X2006 W R - 2\*XX -4T SN  
① ② ③ ④ ⑤ ⑥

- ① XKB Series No.
- ② Category: W-WAFER
- ③ Welding Board Angle: R-90°
- ④ Row No. - pin No.: 2\*XX-04P~20P
- ⑤ Material: 4T-PA4T 94V-0
- ⑥ Plating Category : SN-Bright Tin Plating




6P~14P Without Guideway  
16P~40P With Guideway  
Scale: 1/0.5

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2*04	6.00	10.00	2*13	24.00	28.00
2*05	8.00	12.00	2*14	26.00	30.00
2*06	10.00	14.00	2*15	28.00	34.00
2*07	12.00	16.00	2*16	30.00	36.00
2*08	14.00	18.00	2*17	32.00	38.00
2*09	16.00	20.00	2*18	34.00	40.00
2*10	18.00	22.00	2*19	36.00	42.00
2*11	20.00	24.00	2*20	38.00	44.00
2*12	22.00	26.00			



Recommended P.C.B. Layout  
General Tolerance ±0.05



X2006WR-2*XX-4TSN	PA4T UL 94V-0	X2006T	X2006H
PART NO	Material	Suitable XKB Terminal	Suitable XKB Terminal

广东星坤科技股份有限公司

DATE DESCRIPTION DATE REVISED APPROVED

文件工程章

			XKB	ANGLAR	±5°
				L ≤ 4	±0.2
				4 < L ≤ 16	±0.3
				16 < L ≤ 63	±0.4
				L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES
www.helloxkb.com					

DSND		DATE		SCALE: N/A	MODEL TYPE: X2006WR-2*XX-4TSN
DWN		DATE		VIEW:	PART NO.:
CHKD		DATE		UNIT: mm/in	DWG NO.:
APPD		DATE		SIZE: A4	
KKB INDUSTRIAL PRECISION CO., LIMITED				WEIGHT	SHEET
					1/1
				REVISION	A0