NOT RECOMMENDED FOR NEW DESIGN USE RS1A - RS1M Series



PR1001G - PR1007G


1.0A FAST RECOVERY GLASS PASSIVATED RECTIFIER

Features

- Glass Passivated Die Construction
- Fast Switching for High Efficiency
- Surge Overload Rating to 30A Peak
- Low Reverse Leakage Current
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)

Mechanical Data

- Case: DO-41 Plastic
- Case Material: Molded Plastic. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish—Tin. Plated Leads Solderable per MIL-STD-202, Method 208 (3)
- Polarity: Cathode Band
- Weight: 0.35 grams (Approximate)



Top View



Schematic View

Ordering Information (Note 3)

Part Number	Case	Packaging			
PR1001G-T	DO-41	5K/Tape & Reel, 13-inch			
PR1002G-T	DO-41	5K/Tape & Reel, 13-inch			
PR1003G-T	DO-41	5K/Tape & Reel, 13-inch			
PR1004G-T	DO-41	5K/Tape & Reel, 13-inch			
PR1005G-T	DO-41	5K/Tape & Reel, 13-inch			
PR1006G-T	DO-41	5K/Tape & Reel, 13-inch			
PR1007G-T	DO-41	5K/Tape & Reel, 13-inch			

Notes:

- $1. \; EU \; Directive \; 2002/95/EC \; (RoHS), \; 2011/65/EU \; (RoHS \; 2) \; \& \; 2015/863/EU \; (RoHS \; 3). \\ compliant. \; All \; applicable \; RoHS \; exemptions \; applied. \\$
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. For packaging details, go to our website at http://www.diodes.com/products/packages.html.

Marking Information



PR100XG = Product Type Marking Code X = 1, 2, 3, 4, 5, 6, 7

Dill = Manufacturers' Code Marking
YWW = Date Code Marking
Y = Last Digit of Year (ex: 4 for 2014)
WW = Week Code (01 to 53)



Maximum Ratings and Electrical Characteristics @TA = +25°C, unless otherwise specified.

Single phase, half wave, 60Hz, resistive or inductive load.

Characteristic	Symbol	PR1001 G	PR1002 G	PR1003 G	PR1004 G	PR1005 G	PR1006 G	PR1007 G	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage (Note 7)	V _{RRM} V _{RWM} V _R	50	100	200	400	600	800	1000	V
RMS Reverse Voltage	V _{R(RMS)}	35	70	140	280	420	560	700	V
Average Rectified Output Current (Note 4) @ T _A = +55°C	Io				1.0				Α
Non-Repetitive Peak Forward Surge Current 8.3ms Single Half Sine-Wave Superimposed on Rated Load	I _{FSM}	30					Α		
Forward Voltage Drop @ I _F = 1.0A	V _{FM}	1.3					V		
Peak Reverse Current @ T _A = +25°C at Rated DC Blocking Voltage (Note 7) @ T _A = +100°C	I _{RM}	5.0 50					μΑ		
Reverse Recovery Time (Note 6)	t _{RR}		15	50		250	50	00	ns
Typical Total Capacitance (Note 5)	Ст		1	5			8		pF

Thermal Characteristics

Characteristic	7	Symbol	Value	Unit
Typical Thermal Resistance Junction to Ambient (Note 4)		R _{eJA}	95	°C/W
Operating and Storage Temperature Range		T _J , T _{STG}	-65 to +150	°C

Notes:

- 4. Valid provided that leads are maintained at ambient temperature at a distance of 9.5mm from the case.

 5. Measured at 1.0MHz and applied reverse voltage of 4.0V DC.

 6. Measured with I_F = 0.5A, I_R = 1.0A, I_{RR} = 0.25A. See Figure 5.

 7. Short duration pulse test used to minimize self-heating effect.





Fig. 5 Reverse Recovery Time Characteristic and Test Circuit



Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

DO-41 (Plastic)



DO-41 (Plastic)					
Dim	Min	Max			
Α	25.40	_			
В	4.06	5.21			
С	0.71	0.864			
D	2.00	2.72			
All Dimensions in mm					



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2018, Diodes Incorporated

www.diodes.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Diodes Incorporated:

PR1001G-T PR1002G-T PR1003G-T PR1004G-T PR1005G-T PR1006G-T PR1007G-T