

Low Consumption Current High PSRR 300mA CMOS Voltage Regulator

LR6230 Series

■ INTRODUCTION

The LR6230 series are a group of positive voltage regulators manufactured by CMOS technologies with high ripple rejection, low power consumption and low dropout voltage, which can prolong battery life in portable electronics. The LR6230 series work with low-ESR ceramic capacitors, reducing the amount of board space necessary for power applications. The LR6230 series consume less than 0.1uA in shutdown mode and have fast turn-on time less than 50us. The series are very suitable for the battery-powered equipments, such as RF applications and other systems requiring a quiet voltage source.

equiling a quiet voltage

Cellular and Smart Phones

APPLICATIONS

- Laptop, Palmtops and PDA
- Digital Still and Video Cameras

■ FEATURES

Low Dropout Voltage: 150mV@150mA

Low Quiescent Current: 5μA

High Ripple Rejection: 65dB@1kHz

 Excellent Line and Load Transient Response

Operating Voltage: 2.0V∼7.0V

Output Voltage: 1.2 ~ 5.0V


High Accuracy: $\pm 2/\pm 1$ (Typ.)

Built-in Current Limiter, Short-Circuit
Protection

TTL- Logic-Controlled Shutdown Input

- MP3, MP4 Player
- Radio control systems
- Battery-Powered Equipment

■ BLOCK DIAGRAM



ORDER INFORMATION


LR6230(1)(2)(3)(4)(5)

DESIGNATOR	SYMBOL	DESCRIPTION			
<u> </u>	Α	Standard			
U)	В	With Shutdown Function			
23	Integer	Output Voltage e.g.1.8V=②:1, ③:8			
	M	Package:SOT-23-3/5			
	U	Package:SC-70-5			
(4)	P/PT	Package:SOT-89-3/5			
	F	Package:DFN1×1-4			
(5)	-	2% Accuracy			
9	1	1% Accuracy			



■ PIN CONFIGURATION

SOT-23-3 SOT-23-5 DFN1×1-4 SOT-89-3 SOT-89-5



			PIN NUN	/IBER			
	SOT	-23-3		SOT	-89-3	PIN NAME	FUNCTION
M	MA	МС	MY	Р	PT		
1	2	3	3	1	2	V _{SS}	Ground
2	1	2	1	3	1	V _{OUT}	Output
3	3	1	2	2	3	V _{IN}	Power input

SOT-23-5/SC-70-5

PIN NUMBER	SYMBOL FUNCTION	
1	V _{IN} Power Input Pin	
2	V _{SS}	Ground
3	CE	Chip Enable Pin
4	NC	No Connection
5	V _{OUT}	Output Pin

DFN1×1-4

PIN NUMBER	CVMDOL	FUNCTION
F	SYMBOL	FUNCTION
1	V _{OUT}	Output Pin
2	V _{SS}	Ground
3	CE	Chip Enable Pin
4	V _{IN}	Power Input Pin

SOT-89-5

PIN NUM	PIN NUMBER SYMBOL		FUNCTION	
Р	PT	STINIBUL	FUNCTION	
1	5	V _{OUT}	Output Pin	
2	2	V _{SS}	Ground	
3	1	NC	No Connection	
4	3	CE	Chip Enable Pin	
5	4	V _{IN}	Power Input Pin	



■ ABSOLUTE MAXIMUM RATINGS

(Unless otherwise specified, Ta=25°C)

PARAMETER	PARAMETER		RATINGS	UNITS
Input Voltage		V_{IN}	V _{SS} -0.3~V _{SS} +8	V
Output Curren	ıt	I _{OUT}	600	mA
Output Voltage	е	V_{OUT}	V _{SS} -0.3~V _{IN} +0.3	V
	SOT-23	Pd	250	mW
	SC-70	Pd	250	mW
Power Dissipation	DFN1X1-4	Pd	400	mW
	SOT-89	Pd	500	mW
	TO-92	Pd	500	mW
Operating Temperature		T_{opr}	-40~+85	$^{\circ}\!\mathbb{C}$
Storage Temperature		T_{stg}	-40~+125	$^{\circ}\!\mathbb{C}$
Soldering Temperature	e & Time	T_{solder}	260℃, 10s	

■ ELECTRICAL CHARACTERISTICS

LR6230 Series $(V_{IN}=V_{OUT}+1V, C_{IN}=C_{OUT}=1\mu F, Ta=25\%, unless otherwise specified)$

PARAMETER	SYMBOL	CONDITIONS	MIN.	TYP.	MAX.	UNITS
Output Voltage	V _{OUT} (E) (Note 2)	I _{OUT} =1mA	V _{OUT} *0.98	V _{OUT}	V _{OUT} *1.02	V
Supply Current	I _{SS}	I _{OUT} =0		5	10	μΑ
Standby Current	I _{STBY}	CE = V _{SS}			0.1	μΑ
Output Current	I _{OUT}	_	300			mA
Dropout Voltage (Note 3)	V _{dif}	I _{OUT} =150mA V _{OUT} ≥3.0V		150		mV
Load Regulation	<u>∆</u> V _{OUT}	V _{IN} = V _{OUT} +1V, 1mA≤I _{OUT} ≤100mA		10		mV
Line Regulation	$\frac{\Delta V_{OUT}}{V_{OUT} \times \Delta V_{IN}}$	I _{OUT} =10mA V _{OUT} +1V≤V _{IN} ≤6V		0.01	0.2	%/V
Output Voltage Temperature Characteristics	$\frac{\Delta V_{OUT}}{\Delta T \times V_{OUT}}$	I _{OUT} =10mA -40≤T≤+85		100		ppm
Short Current	I _{Short}	V _{OUT} =V _{SS}		50		mA
Input Voltage	V _{IN}	_	2.0		7.0	V
Power Supply 1kHz	PSRR	I _{OUT} =50mA		65		dB
Rejection Rate 10kHz		001		50		
CE "High" Voltage	V _{CE} "H"		1.5		V _{IN}	V
CE "Low" Voltage	V _{CE} "L"				0.3	V


NOTE:


- 1. V_{OUT}: Specified Output Voltage.
- 2. V_{OUT} (E) : Effective Output Voltage (le. The Output Voltage When V_{IN} = (V_{OUT} +1.0V) And Maintain A Certain I_{OUT} Value).



3. V_{dif}: The Difference Of Output Voltage And Input Voltage When Input Voltage Is Decreased Gradually Till Output Voltage Equals To 98% Of V_{OUT} (E).


■ TYPICAL APPLICATION








■ TYPICAL PERFORMANCE CHARACTERISTICS

 $(V_{CE}=V_{IN}=V_{OUT}+1V, C_{IN}=C_{OUT}=1\mu F, T_A=25^{\circ}C, unless otherwise specified)$















TYPICAL PERFORMANCE CHARACTERISTICS

(V_{CE}=V_{IN}=V_{OUT}+1V, C_{IN}=C_{OUT}=1 μ F, T_A=25 $^{\circ}$ C,unless otherwise specified)












■ PACKAGING INFORMATION


• SOT-23-3 PACKAGE OUTLINE DIMENSIONS



S. mh a l	Dimensions Ir	Dimensions In Millimeters		In Inches
Symbol	Min	Max	Min	Max
Α	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.500	0.012	0.020
С	0.100	0.200	0.004	0.008
D	2.820	3.020	0.111	0.119
E	1.500	1.700	0.059	0.067
E1	2.650	2.950	0.104	0.116
е	0.950(BSC)		0.037(BSC)
e1	1.800	2.000	0.071	0.079
L	0.300	0.600	0.012	0.024
θ	0°	8°	0°	8°




• SOT-23-5 PACKAGE OUTLINE DIMENSIONS



C. mb a l	Dimensions In	Millimeters	Dimensions	In Inches
Symbol	Min	Max	Min	Max
Α	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.500	0.012	0.020
С	0.100	0.200	0.004	0.008
D	2.820	3.020	0.111	0.119
E	1.500	1.700	0.059	0.067
E1	2.650	2.950	0.104	0.116
е	0.950(BSC)	0.037(BSC)
e1	1.800	2.000	0.071	0.079
L	0.300	0.600	0.012	0.024
θ	0°	8°	0°	8°




• SC-70-5 PACKAGE OUTLINE DIMENSIONS



Cuma la a l	Dimensions In Millimeters		Dimensions In Inches	
Symbol	Min	Max	Min	Max
А	0.800	1.100	0.031	0.044
A1	0.000	0.100	0.000	0.004
В	1.150	1.350	0.045	0.054
b	0.150	0.400	0.006	0.016
С	1.800	2.450	0.071	0.096
D	1.800	2.250	0.071	0.089
е	0.650		0.0)26
Н	0.080	0.260	0.003	0.010
L	0.210	0.460	0.008	0.018




SOT-89-3 PACKAGE OUTLINE DIMENSIONS




Symbol	Dimensions	In Millimeters	Dimensions In Inches		
Syllibol	Min	Max	Min	Max	
Α	1.400	1.600	0.055	0.063	
b	0.320	0.520	0.013	0.197	
b1	0.400	0.580	0.016	0.023	
С	0.350	0.440	0.014	0.017	
D	4.400	4.600	0.173	0.181	
D1	1.550) REF	0.061	REF	
E	2.300	2.600	0.091	0.102	
E1	3.940	4.250	0.155	0.167	
е	1.500 TYP		0.060TYP		
e1	3.000	3.000 TYP 0.118TYP		BTYP	
L	0.900	1.200	0.035	0.047	



• TO-92 PACKAGE OUTLINE DIMENSIONS






Cymh ol	Dimensions	In Millimeters	Dimension	s In Inches
Symbol	Min	Max	Min	Max
А	3.300	3.700	0.130	0.146
A1	1.100	1.400	0.043	0.055
b	0.380	0.550	0.015	0.022
С	0.360	0.510	0.014	0.020
D	4.400	4.700	0.173	0.185
D1	3.430		0.135	
Е	4.300	4.700	0.169	0.185
е	1.270) TYP	0.050) TYP
e1	2.440	2.640	0.096	0.104
L	14.100	14.500	0.555	0.571
Ф		1.600		0.063
h	0.000	0.380	0.000	0.015



• DFN1×1-4 PACKAGE OUTLINE DIMENSIONS




COMMON DIMENSIONS (UNITS OF MEASURE=MILLIMETER)

$\overline{}$					
SYMBOL	MIN	NOM	MAX		
Α	0.34	0.37	0.40		
A1	0.00	0.02	0.05		
A3	0.100REF				
b	0.17	0.22	0.27		
D	0.95	1.00	1.05		
E	0.95	1.00	1.05		
D2	0.43	0.48	0.53		
E2	0.43	0.48	0.53		
L	0.20	0.25	0.30		
е	_	0.65	_		
K	0.15	_	_		



• SOT-89-5 PACKAGE OUTLINE DIMENSIONS



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
Α	1.400	1.600	0.055	0.063
b	0.320	0.520	0.013	0.020
b1	0.360	0.560	0.014	0.022
С	0.350	0.440	0.014	0.017
D	4.400	4.600	0.173	0.181
D1	1.400	1.800	0.055	0.071
E	2.300	2.600	0.091	0.102
E1	3.940	4.250	0.155	0.167
е	1.500TYP		0.060TYP	
e1	2.900	3.100	0.114	0.122
L	0.900	1.100	0.035	0.043

单击下面可查看定价,库存,交付和生命周期等信息

>>LRC(乐山无线电)