



ADTC144WCAQ

NPN PRE-BIASED SMALL SIGNAL SURFACE MOUNT TRANSISTOR

Features

- Epitaxial Planar Die Construction
- Complementary PNP Types Available (ADTA)
- Built-In Biasing Resistors, $R1 \neq R2$
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- Qualified to AEC-Q101 Standards for High Reliability
- PPAP Capable (Note 4)


R1 (NOM)	R2 (NOM)
47kΩ	22kΩ

Mechanical Data


- Case: SOT23
- Case Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208 ⁽³⁾
- Weight: 0.008 grams (Approximate)



Top View



Device Schematic



Equivalent Inverter Circuit

Ordering Information (Note 5)

Part Number	Compliance	Marking	Reel Size (inches)	Tape Width (mm)	Quantity Per Reel
ADTC144WCAQ-7	Automotive	2C2	7	8	3,000
ADTC144WCAQ-13	Automotive	2C2	13	8	10,000

No purposely added lead. Fully EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant.
See http://www.diodes.com/quality/lead_free.html for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green"

2. See http://www and Lead-free.


Notes:

3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

4. Automotive products are AEC-Q101 qualified and are PPAP capable. Refer to https://www.diodes.com/quality/product-compliance-definitions/.

5. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information



2C2 = Product Type Marking Code YM = Date Code Marking Y = Year (ex: E = 2017) M = Month (ex: 9 = September)

Date Code Key

Year	2017	2018	2019	2020	202 ⁻	1 20	22	2023	2024	2025	2026	2027
Code	E	F	G	Н			J	K	L	М	Ν	0
Month	Jan	Feb	Mar	Apr	Мау	Jun	Ju	l Aug	g Sep	Oct	Nov	Dec
Code	1	2	3	4	5	6	7	8	9	0	N	D



Absolute Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Supply Voltage <pin: (2)="" (3)="" to=""></pin:>	Vcc	50	V
Input Voltage <pin: (1)="" (2)="" to=""></pin:>	V _{IN}	-10 to +40	V
Output Current	lo	30	mA
Output Current	I _C (Max)	100	mA


Thermal Characteristics (@T_A = +25°C, unless otherwise specified.)


Characteristic	Symbol	Value	Unit
Power Dissipation (Note 6)	PD	310	mW
Thermal Resistance, Junction to Ambient Air (Note 6)	R _{0JA}	403	°C/W
Operating and Storage Temperature Range	T _J , T _{STG}	-55 to +150	°C

Note: 6. Mounted on FR-4 PC Board with minimum recommended pad layout.



Thermal Characteristics and Derating Information







Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)


Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition
Input Voltage	V _{I(OFF)} (Note 7)	0.8	_	—	V	$V_{CC} = 5V, I_{O} = 100 \mu A$
input voltage	VI(ON) (Note 8)	—	—	4	v	$V_0 = 0.3V, I_0 = 2mA$
Output Voltage	V _{O(ON)}	—	0.1	0.3	V	$I_0/I_1 = 10 \text{mA}/0.5 \text{mA}$
Input Current	lı	_	_	0.16	mA	$V_1 = 5V$
Output Current	I _{O(OFF)}	—	—	0.5	μA	$V_{CC} = 50V, V_I = 0V$
DC Current Gain	GI	56	_		_	$V_0 = 5V, I_0 = 5mA$
Input Resistor Tolerance	ΔR_1	-30	—	+30	%	—
Resistance Ratio Tolerance	$\Delta R_2/R_1$	-20		+20	%	—
Gain-Bandwidth Product (Note 9)	f _T		250		MHz	$V_{CE} = 10V, I_E = 5mA,$ f = 100MHz

Notes:

Guarantees that the device will be switched OFF if the Input Voltage is less than 0.8V.
Guarantees that the device will be switched ON if the Input Voltage is more than 4V.
Transistor - For Reference Only.



Typical Characteristics (@T_A = +25°C, unless otherwise specified.)






Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT23




	SOT23							
Dim	Min	Max	Тур					
Α	0.37	0.51	0.40					
В	1.20	1.40	1.30					
С	2.30	2.50	2.40					
D	0.89	1.03	0.915					
F	0.45	0.60	0.535					
G	1.78	2.05	1.83					
Н	2.80	3.00	2.90					
J	0.013	0.10	0.05					
ĸ	0.890	1.00	0.975					
K1	0.903	1.10	1.025					
L	0.45	0.61	0.55					
L1	0.25	0.55	0.40					
М	0.085	0.150	0.110					
а	0°	8°						
All	Dimens	ions in	mm					

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT23



Dimensions	Value (in mm)
С	2.0
Х	0.8
X1	1.35
Y	0.9
Y1	2.9



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2017, Diodes Incorporated

www.diodes.com