



DMP3056L

30V P-CHANNEL ENHANCEMENT MODE MOSFET

Product Summary

BVDSS	Rds(on) max	ID MAX TA = +25°C
-30V	50mΩ @ V _{GS} =-10V	-4.3A
-30 V	70mΩ @ V _{GS} =-4.5V	-3.7A

Description and Applications

This new generation MOSFET has been designed to minimize the on-state resistance $(R_{DS(ON)})$ yet maintain superior switching performance, making it ideal for high-efficiency power management applications.

Features

- Low On-Resistance
- Low Gate Threshold Voltage
- Low Input Capacitance
- Fast Switching Speed
- Low Input/Output Leakage
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please contact us or your local Diodes representative.

https://www.diodes.com/quality/product-definitions/


Mechanical Data

- Case: SOT23
- Case Material: Molded Plastic. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Annealed over Copper Lead-Frame. Solderable per MIL-STD-202, Method 208 (3)
- Weight: 0.009 grams (Approximate)






Top View



Top View Pin Configuration



Equivalent Circuit


Ordering Information (Note 4)

Part Number	Case	Packaging
DMP3056L-7	SOT23 (Standard)	3000/Tape & Reel
DMP3056L-13	SOT23 (Standard)	10000/Tape & Reel

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/

Marking Information



 $\begin{array}{l} \text{6L = Product Type Marking Code} \\ \text{YM = Date Code Marking} \\ \text{Y or } \overline{\text{Y}} = \text{Year (ex: I = 2021)} \\ \text{M or } \overline{\text{M}} = \text{Month (ex: 9 = September)} \\ \end{array}$

Date Code Key

Year	2014		2021	2022	2023	2024	2025	2026	2027	2028	2029	2030
Code	В		I	J	K	L	М	N	0	Р	R	S
Month	Jan	Feb	Mar	Apr	May	Jun	Jul	Aug	Sep	Oct	Nov	Dec

June 2021

© Diodes Incorporated



Maximum Ratings (@ $T_A = +25^{\circ}C$, unless otherwise specified.)

Characteristi	С		Symbol	Value	Unit
Drain-Source Voltage			VDSS	-30	V
Gate-Source Voltage		Vgss	±25	V	
Drain Current (Note 5) V _{GS} = -10V	Steady State	lo	-4.3 -3.4	А	
Pulsed Drain Current (Note 6)			I _{DM}	-20	А

Thermal Characteristics

Characteristic	Symbol	Value	Unit
Total Power Dissipation (Note 5)	P _D	1.38	W
Thermal Resistance, Junction to Ambient (Note 5)	$R_{\theta JA}$	91	°C/W
Operating and Storage Temperature Range	T _J , T _{STG}	-55 to +150	°C

Electrical Characteristics (@ TA = +25°C, unless otherwise specified.)


Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition
OFF CHARACTERISTICS (Note 7)			- 714			
Drain-Source Breakdown Voltage	BV _{DSS}	-30	_	_	V	$V_{GS} = 0V, I_{D} = -250\mu A$
Zero Gate Voltage Drain Current	IDSS	_	_	-1	μΑ	V _{DS} = -30V, V _{GS} = 0V
Gate-Source Leakage	Igss	_	_	±100 ±800	nA	$V_{GS} = \pm 20V, V_{DS} = 0V$ $V_{GS} = \pm 25V, V_{DS} = 0V$
ON CHARACTERISTICS (Note 7)	•		•	•	•	
Gate Threshold Voltage	V _{GS(TH)}	-1	_	-2.1	V	$V_{DS} = V_{GS}$, $I_D = -250\mu A$
Static Drain-Source On-Resistance	RDS(ON)	_	35 50	50 70	mΩ	$V_{GS} = -10V, I_D = -6.0A$ $V_{GS} = -4.5V, I_D = -5.0A$
Diode Forward Voltage	VsD	_	_	-1.2	V	VGS = 0V, IS = -1.7A
DYNAMIC CHARACTERISTICS (Note 8)						
Input Capacitance	Ciss		642	_	pF	
Output Capacitance	Coss		65	_	pF	$V_{DS} = -25V$, $V_{GS} = 0V$, $f = 1.0MHz$
Reverse Transfer Capacitance	C _{rss}		48	_	pF	
Gate Resistance	Rg	_	15	_	Ω	$V_{DS} = 0V$, $V_{GS} = 0V$, $f = 1.0MHz$
Total Gate Charge (V _{GS} = -4.5V)	QG	_	5.8	_	nC	V _{DS} = -15V, I _D = -6A
Total Gate Charge (V _{GS} = -10V)	Q _G	_	11.8	_		
Gate-Source Charge	Qgs	_	2.0	_	nC	V _{DS} = -15V, I _D = -6A
Gate-Drain Charge	Q _{GD}	_	2.4	_		
Turn-On Delay Time	t _D (ON)	_	4.9	_		
Rise Time	t _R	_	4.7	_]	V _{DS} = -15V, V _{GS} = -10V,
Turn-Off Delay Time	tD(OFF)	_	35.2	_	ns	$I_D = -1A$, $R_G = 6.0\Omega$
Fall Time	tF	_	18.2	_]	


Notes: 5. Device mounted on FR-4 substrate PC board, 2oz copper, with thermal vias to bottom layer 1inch square copper plate.

^{6.} Pulse width ≤10µS, Duty Cycle ≤1%.
7. Short duration pulse test used to minimize self-heating effect.

^{8.} Guaranteed by design. Not subject to production testing.










Figure 5. Typical On-Resistance vs. Drain Current and Temperature




Figure 2. Typical Transfer Characteristic




Figure 4. Typical Transfer Characteristic




Figure 6. On-Resistance Variation with Temperature






Figure 7. On-Resistance Variation with Temperature





Figure 9. Diode Forward Voltage vs. Current







Figure 8. Gate Threshold Variation vs. Junction Temperature



100 $R_{\text{DS}(\text{ON})}$ Limited =100µs ID, DRAIN CURRENT (A) 10 $T_{J,(MAX)}$ =150°C 0.1 P_w=100ms T_A=25°C Single Pulse DUT on 1*MRP board P_W=10ms V_{GS}= -10V 0.01 0.1 10 100 V_{DS}, DRAIN-SOURCE VOLTAGE (V) Figure 12. SOA, Safe Operation Area







Figure 13. Transient Thermal Resistance



Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT23 (Standard)




SOT23 (Standard)							
Dim	Min	Max	Тур				
Α	0.90	1.15	1.025				
A1	0.00	0.10	0.05				
A2	0.85	1.10	0.975				
b	0.30	0.51	0.40				
С	0.080	0.202	0.11				
D	2.80	3.00	2.90				
Е	2.25	2.55	2.40				
E1	1.20	1.40	1.30				
е	0.89	1.03	0.915				
e1	1.78	2.05	1.83				
F	0.40	0.60	0.535				
L1	0.45	0.61	0.55				
L	0.25	0.55	0.40				
а	0°	8°					
All Dimensions in mm							

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT23 (Standard)



Dimensions	Value (in mm)			
С	2.0			
Х	0.8			
X1	1.35			
Y	0.9			
V1	2.0			



IMPORTANT NOTICE

- 1. DIODES INCORPORATED AND ITS SUBSIDIARIES ("DIODES") MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- 2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes products. Diodes products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of the Diodes products for their intended applications, (c) ensuring their applications, which incorporate Diodes products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- 3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
- 4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- 5. Diodes products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- 6. Diodes products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- 7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- 8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

Copyright © 2021 Diodes Incorporated

www.diodes.com