



DMTH10H010SPSQ

100V 175°C N-CHANNEL ENHANCEMENT MODE MOSFET PowerDI5060-8

Product Summary

BV _{DSS}	DSS R _{DS(ON)} Max I _D (Note 1	
100\/	8.8mΩ @ V _{GS} = 10V	100A
100V	11.5mΩ @ V _{GS} = 6V	100A

Description

This MOSFET is designed to meet the stringent requirements of Automotive applications. It is qualified to AEC-Q101, supported by a PPAP.

Applications

- Motor Control
- DC-DC Converters
- Power Management


Features

- Rated to +175°C Ideal for High Ambient Temperature Environments
- 100% Unclamped Inductive Switching Ensures More Reliable and Robust End Application
- Low R_{DS(ON)} Minimizes On-State Losses
- Fast Switching Speed
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- Qualified to AEC-Q101 Standards for High Reliability
- PPAP Capable (Note 4)

Mechanical Data

- Case: PowerDI[®]5060-8
- Case Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminal Connections: See Diagram Below
- Terminal Finish Matte Tin Annealed over Copper Leadframe. Solderable per MIL-STD-202, Method 208 (3)
- Weight: 0.097 grams (Approximate)





Ordering Information (Note 4)

Part Number	Case	Packaging
DMTH10H010SPSQ-13	PowerDI5060-8	2,500 / Tape & Reel

1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied. 2. See http://www.diodes.com/quality/lead_free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green"

and Lead-free.

3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

4. Automotive products are AEC-Q101 qualified and are PPAP capable. Refer to https://www.diodes.com/quality/.

5. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information

Notes:



J : = Manufacturer's Marking
TH10H010S = Product Type Marking Code
YYWW = Date Code Marking
YY = Last Two Digits of Year (ex: 18 = 2018)
WW = Week Code (01 to 53)

PowerDI is a registered trademark of Diodes Incorporated. DMTH10H010SPSQ Document number: DS40018 Rev. 3 - 2



Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit	
Drain-Source Voltage	V _{DSS}	100	V	
Gate-Source Voltage		V _{GSS}	±20	V
Continuous Drain Current, V _{GS} = 10V (Note 6)	T _A = +25°C T _A = +100°C	ID	11.8 8.3	А
Continuous Drain Current, V _{GS} = 10V (Note 7)	T _C = +25°C (Note 10) T _C = +100°C	۱ _D	100 87	A
Pulsed Drain Current (10µs Pulse, Duty Cycle = 1%)	I _{DM}	250	А	
Maximum Continuous Body Diode Forward Current	Is	100	A	
Avalanche Current, L = 0.3mH	I _{AS}	25	A	
Avalanche Energy, L = 0.3mH	Eas	93.7	mJ	
Avalanche Current (Note 8), L = 3mH	I _{AS}	14.3	А	
Avalanche Energy (Note 8), L = 3mH	E _{AS}	307	mJ	

Thermal Characteristics

Characteristic		Symbol	Value	Unit
Total Power Dissipation (Note 6)	T _A = +25°C	PD	1.5	W
Thermal Resistance, Junction to Ambient (Note 6)		R _{0JA}	99	°C/W
Total Power Dissipation (Note 7)	T _C = +25°C	PD	166	W
Thermal Resistance, Junction to Case (Note 7)	R _{θJC}	0.9	°C/W	
Operating and Storage Temperature Range	T _{J,} T _{STG}	-55 to +175	°C	

Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition	
OFF CHARACTERISTICS (Note 8)							
Drain-Source Breakdown Voltage	BV _{DSS}	100	—	—	V	$V_{GS} = 0V$, $I_D = 1mA$	
Zero Gate Voltage Drain Current	I _{DSS}	_	—	1	μA	$V_{DS} = 80V, V_{GS} = 0V$	
Gate-Source Leakage	IGSS		—	±100	nA	$V_{GS} = \pm 20V, V_{DS} = 0V$	
ON CHARACTERISTICS (Note 8)							
Gate Threshold Voltage	V _{GS(TH)}	2	—	4	V	$V_{DS} = V_{GS}$, $I_D = 250 \mu A$	
Static Drain-Source On-Resistance			6.6	8.8	mΩ	V _{GS} = 10V, I _D = 13A	
	R _{DS(ON)}		8.5	11.5	11122	$V_{GS} = 6V, I_D = 13A$	
Diode Forward Voltage	V _{SD}		0.8	1.3	V	$V_{GS} = 0V, I_{S} = 13A$	
DYNAMIC CHARACTERISTICS (Note 9)							
Input Capacitance	Ciss		4468	—		$V_{DS} = 50V, V_{GS} = 0V$ f = 1MHz	
Output Capacitance	Coss	-	746	—	pF		
Reverse Transfer Capacitance	C _{rss}		32	—			
Gate Resistance	Rg	-	0.91	—	Ω	$V_{DS} = 0V, V_{GS} = 0V, f = 1MHz$	
Total Gate Charge	Qg	_	56.4	_		V/ 50V/1 40A	
Gate-Source Charge	Q _{gs}	_	15.4	—	nC	$V_{DD} = 50V, I_D = 13A,$ $V_{GS} = 10V$	
Gate-Drain Charge	Q _{gd}	_	14	—			
Turn-On Delay Time	t _{D(ON)}	_	18.6	_		V _{DD} = 50V, V _{GS} = 10V,	
Turn-On Rise Time	t _R	_	22.5	_			
Turn-Off Delay Time	t _{D(OFF)}	_	44.8	_	ns	$I_D = 13A, R_g = 6\Omega$	
Turn-Off Fall Time	tF	-	29.5	_			
Reverse Recovery Time	t _{RR}	_	54.5	_	ns	1 12 A di/dt 100 A /up	
Reverse Recovery Charge	Q _{RR}	_	106.4	_	nC	I _F = 13A, di/dt = 100A/μs	


Notes: 6. Device mounted on FR-4 PC board, with minimum recommended pad layout, single sided.

Thermal resistance from junction to soldering point (on the exposed drain pad).
Short duration pulse test used to minimize self-heating effect.

Guaranteed by design. Not subject to product testing
Package limited.




DMTH10H010SPSQ






DMTH10H010SPSQ



DMTH10H010SPSQ Document number: DS40018 Rev. 3 - 2










Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

PowerDI5060-8




	PowerDI5060-8					
Dim	Min	Max	Тур			
Α	0.90	1.10	1.00			
A1	0.00	0.05	-			
b	0.33	0.51	0.41			
b2	0.200	0.350	0.273			
b3	0.40	0.80	0.60			
С	0.230	0.330	0.277			
D		5.15 BSC	;			
D1	4.70	5.10	4.90			
D2	3.70	4.10	3.90			
D3	3.90 4.30 4.10					
E	6.15 BSC					
E1	5.60	6.00	5.80			
E2	3.28	3.68	3.48			
E3	3.99	4.39	4.19			
е	1.27 BSC					
G	0.51	0.71	0.61			
K	0.51	-	-			
L	0.51	0.71	0.61			
L1	0.100	0.200	0.175			
М	3.235	4.035	3.635			
M1	1.00	1.40	1.21			
Θ	10°	12°	11°			
Θ1	6°	8°	7°			
Al	All Dimensions in mm					

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

PowerDI5060-8



Dimensions	Value (in mm)
С	1.270
G	0.660
G1	0.820
Х	0.610
X1	4.100
X2	0.755
X3	4.420
X4	5.610
Y	1.270
Y1	0.600
Y2	1.020
Y3	0.295
Y4	1.825
Y5	3.810
Y6	0.180
Y7	6.610



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2018, Diodes Incorporated

www.diodes.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Diodes Incorporated: DMTH10H010SPSQ-13