


#### **Features**


- Single-Supply Operation from +1.8V ~ +5.5V
- Rail-to-Rail Input / Output
- Gain-Bandwidth Product: 1.8MHz (Typ@25°C)
- Low Input Bias Current: 20pA (Typ@25°C)
- Low Offset Voltage: 5µV (Max @25°C)
- Quiescent Current: 220µA per Amplifier (Typ)
- Operating Temperature: -45°C ~ +125°C
- Zero Drift: 0.005µV/°C (Typ)
  Embedded RF Anti-EMI Filter


### **Applications**

- Transducer Application
- Temperature Measurements
- Electronics Scales
- · Handheld Test Equipment
- Battery-Powered Instrumentation

### **Pin Configuration**










Figure 1. Pin Assignment Diagram



## **Absolute Maximum Ratings**

Condition	Min	Max		
Power Supply Voltage (V <sub>DD</sub> to Vss)	-0.5V	+7.5V		
Analog Input Voltage (IN+ or IN-)	Vss-0.5V	V <sub>DD</sub> +0.5V		
PDB Input Voltage	Vss-0.5V	+7V		
Operating Temperature Range	-45°C	+125°C		
Junction Temperature	+16	0°C		
Storage Temperature Range	-55°C	+150°C		
Lead Temperature (soldering, 10sec)	+26	+260°C		
Package Thermal Resistance (T <sub>A</sub> =+25℃)				
SOP-8, θ <sub>JA</sub>	125°	125°C/W		
MSOP-8, θ <sub>JA</sub>	216°	216°C/W		
SOT23-5, θ <sub>JA</sub>	190°	190°C/W		
ESD Susceptibility				
НВМ	64	6KV		
MM	40	400V		

**Note:** Stress greater than those listed under Absolute Maximum Ratings may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions outside those indicated in the operational sections of this specification are not implied. Exposure to absolute maximum rating conditions for extended periods may affect reliability.

# **Package/Ordering Information**

MODEL	CHANNEL	ORDER NUMBER	PACKAGE DESCRIPTION	PACKAGE OPTION	MARKING INFORMATION
	Cinalo	OPA335AIDB	SOT23-5	Tape and Reel,3000	335
OPA335 Single	OPA335AID	SOP-8	Tape and Reel,4000	OPA335	
OPA2335	Dual	OPA2335	SOP-8	Tape and Reel,4000	OPA2335
UFA2333	Dual	OPA2335AIDG	MSOP-8	Tape and Reel,3000	OPA2335
0540004	Quad	OPA2334AIDB	TSSOP-14	Tape and Reel,3000	OPA2334
OPA2334	Quau	OPA2334AID	SOP-14	Tape and Reel,2500	OPA2334




### **Electrical Characteristics**

(Vs = +5V, VcM = +2.5V, Vo = +2.5V, TA = +25  $^{\circ}\mathrm{C}$  , unless otherwise noted.)

PARAMETER	CONDITIONS	MIN	TYP	MAX	UNITS
INPUT CHARACTERISTICS		•			
Input Offset Voltage (V <sub>OS</sub> )			1	5	μV
Input Bias Current (I <sub>B</sub> )			20		pA
Input Offset Current (I <sub>OS</sub> )			10		pA
Common-Mode Rejection Ratio (CMRR)	V <sub>CM</sub> = 0V to 5V		110		dB
Large Signal Voltage Gain ( A <sub>VO</sub> )	$R_L = 10k\Omega$ , $V_O = 0.3V$ to 4.7V		145		dB
Input Offset Voltage Drift ( $\Delta V_{OS}/\Delta_T$ )			5	50	nV/℃
OUTPUT CHARACTERISTICS		•			
Outrot Vallage High (V )	$R_L = 100k\Omega$ to - $V_S$		4.998		V
Output Voltage High (V <sub>OH</sub> )	$R_L = 10k\Omega$ to - $V_S$		4.994		V
Output Valtaga Laur (V )	$R_L = 100k\Omega$ to + $V_S$		2		mV
Output Voltage Low (V <sub>OL</sub> )	$R_L = 10k\Omega$ to + $V_S$		5		mV
Short Circuit Limit (I <sub>SC</sub> )	$R_L$ =10 $\Omega$ to - $V_S$		60		mA
Output Current (I <sub>O</sub> )			65		mA
POWER SUPPLY					
Power Supply Rejection Ratio (PSRR)	V <sub>S</sub> = 2.5V to 5.5V		115		dB
Quiescent Current (IQ)	$V_O = 0V$ , $R_L = 0\Omega$		220		μA
DYNAMIC PERFORMANCE					
Gain-Bandwidth Product (GBP)	G = +100		1.8		MHz
Slew Rate (SR)	$R_L = 10k\Omega$		0.95		V/µs
Overload Recovery Time			0.10		ms
NOISE PERFORMANCE		•	•		-
Voltage Noise (e <sub>n</sub> p-p)	0Hz to 10Hz		0.3		µV <sub>P-P</sub>
Voltage Noise Density (en)	f = 1kHz		38		$nV/\sqrt{Hz}$




### **Typical Performance characteristics**





### **Typical Performance characteristics**

Time (10s/div)



Time (10s/div)






Figure 2. Indirectly Driving a Capacitive Load Using Isolation Resistor

The bigger the  $R_{ISO}$  resistor value, the more stable  $V_{OUT}$  will be. However, if there is a resistive load  $R_L$  in parallel with the capacitive load, a voltage divider (proportional to  $R_{ISO}/R_L$ ) is formed, this will result in a gain error.

The circuit in Figure 3 is an improvement to the one in Figure 2.  $R_F$  provides the DC accuracy by feed-forward the  $V_{IN}$  to  $R_L$ .  $C_F$  and  $R_{ISO}$  serve to counteract the loss of phase margin by feeding the high frequency component of the output signal back to the amplifier's inverting input, thereby preserving the phase margin in the overall feedback loop. Capacitive drive can be increased by increasing the value of  $C_F$ . This in turn will slow down the pulse response.




Figure 3. Indirectly Driving a Capacitive Load with DC Accuracy



### **Typical Application Circuits**

#### **Differential amplifier**

The differential amplifier allows the subtraction of two input voltages or cancellation of a signal common the two inputs. It is useful as a computational amplifier in making a differential to single-end conversion or in rejecting a common mode signal. Figure 4. shown the differential amplifier using OPA335/2335/2334.




Figure 4. Differential Amplifier

$$V_{\text{OUT}} = (\frac{R_1 + R_2}{R_3 + R_4}) \frac{R_4}{R_1} V_{\text{IN}} - \frac{R_2}{R_1} V_{\text{IP}} + (\frac{R_1 + R_2}{R_3 + R_4}) \frac{R_3}{R_1} V_{\text{REF}}$$

If the resistor ratios are equal (i.e. R<sub>1</sub>=R<sub>3</sub> and R<sub>2</sub>=R<sub>4</sub>), then

$$V_{\text{OUT}} = \frac{R_2}{R_1} (V_{\text{IP}} - V_{\text{IN}}) + V_{\text{REF}}$$

#### **Low Pass Active Filter**

The low pass active filter is shown in Figure 5. The DC gain is defined by  $-R_2/R_1$ . The filter has a -20dB/decade roll-off after its corner frequency  $f_c=1/(2\pi R_3C_1)$ .




Figure 5. Low Pass Active Filter



#### **Instrumentation Amplifier**

The triple OPA335/2335/2334 can be used to build a three-op-amp instrumentation amplifier as shown in Figure 6. The amplifier in Figure 6 is a high input impedance differential amplifier with gain of R2/R1. The two differential voltage followers assure the high input impedance of the amplifier.





Figure 6. Instrument Amplifier


www.tokmas.com




# **Package Information**

### SOP-8









Symbol		nsions meters	Dimensions In Inches		
•	MIN	MAX	MIN	MAX	
Α	1.350	1.750	0.053	0.069	
A1	0.100	0.250	0.004	0.010	
A2	1.350	1.550	0.053	0.061	
b	0.330	0.510	0.013	0.020	
С	0.170	0.250	0.008	0.010	
D	4.700	5.100	0.185	0.200	
E	3.800	4.000	0.150	0.157	
E1	5.800	6.200	0.228	0.244	
e	1.27	1.27 BSC		BSC	
L	0.400	1.270	0.016	0.050	
е	0°	8°	0°	8°	



### MSOP-8








Symbol		nsions imeters	Dimensions In Inches		
•	MIN	MAX	MIN	MAX	
Α	0.820	1.100	0.032	0.043	
A1	0.020	0.150	0.001	0.006	
A2	0.750	0.950	0.030	0.037	
b	0.250	0.380	0.010	0.015	
С	0.090	0.230	0.004	0.009	
D	2.900	3.100	0.114	0.122	
E	2.900	3.100	0.114	0.122	
E1	4.750	5.050	0.187	0.199	
e	0.650 BSC		0.026	BSC	
L	0.400	0.800	0.016	0.031	
θ	0°	6°	0°	6°	




### SOT23-5




Symbol	Dimensions In Millimeters		Dimensions In Inches		
,	MIN	MAX	MIN	MAX	
Α	1.050	1.250	0.041	0.049	
A1	0.000	0.100	0.000	0.004	
A2	1.050	1.150	0.041	0.045	
b	0.300	0.500	0.012	0.020	
С	0.100	0.200	0.004	0.008	
D	2.820	3.020	0.111	0.119	
E	1.500	1.700	0.059	0.067	
E1	2.650	2.950	0.104	0.116	
e	0.950 BSC		0.037 BSC		
e1	1.900 BSC		0.075	BSC	
L	0.300	0.600	0.012	0.024	
θ	0°	8°	0°	8°	





#### **SOP-14**





RECOMMENDED LAND PATTERN (Unit: mm)






Symbol	Dimensions In Millimeters			Dimensions In Inches		
	MIN	MOD	MAX	MIN	MOD	MAX
Α	1.35		1.75	0.053		0.069
A1	0.10		0.25	0.004		0.010
A2	1.25		1.65	0.049		0.065
A3	0.55		0.75	0.022		0.030
b	0.36		0.49	0.014		0.019
D	8.53		8.73	0.336		0.344
E	5.80		6.20	0.228		0.244
E1	3.80		4.00	0.150		0.157
е		1.27 BSC		0.050 BSC		
L	0.45		0.80	0.018		0.032
L1	1.04 REF				0.040 REF	
L2		0.25 BSC		0.01 BSC		
R	0.07			0.003		
R1	0.07			0.003		
h	0.30		0.50	0.012		0.020
θ	0°		8°	0°		8°



### TSSOP-14



Secondary 1	Dimensions In	Millimeters	Dimensions In Inches		
Symbo1	Min	Max	Min	Max	
D	4.900	5. 100	0. 193	0.201	
E	4.300	4. 500	0.169	0.177	
ь	0.190	0.300	0.007	0.012	
с	0.090	0.200	0.004	0.008	
E1	6. 250	6. 550	0. 246	0.258	
A		1. 200		0.047	
A2	0.800	1.000	0.031	0.039	
A1	0.050	0. 150	0.002	0.006	
е	0.65	0.65 (BSC)		(BSC)	
L	0.500	0.700	0.020	0.028	
Н	0.25(TYP)		0.01(	TYP)	
θ	1 °	7°	1°	7°	