



USB 3.2 Gen 2x2 ReDriver

Features

- 5Gbps & 10Gbps Serial Link with Linear Equalizer
- USB 3.2 Gen 2 and Gen 1 Compatible
- USB 3.2 Gen 2x2 Compatible
- Four 10Gbps Differential Signal Pairs
- Pin Adjustable Receiver Equalization
- Pin Adjustable Flat Gain
- 100Ω Differential CML I/Os
- Automatic Receiver Detect
- Auto Slumber Mode for Adaptive Power Management
- Single Supply Voltage: 3.3V
- Patented Technology
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please contact us or your local Diodes representative.

https://www.diodes.com/quality/product-definitions/

- Packaging (Pb-free & Green available):
 - ^o 34-pin, UQFN 2.5mm × 4.5mm (ZTF34)


Description

The PI3EQX2024 is a low-power, high-performance, USB 3.2 Gen 2x2 linear ReDriver[™] designed specifically for the USB 3.2 protocol.

The device provides programmable equalization and flat gain to optimize performance over a variety of physical mediums by reducing intersymbol interference. PI3EQX2024 supports two 100Ω differential CML data I/Os between the Protocol ASIC to a switch fabric, over cable, or to extend the signals across other distant data pathways on the user's platform.

The integrated equalization circuitry provides flexibility with signal integrity of the signal before the ReDriver. Each channel operates fully independently. The channels' input signal level determines whether the output is active.

The PI3EQX2024 also includes an automatic receiver detect function. The receiver detection loop is active again if the corresponding channel's signal detector is idle for longer than 7.3ms. The channel then moves to unplug mode if load is not detected, or it returns to low-power mode (slumber mode) due to inactivity.



Notes:

ReDriver is a trademark of Diodes Incorporated. PI3EQX2024 Document Number DS43042 Rev 2-2


^{1.} No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.

^{2.} See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free. 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.






Block Diagram







Pin Configuration



Pin Description

Pin #	Pin Name	Туре	Description
13, 17, 30, 34	VDD	Power	3.3V power supply, ±0.3V
32, 23	FGA, FGB	Turnet	The DC flat gain selection. 4-level input pins. With internal 100k Ω pullup resistor
6, 15	FGC, FGD	Input	and $200 k\Omega$ pulldown resistor.
31, 24	EQA, EQB	Input	The EQ selection. 4-level input pins. With internal $100k\Omega$ pullup resistor and
7, 14	EQC, EQD	Input	200kΩ pulldown resistor.
1, 2	RXAP, RXAN		
25, 26 RXBP, RXBN 8, 9 RXCP, RXCN		Innut	CML input terminals. With selectable input termination between 50 Ω to VDD,
		Input	270k Ω to VbiasRx, or 67k Ω to GND.
18, 19	RXDP, RXDN		
29, 28	TXAP, TXAN		
5, 4	TXBP, TXBN	Output	CML output terminals. With selectable output termination between 50 Ω to
22, 21	TXCP, TXCN	Output	VDD, $6k\Omega$ to VDD, $6k\Omega$ to VbiasTx or $67k\Omega$ to GND.
12, 11	TXDP, TXDN		
			Channel Enable. With internal 300 k Ω pullup resistor.
33	EN	Input	"High" – Channel is in normal operation.
			"Low" – Channel is in power down mode.
16	CAP_EXT	I/O	Decoupling Capacitor for Internal Bias.
3, 10, 20, 27, Center Pad	GND	GND	Supply Ground





Power Management

Notebooks, netbooks, and other power sensitive consumer devices require judicious use of power in order to maximize battery life. In order to minimize the power consumption of our devices, Diodes added an additional adaptive power management feature. When a signal detector is idle for longer than 1.3ms, the corresponding channel moves to low-power mode ONLY, which means both channels move to low-power mode individually.

In low-power mode, the signal detector continues monitoring the input channel. If a channel is in low-power mode and the input signal is detected, the corresponding channel wakes up immediately. If a channel is in low-power mode and the signal detector is idle longer than 6ms, the receiver detection loop is active again. If load is not detected, then the channel moves to device unplug mode and monitors the load continuously. If load is detected, it returns to low-power mode, and receiver detection is active again per 6ms.

Operating Modes

Mode	R _{IN}	R _{OUT}
PD	$67 \mathrm{k}\Omega$ to GND	$67 \mathrm{k}\Omega$ to GND
Unplug Mode	270k Ω to VbiasRx	6kΩ to VbiasTx
Deep Slumber Mode	50Ω to Vdd	6kΩ to VbiasTx
Slumber Mode	50Ω to Vdd	$6k\Omega$ to Vdd
Active Mode	50Ω to Vdd	50Ω to Vdd





Equalization Setting:

EQA/B/C/D are the selection pins for the equalization selection.

	Equalizer Settings (dB)				
EQA/B/C/D	@ 2.5GHz	(a) 5GHz			
0 (Tie 1K Ω to GND)	6.7	12.4			
R (Tie 68KΩ to GND)	3.5	8.0			
F (Leave Open)	5.3	10.6			
1 (Tie 1K Ω to VDD)	8.4	14.6			

Flat Gain Setting:

FGA/B/C/D are the selection pins for the DC gain.

	Flat Gain Settings
FGA/B/C/D	dB
0 (Tie 1K Ω to GND)	-1.6
R (Tie $68K\Omega$ to GND)	-0.5
F (Leave Open)	1.0
1 (Tie 1K Ω to VDD)	2.7

Channel Enable Setting:

	Channel Enable Settings
EN	Setting
0	Disabled
1	Enabled (Default)





Maximum Ratings

(Above which useful life may be impaired. Fo	or user guidelines, not tested.)
Storage Temperature	65°C to +150°C
Supply Voltage to Ground Potential	0.5V to +3.8V
DC SIG Voltage	$-0.5V$ to $V_{DD} + 0.5V$
Output Current	–25mA to +25mA
ESD, Human Body Model	2kV to +2kV
Power Dissipation Continuous	
Max Junction Temperature	

Note:

Stresses greater than those listed under MAXIMUM RATINGS may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect reliability.

Control Pin Specifications (VDD = 3.3 ± 0.3 V, TA = -40 to 85°C)

Symbol	Parameter	Min.	Min. Typ.		Units
2-Level Cont	rol Pins				
V _{IH}	DC Input Logic High	VDD × 0.65	_	—	V
V _{IL}	DC Input Logic Low	_	—	$VDD \times 0.35$	V
I _{IH}	Input High Current	_	—	25	μA
I _{IL}	Input Low Current	-25	—	—	μA
4-Level Cont	rol Pins				
V _{IH}	DC Input Logic "High"	$0.92 \times \text{VDD}$	VDD	—	V
V _{IF}	DC Input Logic "Float"	$0.59 \times VDD$	0.67 × VDD	$0.75 \times \text{VDD}$	V
V _{IR}	DC Input Logic "With Rext to GND"	$0.25 \times \text{VDD}$	$0.33 \times VDD$	$0.41 \times \text{VDD}$	V
V _{IL}	DC Input Logic "Low"	_	GND	$0.08 \times \text{VDD}$	V
I _{IH}	Input High Current	_	_	50	μΑ
I _{IL}	Input Low Current	-50	_	—	μΑ
Rext	External Resistor Connects to GND (±5%)	64.6	68	71.4	kΩ

AC/DC Electrical Characteristics (VDD = 3.3 ± 0.3 V TA = -40 to 85° C)

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Units
Power and Late	ncy			^ 		
V _{dd-3.3}	Supply Voltage		3.0	3.3	3.6	V
I _{active}	Active Mode Current Consumption	EN = 1, 10Gbps, compliance test pat- tern	_	260	334	mA
I _{slumber}	Slumber Mode Current Consumption	$EN = 1$, no input signal longer than $T_{slumber}$	_	32	38	
I _{Deep} Slumber	Deep Slumber Mode Current Consumption	EN = 1 no input signal longer than T _{DeepSlumber}	_	0.8	1.2	mA
Iunplug	Unplug Mode Current Consumption	EN = 1, no output load is detected	_	0.6	0.9	
I _{pd}	Power Down Mode Current Consumption	EN = 0	_	20	120	μΑ
t _{pd}	Latency	From input to output	_		2	ns





AC/DC Electrical Characteristics Cont.

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Units
CML Receiver In	put (100 Ω Differential)			1		
Receiver Electrica	l Specification					
C _{rxparasitic}	The Parasitic Capacitor for RX	_		_	1.0	pF
R _{RX-DIFF-DC}	DC Differential Input Impedance	_	72		120	
R _{RX-SINGLE_DC}	DC Single Ended Input Impedance	DC impedance limits are need to guar- antee RxDet. Measured with respect to GND over a voltage of 500mV max.	18	_	30	Ω
Z _{RX-HIZ-DC-PD}	DC Input CM Input Impedance for V>0 During Reset or Power Down	(Vcm=0 to 500mV)	25	_	_	kΩ
Cac_coupling	AC Coupling Capacitance	—	75	—	265	nF
V _{RX-CM-AC-P}	Common Mode Peak Voltage	AC up to 5GHz	—	—	150	mVpeak
VRX-CM-DC-Active- Idle-Delta-P	Common Mode Peak Voltage Avg _{uo} (V _{TX-D+} + V _{TX-D-})/2-Avg _{u1} (V _{TX-D+} + V _{TX-D-})/2	Between U0 and U1. AC up to 5GHz		_	200	mVpeak
Transmitter Elec	trical Specification					1
V _{TX-DIFF-PP}	Output Differential p-p Voltage Swing	Differential Swing V _{TX-D+} -V _{TX-D-}	_	_	1.2	Vppd
R _{TX-DIFF-DC}	DC Differential TX Impedance		72	_	120	Ω
VTX-RCV-DET	The Amount of Voltage Change Allowed During RxDet		_	_	600	mV
Cac_coupling	AC Coupling Capacitance	—	75	—	265	nF
T _{TX-EYE} (10Gbps)	Transmitter Eye, Include all Jitter	At the silicon pad. 10Gbps	0.646	—	—	UI
T _{TX-EYE} (5Gbps)	Transmitter Eye, Include all Jitter	At the silicon pad. 5Gbps	0.625	—	—	UI
T _{TX-DJ-DD} (10Gbps)	Transmitter Deterministic Jitter	At the silicon pad. 10Gbps	—	—	0.17	UI
T _{TX-DJ-DD} (5Gbps)	Transmitter Deterministic Jitter	At the silicon pad. 5Gbps			0.205	UI
C _{txparasitic}	The Parasitic Capacitor for TX	_			1.1	pF
R _{TX-DC-CM}	Common mode DC Output Impedance	_	18	_	30	Ω
¥7	The Instantaneous Allowed DC Common Mode Voltage at Connector	Min1 is with 200k Ω single ended receiver load respectively.	-0.5		1	V
V _{TX-DC-CM}	Side of the AC Coupling Capacitors	Min2 is with 50Ω single ended receiver load respectively.	-0.3	_	1	v
V _{TX-C}	Common-Mode Voltage	$ V_{TX-D+}+V_{TX-D-} /2$	VDD-2		VDD	V
VTX-CM-AC-PP- Active	Active Mode TX AC Common Mode Voltage	$V_{TX-D+}+V_{TX-D-}$ for both time and amplitude	_	—	100	mVpp
V _{TX-CM-DC-} Active_Idle-Delta	Common Mode Delta Voltage Avg _{uo} (V _{TEX-D+} + V _{TX-D-}])/2-Avg _{u1} (V _{TX-D+} + V _{TX-D-}])/2	Between U0 to U1			200	mV-peak





AC/DC Electrical Characteristics Cont.

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Units
V _{TX} -Idle-Diff-AC-pp	Idle Mode AC Common Mode Delta Voltage V _{TX-D+} -V _{TX-D-}	Between Tx+ and Tx- in idle mode. Use the HPF to remove DC components. =1/LPF. No AC and DC signals are applied to Rx terminals .	_	_	10	mVppd
V _{TX-Idle} -Diff-DC	Idle Mode DC Common Mode Delta Voltage V _{TX-D+} -V _{TX-D-}	Between Tx+ and Tx- in idle mode. Use the LPF to remove DC components. =1/HPF. No AC and DC signals are applied to Rx terminals.	_		10	mV
Channel Perform	nance					
Gp	Peaking Gain (Compensation at 5GHz, Relative to 100MHz, 100mV _{p-p} Sine	EQx=0 EQx=R EQx=F	_	12.4 8.0 10.6	_	dB
	Wave Input)	EQx=1		14.6		
		Variation around typical	-3	—	+3	dB
G _F	Flat Gain (100MHz, EQx=F)	FQx=0 FQx=R FQx=F FQx=1	_	-1.6 -0.5 1.0 2.7	_	dB
		Variation around typical	-3	_	+3	dB
VSW_100M	-1dB Compression Point Output Swing (at 100MHz)	_	_	1000	_	mVppd
V _{SW_5G}	-1dB Compression Point Output Swing (at 5GHz)	_	—	850	_	mVppd
DDNEXT	Differential Near-End Crosstalk ⁽¹⁾	100MHz to 5GHz, Figure 2	—	-40	_	dB
V	Level D. Com D. Line	100MHz to 5GHz, FGx=1, EQx=R, Figure 5	_	0.6		
Vnoise-input	Input-Referred Noise	100MHz to 5GHz, FGx=1, EQx=1, Figure 5	_	0.5	_	mV _{RMS}
17	$O_{\rm rel}$ (2)	100MHz to 5GHz, FGx=1, EQx=R, Figure 5	_	0.8	_	
Vnoise-output	Output-Referred Noise ⁽²⁾	100MHz to 5GHz, FGx=1, EQx=1, Figure 5	_	1		mV _{RMS}
Signal and Frequ	ency Detectors					
V _{th_upm}	Unplug Mode Detector Threshold	Threshold of LFPS when the input impedance of the redriver is $67k\Omega$ to VbiasRx only. Used in the unplug mode.	200	_	800	mVppd
V _{th_dsm}	Deep Slumber Mode Detector Thresh- old	LFPS signal threshold in deep slumber mode	100		600	mVppd





AC/DC Electrical Characteristics Cont.

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Units
V _{th_am}	Active Mode Detector Threshold	Signal threshold in active and slumber mode	45	_	175	mVppd
F _{th}	LFPS Frequency Detector	Detect the frequency of the input CLK pattern	100	_	400	MHz
External Decoup	External Decoupling Capacitor value					
CAP_EXT	External decoupling capacitor for the internal bias		2.2		20	uF

Note:

1. Measured using a vector-network analyzer (VNA) with -15dBm power level applied to the adjacent input. The VNA detects the signal at the output of the victim channel. All other inputs and outputs are terminated with 50Ω .

2. Guaranteed by design and characterization.

Power-up/Power-down Timing and VCM Ramp Rate




Figure 2. Power-up Timing

Power-up Timing

Symbol	Parameter	Condition	Min.	Тур.	Max.	Units
T _{d_EN}	VDD3P3 to EN assertion delay time		0			ms
T _{VCM}	Stabilization time for VCM common mode voltage			330	400	ms




Figure 3. Power-down Timing

Power-down Timing

Symbol	Parameter	Condition	Min.	Тур.	Max.	Units
T _{d_OFF}	Delay time from EN de-assertion to VDD3P3 power off		900			ms








Figure 4. Channel-Isolation Test Configuration




Figure 5. Noise Test Configuration





Figure 6. Test Condition Referenced in the Electrical Characteristic Table





Part Marking








Packaging Mechanical





For latest package information:

See http://www.diodes.com/design/support/packaging/pericom-packaging/packaging-mechanicals-and-thermal-characteristics/.

Ordering Information

Ordering Number	Package Code	Package Description	
PI3EQX2024ZTFEX	ZTF	34-Contact, Ultra Thin Quad Flat No-Lead (UQFN)	
Nata			

Notes:

1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.

2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.

3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

4. E = Pb-free and Green

5. X suffix = Tape/Reel





IMPORTANT NOTICE

1. DIODES INCORPORATED AND ITS SUBSIDIARIES ("DIODES") MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FIT-NESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes products. Diodes products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of the Diodes products for their intended applications, (c) ensuring their applications, which incorporate Diodes products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.

3 Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.

Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product 4. names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.

5 Diodes products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

6. Diodes products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.

7 While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.

Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes 8. assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

Copyright © 2021 Diodes Incorporated

www.diodes.com