



600W SURFACE MOUNT AUTOMOTIVE TRANSIENT VOLTAGE SUPPRESSOR

Product Summary ($@T_A = +25^{\circ}C$)

P _{PK}	I _{FSM} (A)	V _{RWM} (V)	PM _(AV)
600W	100	12-100	5W

Features and Benefits

- 600W Peak Pulse Power Dissipation
- 12V 100V Standoff Voltages
- Glass Passivated Die Construction
- Unidirectional and Bidirectional Versions Available
- Excellent Clamping Capability
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- Qualified to AEC-Q101 Standards for High Reliability
- PPAP Capable (Note 4)

Description and Applications

Suitable to protect sensitive automotive circuits against surges defined in ISO7637-2 and against electrostatic discharges according to ISO10605.

Compliance with the following standards:

- ISO10605, C = 150pF, R = 330Ω: 30kV (Air Discharge) 30kV (Contact Discharge)
- ISO7637-2 (Note 6) Pulse 1: Vs = -150V Pulse 2a: Vs = +112V Pulse 3a: VS= -220V Pulse 3b: VS= +150V



Top View

Mechanical Data

- Case: SMB
- Case Material: Molded Plastic.
 UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Lead Free Plating (Matte Tin Finish). Solderable per MIL-STD-202, Method 208 (3)
- Weight: 0.1 grams (Approximate)



Bottom View

Ordering Information (Note 5)

Part Number	Qualification	Case	Packaging
SMBJXXX(C)AQ-13-F	Automotive	SMB	3000/Tape & Reel

*x = Device Voltage, e.g., SMBJ14A-13-F.

Notes:

- 1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. Automotive products are AEC-Q101 qualified and are PPAP capable. Refer to https://www.diodes.com/quality/.
- 5. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.


Cathode Band for Unidirectional Device

6. Not applicable to parts with stand-off voltage lower than the average battery voltage (13.5V).

Marking Information

Bidirectional Device

C):: YWW xx



 $\begin{array}{l} xx = \mbox{Product Type Marking Code (See Page 3)} \\ \end{tabular} \\ \e$



Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Peak Pulse Power Dissipation			
(Non Repetitive Current Pulse Derated above $T_A = +25^{\circ}C$)	P _{PK}	600	W
(Note 7)			
Peak Power Derating Above +25°C	P _{DER}	4.8	W/°C
Peak Forward Surge Current, 8.3ms Single Half Sine Wave Superimposed on Rated Load (Notes 7. 8, & 9)	I _{FSM}	100	А
Steady State Power Dissipation @ T _L = +75°C	PM _(AV)	5.0	W
Instantaneous Forward Voltage @ I _{PP} = 35A (Notes 7, 8, & 9)	V _F	3.5	V

Thermal Characteristics

Characteristic	Symbol	Value	Unit	
Operating Temperature Range	TJ	-55 to +150	°C	
Storage Temperature Range	T _{STG}	-55 to +175	°C	

Notes: 7. Valid provided that terminals are kept at ambient temperature.

Measured with 8.3ms single half sine-wave. Duty cycle = 4 pulses per minute maximum.
 Unidirectional units only.



Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)


Part Number Add C for Bi- Directional (Note 10)	Reverse Standoff Voltage	Vo	kdown Itage · (Note 11)	Test Current	Max Reverse Leakage @ V _{RWM}	Max Clamping Voltage @ I _{pp} (Note 12)	Max. Peak Pulse Current I _{pp}	Marking	g Code
See Note 7	V _{RWM} (V)	Min (V)	Max (V)	l⊤(mA)	Ι _R (μΑ)	Vc (V)	(A)	BI-	UNI-
SMBJ12(C)AQ	12.0	13.30	15.30	1.0	5.0	19.9	30.2	BE	LE
SMBJ14(C)AQ	14.0	15.60	17.90	1.0	5.0	23.2	25.8	BK	LK
SMBJ15(C)AQ	15.0	16.70	19.20	1.0	5.0	24.4	24.0	BM	LM
SMBJ16(C)AQ	16.0	17.80	20.50	1.0	5.0	26.0	23.1	BP	LP
SMBJ17(C)AQ	17.0	18.90	21.70	1.0	5.0	27.6	21.7	BR	LR
SMBJ18(C)AQ	18.0	20.00	23.30	1.0	5.0	29.2	20.5	BT	LT
SMBJ20(C)AQ	20.0	22.20	25.50	1.0	5.0	32.4	18.5	BV	LV
SMBJ22(C)AQ	22.0	24.40	28.00	1.0	5.0	35.5	16.9	BX	LX
SMBJ24(C)AQ	24.0	26.70	30.70	1.0	5.0	38.9	15.4	ΒZ	LZ
SMBJ26(C)AQ	26.0	28.90	33.20	1.0	5.0	42.1	14.2	CE	ME
SMBJ28(C)AQ	28.0	31.10	35.80	1.0	5.0	45.4	13.2	CG	MG
SMBJ30(C)AQ	30.0	33.30	38.30	1.0	5.0	48.4	12.4	CK	MK
SMBJ33(C)AQ	33.0	36.70	42.20	1.0	5.0	53.3	11.3	CM	MM
SMBJ36(C)AQ	36.0	40.00	46.00	1.0	5.0	58.1	10.3	CP	MP
SMBJ51(C)AQ	51.0	56.70	65.20	1.0	5.0	82.4	7.3	CZ	MZ
SMBJ58(C)AQ	58.0	64.40	74.60	1.0	5.0	93.6	6.4	DG	NG
SMBJ100(C)AQ	100.0	111.0	128.00	1.0	5.0	162.0	3.7	DZ	NZ

Notes: 10. Suffix C denotes bidirectional device.

11. V_{BR} measured with I_T current pulse = 10ms to 15ms.

12. Per 10 × 1000 μ s waveform. See Figure 4.





10,000 Measured at zero bias C_T, CAPACITANCE (pF) 1000 Uni-di rectiona 100 **Bi-directional** 1 1 1 1 1 = 25°C , = 1.0 MHz V_{sig} = 50 mV p-p 10 1.1 1 10 100 1000 V_{RWM}, REVERSE STANDOFF VOLTAGE (V) Fig. 2 Typical Total Capacitance t, = 10μs I_{PP}, PEAK PULSE CURRENT (%I_{PD}) 100 Peak Value I_{pp} Half Value I_{pp}/2 50 10 X 1000 Waveform as defined by R.E.A. 0 3 0 1 2 t, TIME (ms) Fig. 4 Pulse Waveform 5.0 $\mathsf{PM}_{(\mathsf{AV})}$, STEADY STATE POWER DISSIPATION (W) 4.0 3.0 2.0 60Hz Resistive or Inductive Load 1.0 0.0 0 25 50 75 100 125 150 175 200

SMBJ12(C)AQ - SMBJ100(C)AQ


T_L, LEAD TEMPERATURE (°C) Fig. 6 Steady State Power Derating Curve

SMBJ12(C)AQ - SMBJ100(C)AQ Document number: DS40740 Rev. 3 - 2



Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.




SMB				
Dim	Min	Max		
Α	3.30	3.94		
В	4.06	4.57		
С	1.96	2.21		
D	0.15	0.31		
ш	5.00	5.59		
G	0.05	0.20		
Н	0.76	1.52		
J	2.00	2.50		
All Dimensions in mm				

Note: 12. The bar in the upper drawing is polarity indicator for Cathode Band. It is for unidirectional devices only. Bidirectional devices have no polarity Indicator.

SMB

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.



SMB

Dimensions	Value (in mm)	
С	4.30	
G	1.80	
Х	2.50	
X1	6.80	
Y	2.30	

SMBJ12(C)AQ - SMBJ100(C)AQ Document number: DS40740 Rev. 3 - 2



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2019, Diodes Incorporated

www.diodes.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Diodes Incorporated:

 SMBJ18CAQ-13-F
 SMBJ26AQ-13-F
 SMBJ17CAQ-13-F
 SMBJ30AQ-13-F
 SMBJ30CAQ-13-F
 SMBJ15AQ-13-F

 SMBJ22AQ-13-F
 SMBJ22CAQ-13-F
 SMBJ36AQ-13-F
 SMBJ33CAQ-13-F
 SMBJ14AQ-13-F
 SMBJ20CAQ-13-F

 SMBJ28AQ-13-F
 SMBJ36CAQ-13-F
 SMBJ15CAQ-13-F
 SMBJ26CAQ-13-F
 SMBJ16CAQ-13-F
 SMBJ16AQ-13-F

 SMBJ17AQ-13-F
 SMBJ33AQ-13-F
 SMBJ18AQ-13-F
 SMBJ20AQ-13-F
 SMBJ28CAQ-13-F
 SMBJ24AQ-13-F

 SMBJ24CAQ-13-F
 SMBJ14CAQ-13-F
 SMBJ100AQ-13-F
 SMBJ12AQ-13-F
 SMBJ12AQ-13-F

 SMBJ51CAQ-13-F
 SMBJ58AQ-13-F
 SMBJ58CAQ-13-F
 SMBJ100CAQ-13-F
 SMBJ5.0CAQ-13-F