


SEC:A-A



SEC:B-B

Ordering Information & Specifications

Part No.	Wire Range	Insulation O.D.	Material	Finish	Q'ty/Reel
C4255F-TBE-A	AWG#18-#24	3.10mm(max)	Brass	Tin-plated	5,000pcs
C4255F-TPE-A	AWG#18-#24	3.10mm(max)	Phosphor Bronze	Tin-plated	5,000pcs
C4255F-HBE-A	AWG#18-#24	3.10mm(max)	Brass	Gold-flash 1u"	5,000pcs
C4255F-HBE-A1	AWG#18-#24	3.10mm(max)	Brass	Gold-plated 15u"	5,000pcs
C4255F-HPE-A1	AWG#18-#24	3.10mm(max)	Phosphor Bronze	Gold-plated 15u"	5,000pcs
C4255F-TPE-01	AWG#18-#24	3.10mm(max)	Phosphor Bronze	Tin-plated 100u"(MIN.)	5,000pcs
C4255F-GPE-A	AWG#18-#24	3.10mm(max)	Phosphor Bronze	All Gold-flash 1u"	5,000pcs

Note:E-Stamping before Tin-plated or Gold-plated

			燦達電子工業股份有限公司 JOINT TECH ELECTRONIC IND. CO., LTD.		
		UNIT	SCALE	SHEET	
		mm	1 : 1	1 of 1	
		DRAWN BY		APPROVED BY	
		歐陽小強		謝瑞清	
		2007.11.24		2007.11.24	
		GENERAL TOLERANCE			
A5	EN20201224531	2020.12.24	黃潮		
A4	EN1307240254	2013.08.01	劉包根		
A3	EN110729323	2011.07.29	謝金發		
A2	EN1011110261	2010.11.11	陳敏		
REV.	DESCRIPTION	DATE	NAME		
				X.X±0.25	
				X.XX±0.15	
				X.XXX±0.05	
				ANGLE±	
				DRAW NO. :	
				C4255F-XX-A	
				REV. A5	

4.20mm PITCH  
CRIMP TERMINAL-FEMALE,  
MINI-FIT

DRAW NO. : C4255F-XX-A

REV. A5