


SEC:A-A



SEC:B-B

Ordering Information & Specifications

Part No	Wire Range	Insulation O.D.	Material	Finish	Qty/reel
C4255M-TBE-A	AWG#18-#24	3.10mm(max)	Brass	Tin-plated	5,000pcs
C4255M-HBE-A	AWG#18-#24	3.10mm(max)	Brass	Gold-flash 1u"	5,000pcs
C4255M-HBE-A1	AWG#18-#24	3.10mm(max)	Brass	Gold-plated 15u"	5,000pcs
C4255M-GPE-A	AWG#18-#24	3.10mm(max)	Phosphor Brass	All Gold-flash 1u"	5,000pcs

Note:E-Stamping before Tin-plated or Gold-plated

				燦達電子工業股份有限公司 JOINT TECH ELECTRONIC IND. CO., LTD.			
		UNIT		SCALE		SHEET	
		mm		1 : 1		1 of 1	
		DRAWN BY		APPROVED BY		TITLE: 4.20mm PITCH CRIMP TERMINAL-MALE, MINI-FIT	
		朱恆秀		謝瑞清			
		2009.04.02		2009.04.02			
		GENERAL TOLERANCE					
		X. X±0.25		ANGLE±		DRAW NO. : C4255M-XX-A	
		X. XX±0.15					
		X. XXX±0.05					
REV.	DESCRIPTION	DATE	NAME	REV. A3			