



1,500W SURFACE MOUNT AUTOMOTIVE TRANSIENT VOLTAGE SUPPRESSOR

Product Summary (@TA = +25°C)

| P _{PK} | I _{FSM} | V _{RWM} | PM _(AV) |
|-----------------|------------------|------------------|--------------------|
| 1500W | 200A | 5V to 85V | 5W |

Description and Applications

Suitable to protect sensitive automotive circuits against surges defined in ISO7637-2 and against electrostatic discharges according to ISO10605.

Compliance with following standards:

- ISO10605, C = 150pF, R = 330Ω: 30kV (Air Discharge)
 30kV (Contact Discharge)
- ISO7637-2

Pulse 1: $V_S = -100V$ Pulse 2a: $V_S = +50V$

Pulse 3a: $V_S = -150V$ Pulse 3b: $V_S = +100V$

Features and Benefits

- 1,500W Peak Pulse Power Dissipation
- 5V to 85V Standoff Voltages
- Glass Passivated Die Construction
- Unidirectional and Bidirectional Versions Available
- Excellent Clamping Capability
- Fast Response Time
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- The SMCJ5.0(C)AQ SMCJ85(C)AQ are suitable for automotive applications requiring specific change control; these parts are AEC-Q101 qualified, PPAP capable, and manufactured in IATF 16949 certified facilities.

https://www.diodes.com/quality/product-definitions/

Mechanical Data

- Case: SMC
- Case Material: Molded Plastic. UL Flammability Classification Rating 94V-0
- Terminals: Lead-Free Plating (Matte Tin Finish). Solderable per MIL-STD-202, Method 208
- Polarity Indicator: Cathode Band (Note: Bidirectional devices have no polarity indicator.)
- Weight: 0.21 grams (Approximate)

SMC



Top View



Bottom View

Ordering Information (Note 4)

| Part Number | Qualification | Case | Packaging |
|--------------------|---------------|------|------------------|
| SMCJX.X(C)AQ-13-F* | Automotive | SMC | 3000/Tape & Reel |
| SMCJXX(C)AQ-13-F* | Automotive | SMC | 3000/Tape & Reel |

^{*}X = Device Voltage, e.g., SMCJ14AQ-13-F.

Notes:

- 1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information



xxx = Product Type Marking Code (See Page 2)

| = Manufacturers' Marking

YWW = Date Code Marking

Y = Last Digit of Year (ex: 9 for 2019)

WW = Week Code (01 to 53)



Maximum Ratings (@TA = +25°C, unless otherwise specified.)

| Characteristic | Symbol | Value | Unit |
|---|--------------------|-------|------|
| Peak Pulse Power Dissipation | C | 1500 | W |
| (Non-Repetitive Current Pulse Derated Above $T_A = +25^{\circ}C$) (Note 5) | P_{PK} | 1300 | VV |
| Peak Forward Surge Current, | I | 200 | ۸ |
| 8.3ms Single Half Sine-Wave Superimposed on Rated Load (Notes 5, 6, & 7) | IFSM | 200 | A |
| Steady State Power Dissipation @ T _L = +75°C | PM _(AV) | 5.0 | W |
| Instantaneous Forward Voltage @ I _{PP} = 100A (Notes 5 & 7) | V _F | 3.5 | V |

Thermal Characteristics

| Characteristic | Symbol | Value | Unit |
|-----------------------------|------------------|-------------|------|
| Operating Temperature Range | TJ | -55 to +150 | °C |
| Storage Temperature Range | T _{STG} | -55 to +175 | °C |

Notes:


- 5. Valid provided that terminals are kept at ambient temperature.
- 6. Measured with 8.3ms single half sine-wave. Duty cycle = 4 pulses per minute maximum.
- 7. Unidirectional units only.

Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)


| Part Number Add C For Bidirectional | Reverse Standoff Voltage | Vol | down tage · (Note 9) | Test Current | Max. Reverse Leakage @ V _{RWM} (Note 11) | Max. Clamping Voltage @ I _{pp} (Note 10) | Max. Peak Pulse Current | Markin | ıg Code |
|---|--------------------------------|---------|----------------------------|---------------------|---|---|----------------------------|--------|---------|
| (Note 8) | V _{RWM} (V) | Min (V) | Max (V) | I _T (mA) | I _R (μA) | V _C (V) | I _{PP} (A) | ВІ | UNI |
| SMCJ5.0(C)AQ | 5.0 | 6.40 | 7.07 | 10 | 1000 | 9.2 | 163.0 | BDE | GDE |
| SMCJ6.0(C)AQ | 6.0 | 6.67 | 7.37 | 10 | 1000 | 10.3 | 145.6 | BDG | GDG |
| SMCJ6.5(C)AQ | 6.5 | 7.22 | 7.98 | 10 | 500 | 11.2 | 133.9 | BDK | GDK |
| SMCJ7.0(C)AQ | 7.0 | 7.78 | 8.60 | 10 | 200 | 12.0 | 125.0 | BDM | GDM |
| SMCJ7.5(C)AQ | 7.5 | 8.33 | 9.21 | 1.0 | 100 | 12.9 | 116.3 | BDP | GDP |
| SMCJ8.0(C)AQ | 8.0 | 8.89 | 9.83 | 1.0 | 50 | 13.6 | 110.3 | BDR | GDR |
| SMCJ8.5(C)AQ | 8.5 | 9.44 | 10.4 | 1.0 | 20 | 14.4 | 104.2 | BDT | GDT |
| SMCJ9.0(C)AQ | 9.0 | 10.00 | 11.1 | 1.0 | 10 | 15.4 | 97.4 | BDV | GDV |
| SMCJ10(C)AQ | 10.0 | 11.10 | 12.3 | 1.0 | 5.0 | 17.0 | 88.2 | BDX | GDX |
| SMCJ11(C)AQ | 11.0 | 12.20 | 13.5 | 1.0 | 5.0 | 18.2 | 82.4 | BDZ | GDZ |
| SMCJ12(C)AQ | 12.0 | 13.30 | 14.7 | 1.0 | 5.0 | 19.9 | 75.3 | BEE | GEE |
| SMCJ13(C)AQ | 13.0 | 14.40 | 15.9 | 1.0 | 5.0 | 21.5 | 69.7 | BEG | GEG |
| SMCJ14(C)AQ | 14.0 | 15.60 | 17.2 | 1.0 | 5.0 | 23.2 | 64.7 | BEK | GEK |
| SMCJ15(C)AQ | 15.0 | 16.70 | 18.5 | 1.0 | 5.0 | 24.4 | 61.5 | BEM | GEM |
| SMCJ16(C)AQ | 16.0 | 17.80 | 19.7 | 1.0 | 5.0 | 26.0 | 57.7 | BEP | GEP |
| SMCJ17(C)AQ | 17.0 | 18.90 | 20.9 | 1.0 | 5.0 | 27.6 | 53.3 | BER | GER |
| SMCJ18(C)AQ | 18.0 | 20.00 | 22.1 | 1.0 | 5.0 | 29.2 | 51.4 | BET | GET |
| SMCJ20(C)AQ | 20.0 | 22.20 | 24.5 | 1.0 | 5.0 | 32.4 | 46.3 | BEV | GEV |
| SMCJ22(C)AQ | 22.0 | 24.40 | 27.0 | 1.0 | 5.0 | 35.5 | 42.2 | BEX | GEX |
| SMCJ24(C)AQ | 24.0 | 26.70 | 29.5 | 1.0 | 5.0 | 38.9 | 38.6 | BEZ | GEZ |
| SMCJ26(C)AQ | 26.0 | 28.90 | 31.9 | 1.0 | 5.0 | 42.1 | 35.6 | BFE | GFE |
| SMCJ28(C)AQ | 28.0 | 31.10 | 34.4 | 1.0 | 5.0 | 45.4 | 33.0 | BFG | GFG |
| SMCJ30(C)AQ | 30.0 | 33.30 | 36.8 | 1.0 | 5.0 | 48.4 | 31.0 | BFK | GFK |
| SMCJ33(C)AQ | 33.0 | 36.70 | 40.6 | 1.0 | 5.0 | 53.3 | 28.1 | BFM | GFM |
| SMCJ36(C)AQ | 36.0 | 40.00 | 44.2 | 1.0 | 5.0 | 58.1 | 25.8 | BFP | GFP |
| SMCJ48(C)AQ | 48.0 | 53.30 | 58.9 | 1.0 | 5.0 | 77.4 | 19.4 | BFX | GFX |
| SMCJ51(C)AQ | 51.0 | 56.70 | 62.7 | 1.0 | 5.0 | 82.4 | 18.2 | BFZ | GFZ |
| SMCJ85(C)AQ | 85.0 | 94.40 | 104 | 1.0 | 5.0 | 137.0 | 10.4 | BGV | GGV |


Notes:


- 8. Suffix C denotes bidirectional device.
- 9. V_{BR} measured with I_T current pulse = 10ms to 15ms.
- 10. Per $10 \times 1000 \mu s$ waveform. See Figure 4.
- 11. For bidirectional devices having $V_{\text{RWM}}\,\text{of}\,\,10V$ and under, the I_R is doubled.
















Fig. 2 Typical Total Capacitance



t, TIME (ms)
Fig. 4 Pulse Waveform






Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

SMC




| SMC | | | | |
|----------------------|------|------|--|--|
| Dim | Min | Max | | |
| Α | 5.59 | 6.22 | | |
| В | 6.60 | 7.11 | | |
| C | 2.75 | 3.18 | | |
| D | 0.15 | 0.31 | | |
| Е | 7.75 | 8.13 | | |
| G | 0.10 | 0.20 | | |
| Н | 0.76 | 1.52 | | |
| J | 2.00 | 2.50 | | |
| All Dimensions in mm | | | | |


Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SMC



| Dimensions | Value (in mm) | |
|------------|------------------|--|
| С | 6.90 | |
| G | 4.40 | |
| Х | 2.50 | |
| X1 | 9.40 | |
| Υ | 3 30 | |





IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2019, Diodes Incorporated

www.diodes.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Diodes Incorporated:

 SMCJ28CAQ-13-F
 SMCJ22CAQ-13-F
 SMCJ33CAQ-13-F
 SMCJ17CAQ-13-F
 SMCJ36AQ-13-F
 SMCJ30CAQ-13-F

 SMCJ15AQ-13-F
 SMCJ20AQ-13-F
 SMCJ22AQ-13-F
 SMCJ36CAQ-13-F
 SMCJ20CAQ-13-F
 SMCJ30AQ-13-F

 SMCJ26AQ-13-F
 SMCJ24AQ-13-F
 SMCJ33AQ-13-F
 SMCJ24CAQ-13-F
 SMCJ16AQ-13-F
 SMCJ16CAQ-13-F

 SMCJ17AQ-13-F
 SMCJ14AQ-13-F
 SMCJ15CAQ-13-F
 SMCJ18CAQ-13-F
 SMCJ14CAQ-13-F
 SMCJ18AQ-13-F

 SMCJ26CAQ-13-F
 SMCJ28AQ-13-F
 SMCJ48CAQ-13-F
 SMCJ9.0AQ-13-F
 SMCJ11AQ-13-F
 SMCJ12CAQ-13-F

 SMCJ7.0AQ-13-F
 SMCJ6.0AQ-13-F
 SMCJ11CAQ-13-F
 SMCJ9.0CAQ-13-F
 SMCJ13CAQ-13-F

 SMCJ12AQ-13-F
 SMCJ7.5AQ-13-F
 SMCJ10CAQ-13-F
 SMCJ6.0CAQ-13-F
 SMCJ5.0AQ-13-F
 SMCJ7.0CAQ-13-F

 SMCJ10AQ-13-F
 SMCJ51CAQ-13-F
 SMCJ13AQ-13-F
 SMCJ8.5CAQ-13-F
 SMCJ8.5CAQ-13-F

 SMCJ10AQ-13-F
 SMCJ7.5CAQ-13-F
 SMCJ6.5AQ-13-F
 SMCJ6.5CAQ-13-F
 SMCJ8.5AQ-13-F