



DUAL SURFACE MOUNT SCHOTTKY BARRIER DIODE

Product Summary

V _R (V)	I _F (A)	V _F Max (V) @ +25°C	I _R Max (μA) @ +25°C	
20	0.4	0.43	250	

Features and Benefits

- Very Low Forward Voltage Drop
- Guard Ring Construction for Transient Protection
- High Conductance
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- Qualified to AEC-Q101 Standards for High Reliability
- PPAP Capable (Note 4)

Applications


- DC-DC Converters
- Mobile Telecommunications
- Blocking Diodes
- Reverse Polarity Protection

Mechanical Data


- Case: SOT23
- Case Material: Molded Plastic. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Lead Free Plating (Matte Tin Finish Annealed over Alloy 42 Leadframe). Solderable per MIL-STD-202, Method 208 [®]
- · Polarity: See Diagram
- Weight: 0.008 grams (Approximate)







SDM40E20LSQ



SDM40E20LAQ


Ordering Information (Note 5)

Part Number	Compliance	Case	Packaging
SDM40E20LSQ-7-F	Automotive	SOT23	3000/Tape & Reel
SDM40E20LAQ-7	Automotive	SOT23	3000/Tape & Reel

1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.


- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. Automotive products are AEC-Q101 qualified and are PPAP capable. Refer to https://www.diodes.com/quality/.
- 5. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/

Marking Information



KSW = SDM40E20LSQ Product Type Marking Code YM = Date Code Marking Y = Year (ex: G = 2019)

M = Month (ex: 9 = September)



KWA = SDM40E20LAQ Product Type Marking Code YM = Date Code Marking Y = Year (ex: G = 2019) M = Month (ex: 9 = September)

Date Code Key

Notes:

Year	2015	2016	2017	2018	3 201	19 20	020	2021	2022	2023	2024	2025
Code	С	D	Е	F	G	i	Н	I	J	K	L	М
Month	Jan	Feb	Mar	Apr	Мау	Jun	Jul	Aug	у Ѕер	Oct	Nov	Dec
Code	1	2	3	4	5	6	7	8	9	0	N	D



Maximum Ratings ($@T_A = +25^{\circ}C$, unless otherwise specified.)

Single phase, half wave, 60Hz, resistive or inductive load.

For capacitive load, derate current by 20%.

Characteristic	Symbol	Value	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	V _{RRM} V _R wm V _R	20	V
RMS Reverse Voltage	$V_{R(RMS)}$	14	V
Forward Continuous Current (Note 6)	l _F	0.4	A
Non-Repetitive Peak Forward Surge Current 8.3ms Single Half Sine-Wave Superimposed on Rated Load	IFSM	2	А

Thermal Characteristics

Characteristic	Symbol	Value	Unit		
Power Dissipation	(Note 6)	D-	225	mW	
	(Note 7)	P_{D}	300	IIIVV	
Typical Thermal Resistance Junction to Ambient (Note 6)		7	444	°C/W	
	(Note 7)	$R_{\theta JA}$	333	C/VV	
Operating and Storage Temperature Range		$T_{J_i}T_{STG}$	-65 to +125	°C	


Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Тур	Max	Unit	Test Conditions
Reverse Breakdown Voltage (Note 8)	$V_{(BR)R}$	20		_	V	$I_R = 0.5 \text{mA}$
Forward Voltage Drop	\/-	_		0.310	. v	$I_F = 0.1A$
Polward Vollage Diop	VF	_	_	0.430		$I_F = 0.5A$
Leakage Current (Note 8)	1-	_		100		$V_R = 10V$
Leakage Current (Note 8)	IR	_	_	250	μΑ	$V_R = 20V$
Total Capacitance	C _T	_	120	_	pF	$f = 1MHz, V_R = 0V_{DC}$

Notes:

- 6. Device mounted on FR-5 1.0 x 0.75 x 0.062 inch PCB pad layout.
- 7. Device mounted on Alumina PCB, 0.4 inch x 0.3 inch x 0.024 inch pad layout. 8. Short duration pulse test used to minimize self-heating effect.








Fig. 3 Total Capacitance vs. Reverse Voltage, Per Element




Fig. 2 Typical Reverse Characteristics, Per Element





Fig. 4 Forward Current Derating Curve, Per Element



Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT23




SOT23							
Dim	Min	Max	Тур				
Α	0.37	0.51	0.40				
В	1.20	1.40	1.30				
С	2.30	2.50	2.40				
D	0.89	1.03	0.915				
F	0.45	0.60	0.535				
G	1.78	2.05	1.83				
Н	2.80	3.00	2.90				
7	0.013	0.10	0.05				
K	0.890	1.00	0.975				
K1	0.903	1.10	1.025				
L	0.45	0.61	0.55				
L1	0.25	0.55	0.40				
М	0.085	0.150	0.110				
а	0°	8°					
All Dimensions in mm							

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT23



Dimensions	Value (in mm)
С	2.0
Х	0.8
X1	1.35
Y	0.9
V1	2.0



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2019, Diodes Incorporated

www.diodes.com