

Reference Specification

Type EA /Safety Standard Certified Resin Molding SMD Type Ceramic Capacitors for General Purpose

Product specifications in this catalog are as of Jun. 2023, and are subject to change or obsolescence without notice.

Please consult the approval sheet before ordering. Please read rating and Cautions first.

⚠ CAUTION

1. OPERATING VOLTAGE

1) Do not apply a voltage to a safety standard certified product that exceeds the rated voltage as called out in the specifications. Applied voltage between the terminals of a safety standard certified product shall be less than or equal to the rated voltage (+10 %). When a safety standard certified product is used as a DC voltage product, the AC rated voltage value becomes the DC rated voltage value.


(Example: AC250 V (r.m.s.) rated product can be used as DC250 V (+10 %) rated product.)

If both AC rated voltage and DC rated voltage are specified, apply the voltage lower than the respective rated voltage.

- 1-1) When a safety standard certified product is used in a circuit connected to a commercial power supply, ensure that the applied commercial power supply voltage including fluctuation should be less than 10 % above its rated voltage.
- 1-2) When using a safety standard certified product as a DC rated product in circuits other than those connected to a commercial power supply.

When AC voltage is superimposed on DC voltage, the zero-to-peak voltage shall not exceed the rated DC voltage. When AC voltage or pulse voltage is applied, the peak-to-peak voltage shall not exceed the rated DC voltage.

Typical Voltage Applied to the DC Capacitor



(E: Maximum possible applied voltage.)

2) Abnormal voltages (surge voltage, static electricity, pulse voltage, etc.) shall not exceed the rated DC voltage.

2. OPERATING TEMPERATURE AND SELF-GENERATED HEAT

Keep the surface temperature of a capacitor below the upper limit of its rated operating temperature range. Be sure to take into account the heat generated by the capacitor itself.

When the capacitor is used in a high-frequency current, pulse current or the like, it may have the self-generated heat due to dielectric-loss. Applied voltage should be the load such as self-generated heat is within 20 °C on the condition of atmosphere temperature 25 °C. When measuring, use a thermocouple of small thermal capacity-K of Φ0.1 mm and be in the condition where capacitor is not affected by radiant heat of other components and wind of surroundings. Excessive heat may lead to deterioration of the capacitor's characteristics and reliability. (Never attempt to perform measurement with the cooling fan running. Otherwise, accurate measurement cannot be ensured.)

3. TEST CONDITION FOR WITHSTANDING VOLTAGE

1) TEST EQUIPMENT

Test equipment for AC withstanding voltage should be used with the performance of the wave similar to 50/60 Hz sine wave.


If the distorted sine wave or over load exceeding the specified voltage value is applied, the defective may be caused.

2) VOLTAGE APPLIED METHOD


When the withstanding voltage is applied, capacitor's lead or terminal should be firmly connected to the out-put of the withstanding voltage test equipment, and then the voltage should be raised from near zero to the test voltage.

If the test voltage without the raise from near zero voltage would be applied directly to capacitor, test voltage should be applied with the *zero cross. At the end of the test time, the test voltage should be reduced to near zero, and then capacitor's lead or terminal should be taken off the out-put of the withstanding voltage test equipment.

If the test voltage without the raise from near zero voltage would be applied directly to capacitor, the surge voltage may arise, and therefore, the defective may be caused.



- See the right figure -



4. FAIL-SAFE

When capacitor would be broken, failure may result in a short circuit. Be sure to provide an appropriate fail-safe function like a fuse on your product if failure would follow an electric shock, fire or fume.

5. VIBRATION AND IMPACT

Do not expose a capacitor or its leads to excessive shock or vibration during use.

6. SOLDERING

6-1.Reflow Soldering

When soldering capacitor, it should be performed in following conditions.

Soldering temperature : 230 to 260 °C Soldering time : 10 to 30 s Preheating temperature : 170 °C max.

6-2.Flow Soldering

When soldering capacitor, it should be performed in following conditions.

Soldering temperature : 260 °C max.

Soldering time : 5 s max.

Preheating temperature : 120 °C max.


Preheating time : 60 s max.

6-3. Soldering Iron

When soldering this product to a PCB/PWB, do not exceed the solder heat resistance specification of the capacitor. Subjecting this product to excessive heating could melt the internal junction solder and may result in thermal shocks that can crack the ceramic element.

When soldering capacitor with a soldering iron, it should be performed in following conditions.

Temperature of iron-tip : 400 °C max.
Soldering iron wattage : 50 W max.
Soldering time : 3.5 s max.



7. BONDING, RESIN MOLDING AND COATING

Before bonding, molding or coating this product, verify that these processes do not affect the quality of capacitor by testing the performance of the bonded, molded or coated product in the intended equipment.

In case of the amount of applications, dryness / hardening conditions of adhesives and molding resins containing organic solvents (ethyl acetate, methyl ethyl ketone, toluene, etc.) are unsuitable, the outer coating resin of a capacitor is damaged by the organic solvents and it may result, worst case, in a short circuit.

The variation in thickness of adhesive, molding resin or coating may cause a outer coating resin cracking and/or ceramic element cracking of a capacitor in a temperature cycling.

8. OPERATING AND STORAGE ENVIRONMENT

The insulation coating of capacitors does not form a perfect seal; therefore, do not use or store capacitors in a corrosive atmosphere, especially where chloride gas, sulfide gas, acid, alkali, salt or the like are present. And avoid exposure to moisture. Before cleaning, bonding, or molding this product, verify that these processes do not affect product quality by testing the performance of a cleaned, bonded or molded product in the intended equipment.

This one is MSL 3 product. So, in order to avoid the absorption of moisture, capacitors are packed in moisture-proof envelope.

Store the capacitors in the following conditions at all times, and use within 6 months after delivered.

Temperature : 10 to 30 °C Humidity : 60 % max.

Solder the enclosed capacitors within 168 hours after opening the moisture-proof package.

After opening, store the capacitors in moisture-proof package with a desiccant and HIC card and keep the above condition.

In case the storage period has been exceeded 6 months or the indicator color of a enclosed HIC card has changed when the package has been opened, perform baking (60 $^{\circ}$ C × 168 hr) before soldering.

9. LIMITATION OF APPLICATIONS

Please contact us before using our products for the applications listed below which require especially high reliability for the prevention of defects which might directly cause damage to the third party's life, body or property.

- 1. Aircraft equipment
- 2. Aerospace equipment
- 3. Undersea equipment
- 4. Power plant control equipment
- 5. Medical equipment
- 6. Transportation equipment (automotives, trains, ships, etc.)
- 7. Traffic signal equipment
- 8. Disaster prevention / crime prevention equipment
- 9. Data-processing equipment exerting influence on public
- 10. Application of similar complexity and/or reliability requirements to the applications listed in the above.

NOTICE

1. CLEANING (ULTRASONIC CLEANING)

To perform ultrasonic cleaning, observe the following conditions.

Rinse bath capacity: Output of 20 watts per liter or less.

Rinsing time: 5 min maximum.

Do not vibrate the PCB/PWB directly.

Excessive ultrasonic cleaning may lead to fatigue destruction of the terminals.

2. CAPACITANCE CHANGE OF CAPACITORS

Class 1 capacitors

Capacitance might change a little depending on a surrounding temperature or an applied voltage. Please contact us if you use for the strict time constant circuit.

Class 2 capacitors

Class 2 capacitors like temperature characteristic B, E and F have an aging characteristic, whereby the capacitor continually decreases its capacitance slightly if the capacitor leaves for a long time. Moreover, capacitance might change greatly depending on a surrounding temperature or an applied voltage. So, it is not likely to be able to use for the time constant circuit.

Please contact us if you need a detail information.

3. PERFORMANCE CHECK BY EQUIPMENT

Before using a capacitor, check that there is no problem in the equipment's performance and the specifications.


Generally speaking, Class 2 ceramic capacitors have voltage dependence characteristics and temperature dependence characteristics in capacitance. So, the capacitance value may change depending on the operating condition in a equipment. Therefore, be sure to confirm the apparatus performance of receiving influence in a capacitance value change of a capacitor, such as leakage current and noise suppression characteristic.

Moreover, check the surge-proof ability of a capacitor in the equipment, if needed, because the surge voltage may exceed specific value by the inductance of the circuit.

4. Land Dimensions

The recommandable land dimensions for reflow soldering are follows.

Regarding the "a" dimension, to ensure the creepage distance required by the safety standard applys to your equipment.



Dimension	а	b	С
8.0 × 6.0	8.0	2.2	3.6

⚠ NOTE

- 1. Please make sure that your product has been evaluated in view of your specifications with our product being mounted to your product.
- 2. You are requested not to use our product deviating from this specification.

1.Application

This specification is applied to Safety Standard Certified Resin Molding SMD Type Ceramic Capacitors Type EA used for General Electric equipment.

The safety standard certification is obtained by Class X1, Y1.

Do not use these products in any automotive power train or safety equipment including battery charger for electric vehicles and plug-in hybrids.

Approval standard and certified number

	Standard number	*Certified number	Rated voltage
UL/cUL	UL60384-14/CSA E60384-14	E37921	
ENEC (SEMKO)	EN60384-14	SE-ENEC-2300151	X1: AC440 V(r.m.s.) Y1: AC250 V(r.m.s.)
CQC	IEC60384-14	CQC16001142384	11. AC230 V(1.111.5.)
KTC	KC60384-14	HU03008-16007	

^{*}Above Certified number may be changed on account of the revision of standards and the renewal of certification.

2.Rating

2-1. Operating temperature range

-40 ~ 125°C

2-2.Rated Voltage

X1: AC440 V(r.m.s.) Y1: AC250 V(r.m.s.) DC1,000 V

2-3.Part number configuration

ex.)

DK1	E3	EA	152	M	86	R	AH01
Series	Temperature	Certified	Capacitance	Capacitance	Body	Package	Individual
	Characteristics	Type		Tolerance	Dimension		Specification

Series

DK1 denotes resin molding SMD type safety standard recognized ceramic capacitor of class Y1.

• Temperature Characteristics

Please confirm detailed specification on [Specification and test methods].

	and a operation of the contract of the contrac
Code	Temperature Characteristics
1X	SL
B3	В
E3	E

Certified Type

This denotes safety certified type name Type EA.

Capacitance

The first two digits denote significant figures; the last digit denotes the multiplier of 10 in pF. ex.) In case of 152.

$$15 \times 10^2 = 1500 \text{ pF}$$

• Capacitance Tolerance

Please refer to [Part number list].

Body Dimension

Code	Body Dimension
86	8.0 × 6.0 mm

Package

Code	Package
R	Ф330 mm Reel type

 Individual Specification Murata's control code

Please refer to Part number list.

3.Marking

Certified type : EA

Capacitance : Actual value(under 100 pF)

3 digit system(100 pF and over)

Rated Voltage : X1 440~

Y1 250~

Company name code : ©15 (Made in Thailand)

Manufacturing year : Letter code (The last digit of A.D. year.)

Manufacturing month : Code

ex.) YEAR MONTH
2022 11(November)
2N *

*From January to September: "1" to "9",


October: "O", November: "N", December: "D"


KTC Approval mark : [§

(Example)

EA 152 XI 440~ YI 250~ @15 2N [§

4. Part number list







Unit: mm

Customer	Murata	T.C.	Сар.	Cap. tol.	Dimension (mm)			Body	Pack
Part Number	Part Number	1.0.	(pF)		L	W	T max.	Dimension	qty. (pcs)
	DK11XEA100K86RAH01	SL	10	±10%	11.4±0.5	6.0±0.5	2.5	86	2500
	DK11XEA220K86RAH01	SL	22	±10%	11.4±0.5	6.0±0.5	2.5	86	2500
	DK11XEA470K86RAH01	SL	47	±10%	11.4±0.5	6.0±0.5	2.5	86	2500
	DK1B3EA101K86RAH01	В	100	±10%	11.4±0.5	6.0±0.5	2.5	86	2500
	DK1B3EA221K86RAH01	В	220	±10%	11.4±0.5	6.0±0.5	2.5	86	2500
	DK1B3EA331K86RAH01	В	330	±10%	11.4±0.5	6.0±0.5	2.5	86	2500
	DK1B3EA471K86RAH01	В	470	±10%	11.4±0.5	6.0±0.5	2.5	86	2500
	DK1B3EA681K86RAH01	В	680	±10%	11.4±0.5	6.0±0.5	2.5	86	2500
	DK1E3EA102M86RAH01	Е	1000	±20%	11.4±0.5	6.0±0.5	2.5	86	2500
	DK1E3EA152M86RAH01	E	1500	±20%	11.4±0.5	6.0±0.5	2.5	86	2500

PNLIST

Reference only

fication and to the letter of	em perature gth stance (I.R.)	Specification -40 to 125 °C No defects or abnormalities Within the specified dimension. No defects or abnormalities. 6,000 MΩ or more. Within the specified tolerance. DF≦0.025 Temp. Coefficient	Test method Visual inspection. Using calipers and micrometers. The capacitor shall not be damage when AC4,000 V(r.m.s.) is applied between the terminations for 60 s. The insulation resistance shall be measured with DC500±50 V within 60±5 s of charging. The voltage should be applied to the capacitor through a resistor of 1 MΩ. Capacitance/D.F. shall be measured at 20 °C with the frequency of 1±0.2 kHz and a voltage of AC1±0.2 V(r.m.s.).
perating Tem ppearance mensions electric stren sulation Resis apacitance ssipation Fac	gth stance (I.R.)	-40 to 125 °C No defects or abnormalities Within the specified dimension. No defects or abnormalities. 6,000 MΩ or more. Within the specified tolerance. DF≦0.025 Temp. Coefficient	Visual inspection. Using calipers and micrometers. The capacitor shall not be damage when AC4,000 V(r.m.s.) is applied between the terminations for 60 s. The insulation resistance shall be measured with DC500±50 V within 60±5 s of charging. The voltage should be applied to the capacitor through a resistor of 1 MΩ. Capacitance/D.F. shall be measured at 20 °C with the frequency
ppearance mensions electric stren sulation Resis apacitance ssipation Fac apacitance Te	gth stance (I.R.) tor (D.F.)	No defects or abnormalities Within the specified dimension. No defects or abnormalities. $6,000~M\Omega$ or more. Within the specified tolerance. DF ≤ 0.025 Temp. Coefficient	Using calipers and micrometers. The capacitor shall not be damage when AC4,000 V(r.m.s.) is applied between the terminations for 60 s. The insulation resistance shall be measured with DC500±50 V within 60±5 s of charging. The voltage should be applied to the capacitor through a resistor of 1 MΩ. Capacitance/D.F. shall be measured at 20 °C with the frequency
mensions electric strender sulation Residence apacitance ssipation Factor	stance (I.R.)	Within the specified dimension. No defects or abnormalities. $6,000~\text{M}\Omega~\text{or more}.$ Within the specified tolerance. $\text{DF} {\leq} 0.025$ Temp. Coefficient	Using calipers and micrometers. The capacitor shall not be damage when AC4,000 V(r.m.s.) is applied between the terminations for 60 s. The insulation resistance shall be measured with DC500±50 V within 60±5 s of charging. The voltage should be applied to the capacitor through a resistor of 1 MΩ. Capacitance/D.F. shall be measured at 20 °C with the frequency
electric strensulation Residuation Residuation Residuation Residuation Residuation Factoria Residuation Factoria Residuation Factoria Residuation Factoria Residuation Residua	stance (I.R.)	No defects or abnormalities. $6,000~\text{M}\Omega~\text{or more}.$ $\text{Within the specified tolerance}.$ $\text{DF} \leqq 0.025$ Temp. Coefficient	The capacitor shall not be damage when AC4,000 V(r.m.s.) is applied between the terminations for 60 s. The insulation resistance shall be measured with DC500±50 V within 60±5 s of charging. The voltage should be applied to the capacitor through a resistor of 1 MΩ. Capacitance/D.F. shall be measured at 20 °C with the frequency
apacitance ssipation Fac apacitance Te	tor (D.F.)	Within the specified tolerance. DF≦0.025 Temp. Coefficient	The insulation resistance shall be measured with DC500±50 V within 60±5 s of charging. The voltage should be applied to the capacitor through a resistor o 1 MΩ. Capacitance/D.F. shall be measured at 20 °C with the frequency
ssipation Fac apacitance Te	, ,	DF≦0.025 Temp. Coefficient	
apacitance Te	, ,	Temp. Coefficient	of 1±0.2 kHz and a voltage of AC1±0.2 V(r.m.s.).
	emperature	·	
		SL: +350 to -1000 ppm/°C (Temp. Range: 20 to 85°C) Cap. Change B:within ±10 % E:within +20/-55 % (Temp. Range:-25 to 85 °C)	The capacitance measurement shall be made at each step in table *Pretreatment for B, E char. Perform the heat treatment at 150+0/-10 °C for 60±5 min and then let sit for 24±2 h at *room condition.
		-	Step 1 2 3 4 5
			Temp.(°C) 20±2 -25±2 20±2 85±2 20±2
bration	Appearance	No marked defect.	Solder the capacitor to the Test Jig A (glass epoxy board) shown in
sistance			"Complement of test method".
		· ·	The capacitor shall be subjected to a simple harmonic motion having a total amplitude of 1.5mm, the frequency being varied
	Factor (D.F.)		uniformly between the approximate limits of 10 and 55 Hz. The frequency range, from 10 to 55 Hz and return to 10Hz, shall be traversed in approximately 1 min. This motion shall be applied for a period of 2 h in each of 3 mutually perpendicular directions (total of 6 h).
soldered . rosin (JIS K 5902) (25 % r Immerse in solder solution		Immerse the capacitor in the solution of ethanol (JIS K 8101) and rosin (JIS K 5902) (25 % rosin in weight proportion). Immerse in solder solution for 2±0.5 s. Temp. of solder: 245±5 °C	
Soldering Appearance		No marked defects.	Preheat the capacitor at 150 to 180 °C for 90±30 s.
fect eflow)	Capacitance	Within ±10 %	Reflow temp. : 230 °C min. (Max. temp. : 260 °C) Reflow time : 30±10 s.
,		1 000 MO or more	Reflow number of times : 4 times
			Let sit at *room condition for 24±2 h, then measure. • The next reflow porcess should be done after the temperature of
	strength	r ass the near two.4.	the sample has dropped to room temperature. • Pretreatment for B, E char. Capacitor should be stored at 150+0/-10 °C for 1 h, and apply the AC4,000 V(r.m.s.) 60 s then placed at *room condition for 24±2 h before initial measurements.
thesive strengermination	gth of	No removal of the terminations or other defects should occur.	Solder the capacitor to the Test Jig A (glass epoxy board) shown in "Complement of Test method". Then apply 10 N force in the direction of the arrow. 10 N, 10±1 s Glass Epoxy Board
s old	derability of dering ect efflow)	derability of termination dering Appearance Capacitance change I.R. Dielectric strength Diesive strength of mination	Appearance

Reference only

NI.	Item		Item Specification			T	I		
No.			Specification	Fix the serie	olton to di	Test met		oposa, b = = ==1)	
13	Temperature cycle	Appearance Capacitance	No marked defect. Within ±15 %			ne supporting Te nt of test metho		epoxy board)	
		change	Widini ±10 /0	Perform the	5 cycles		according to the 4 heat treatments listed the		
		Dissipation	SL : DF≦0.025	following table		T	T	İ	
		Factor (D.F.)	B,E: DF≦0.05		Step 1	Temp.(°C) -40±3	Time(min.) 30±3		
		I.R.	3,000 MΩ or more	_	2	Room Temp.	2 to 3		
		Dielectric strength	Pass the item No.4.		3	125±3	30±3		
		Suengui			4	Room Temp.	2 to 3		
				Let sit at *roo	om condi	tion for 24±2 h,	then measure.		
				Pretreatme	-		/ 40 00 for 4 lo	and analyths	
						stored at 150+0, s then placed a			
				before initial			at 100m conditi	011 101 2 122 11	
14	Humidity	Appearance	No marked defect.	Sit the capac	citor at 40	0±2 °C and relat	tive humidity 90	to 95 % for	
	(Steady	Capacitance	Within ±20 %	500+24/-0 h.					
	state)	change		Remove and • Pretreatme		r 24±2 h at *roo F char	m condition, the	en measure.	
		Dissipation	SL: DF≦0.025		,	stored at 150+0	/-10 °C for 1 h,	and apply the	
		Factor (D.F.)	B,E: DF≦0.05	AC4,000 V(r.m.s.) 60 s then placed at *room condition for 24±2 h					
		Dielectric	3,000 MΩ or more Pass the item No.4.	perore minal					
		strength							
15	Humidity loading	Appearance	No marked defect.	Apply the rat		ge at 40±2 °C ai	nd relative hum	idity	
		Capacitance change	Within ±20 %		m condition, the	en measure.			
		Dissipation Factor (D.F.)	SL: DF≦0.025 B,E: DF≦0.05	Capacitor sh	and apply the on for 24±2 h				
		I.R.	3,000 M Ω or more	before initial measurements.					
		Dielectric strength	Pass the item No.4.						
16	Life	Appearance	No marked defect.	Impulse Voltage test is perform					
		Capacitance change	Within ±20 %	voltage value	emeans		be subjected to a 8 kV Impulse (the eak) for 3 times or more.		
		I.R.	3,000 MΩ or more]		47704 10 111			
		Dielectric strength	Pass the item No.4.	Front time (T1) Time to half-val					
				Apply voltage 50 % max.	e as Tab	le for 1,000 h at	125+2/-0 °C, r	elative humidity	
						Applied vo			
					, ,	except that one		e voltage is	
				increas	ed to AC	1,000 V(r.m.s.)	IOI U.T S.		
				 Pretreatme Capacitor sh 	nt for B, ould be s .m.s.) 60	stored at 150+0 s then placed a	/-10 °C for 1 h,	and apply the	
* "roo	na a an alitia all Ta		to 35 °C Relative humidity : 45 to 75 %	A to a construction of a con-		. 00 t- 400 l-D-			

* "room condition" Temperature : 15 to 35 °C, Relative humidity : 45 to 75 %, Atmospheric pressure : 86 to 106 kPa

		Reference	e only
No.	Item	Specification	Test method
17	Passive flammability	The burning time should not be exceeded the time 30 s. The tissue paper should not ignite.	The capacitor under test shall be held in the flame in the position which best promotes burning. Each specimen shall only be exposed once to the flame. Time of exposure to flame: 30 s. Length of flame: 12±1 mm Gas burner: Length 35 mm min. Inside dia: 0.5±0.1 mm Outside dia: 0.9 mm max. Gas: Butane gas purity 95 % min. Approximately 8mm burner Approximately 8mm burner Test specimen Test specimen Tissue paper Wood board of approximately 10mm in thickness
18	Active flammability	The cheese-cloth should not be on fire.	The capacitor shall be individually wrapped in at least one but more than two complete layers of cheesecloth. The capacitor shall be subjected to 20 discharges. The interval between successive discharges shall be 5 s. The UAc shall be maintained for 2 min after the last discharge. C1,2 : 1 μF±10 %, C3 : 0.033 μF±5 % 10 kV L1 to L4 : 1.5 mH±20 % 16A Rod core choke R : 100 Ω±2 %, Ct : 3 μF±5 % 10 kV UAc : UR ±5 % UR : Rated voltage F : Fuse, Rated 16 A Cx : Capacitor specimens Ut : Voltage impressed on the tank capacitor Ct

6. Complement of Test Method

6.1.Test Jig


The test jig should be Jig A as described in "Specifications and Test methods".

The specimen should be soldered by the conditions as described below.

Soldering Method: Reflow soldering

Solder: Sn-3.0Ag-0.5Cu

(1) Test Jig A




•Material : Glass Epoxy Board

•Thickness : 1.6 mm

 $\label{eq:thickness} \mbox{ • Thickness of copper foil : } 0.035 \mbox{ mm}$


7. Packing

7.1. Dimension of tape




(Unit: mm)

7.2. Dimension of Reel



(Unit: mm)

(1) Part of the leader and part of the empty tape shall be attached to the end of the tape as follows.



(Unit: mm)

- (2) The top tape or cover tape and base tape are not attached at the end of the tape for a minimum of 2 pitches.
- (3) Missing capacitors number within 0.1 % of the number per reel or 1 pc, whichever is greater, and not continuous.
- (4) The top tape or cover tape and bottom tape shall not protrude beyond the edges of the tape and shall not cover sprocket holes.
- (5) Cumulative tolerance of sprocket holes, 10 pitches: ±0.3 mm.
- (6) Peeling off force: 0.1 to 0.6 N in the direction shown on the follows.



EKBCDK01