

FR Series Voltage Controlled Crystal Oscillator (VCXO) Legacy ST1307 Series 7.0 x 5.0mm

3.3V CMOS Ultra Low Jitter VCXO





7.0 x 5.0mm Ceramic SMD

Product Features

- 1 32MHz Frequency Range
- Cost-effective design
- Commercial and industrial operation
- ±50 ppm stability (or as specified)
- ± 50 to ± 100 ppm absolute (net) pull range
- RoHS Compliant

Product Description


The FR Series voltage controlled crystal oscillator achieves wide pullability over a broad range of operating conditions and frequencies. The device is constructed with a hermetically sealed, guartz crystal resonator and low noise clock IC. The device, available on tape and reel, is contained in a 7.0 x 5.0mm ceramic package.

Applications


The FR Series VCXO is an ideal component in phase locked loop circuits that perform clock smoothing, clock/data recovery, or frequency translation and card synchronization functions, such as:


- SD/HD Video decoding
- SONET/SDH timing control and line cards
- T3/F3 Platforms
- Satellite and microwave communications
- Wireless base stations
- xDSL and DSLAM
- VoIP












Pin Functions:


Pin	Function
1	Voltage Control
2	OE or NC
3	Ground
4	Output
5	NC
6	V _{CC}

Part Ordering Information:



A: Product Family B: XXX = Frequency Code C: YYYY = Specification Code

Following the above format, Saronix-eCera part numbers will be assigned upon confirmation of exact customer requirements.



SaRonix-eCera[™] is a Pericom® Semiconductor company • US: +1-408-435-08<u>00 TW: +886-3-4518888</u> • www.saronix-ecera.com



3.3V CMOS Ultra Low Jitter VCXO FR

FR Series Voltage Controlled Crystal Oscillator (VCXO) Legacy ST1307 Series | 7.0 x 5.0mm

Electrical Performance

Parameter	Min.	Тур.	Max.	Units	Notes
Output Frequency (F _N)	1		32	MHz	As specified
Supply Voltage	+2.97	+3.3	+3.63	V	
Supply Current			15	mA	
Frequency Stability			±50	ppm	See #1 and #2 below
Operating Temperature Range	-40		+85	°C	As specified
Output Logic 0, V _{OL}			10% V _{DD}	V	Capacitive load
Output Logic 1, V _{OH}	90% V _{DD}			V	
Output Load			30	pF	
Duty Cycle	45		55	%	measured 50% V _{DD}
Rise and Fall Time			8	ns	measured 20/80% V _{DD}
Jitter, Total			20	ps pk-pk	

Notes:

 Stability includes all combinations of operating temperature, load changes, rated input (supply) voltage changes, initial calibration tolerance (25°C), aging (10 year at 40°C average effective ambient temperature), shock and vibration.

For specifications othere than those listed, please contact sales.

Frequency Modulation Function

Parameter	Min.	Тур.	Max.	Units	Notes
Absolute Pull Range (APR)	±50 to ±100			ppm	See #1 below
Control Voltage Range	+0.3		+3.0	V _{DC}	As rated
Center Control Voltage		+1.65		V	For RMT center frequency
Monotonic Linearity			10	%	Positive transfer slope
Input Impedance	50			kΩ	Control voltage pin
Modulation Bandwidth	50			kHz	-3dB

Notes:

1. As specified. APR is relative to the nominal output frequency FN; APR is inclusive (net) of frequency deviation due to stability.

Output Enable / Disable Function

Parameter	Min.	Тур.	Max.	Units	Notes
Input Voltage, Output Enable	3.0			V	or open
Input Voltage, Output High Impedance			0.3	V	Output is high impendance

Absolute Maximum Ratings

Parameter	Min.	Тур.	Max.	Units	Notes
Storage Temperature	-55		+125	°C	


SaRonix-eCera™ is a Pericom® Semiconductor company • US: +1-408-435-0800 TW: +886-3-4518888 • www.saronix-ecera.com




3.3V CMOS Ultra Low Jitter VCXO FR

FR Series Voltage Controlled Crystal Oscillator (VCXO) Legacy ST1307 Series | 7.0 x 5.0mm


Test Circuit



Reflow Soldering Profile



Output Waveform



SaRonix-eCera™ is a Pericom® Semiconductor company • US: +1-408-435-0800 TW: +886-3-4518888 • www.saronix-ecera.com



3.3V CMOS Ultra Low Jitter VCXO FR


FR Series Voltage Controlled Crystal Oscillator (VCXO) Legacy ST1307 Series | 7.0 x 5.0mm

Reliability Test Ratings

This product is rated to meet the following test conditions:

Туре	Parameter	Test Condition
Mechanical	Shock	MIL-STD-883, Method 2002, Condition B
Mechanical	Solderability	JESD22-B102-D Method 2 (Preconditioning E)
Mechanical	Terminal strength	MIL-STD-883, Method 2004, Condition D
Mechanical	Gross leak	MIL-STD-883, Method 1014, Condition C
Mechanical	Fine leak	MIL-STD-883, Method 1014, Condition A2 ($R_1 = 2x10^{-8}$ atm cc/s)
Mechanical	Solvent resistance	MIL-STD-202, Method 215
Environmental	Thermal shock	MIL-STD-883, Method 1011, Condition A
Environmental	Moisture resistance	MIL-STD-883, Method 1004
Environmental	Vibration	MIL-STD-883, Method 2007, Condition A
Environmental	Resistance to soldering heat	J-STD-020C Table 5-2 Pb-free devices (2 cycles max)

Mechanical Drawing





Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Diodes Incorporated:

<u>FR0200006</u> <u>FR0610004</u> <u>FR3880012</u> <u>FR6140005</u> <u>FR7420007</u> <u>FRC280001</u> <u>FR1940013</u> <u>FR0560001</u> <u>FR1120004</u> FR6140006 FR2700025 FR2500010 FR1120003 FR1220009 FR2500009 FR1630005 FR1940008 FR1940014</u>