



Ordering Information & Specifications

PART NO.	Wire Range	Insulation O.D.	Material	Finish	Qty/reel
C3030F-TPE-TA	AWG#20-#24	1.85mm(max)	Phosphor Bronze	Tin-plated (Salt Spray 48 hours)	15,000pcs
C3030F-TPE-A	AWG#20-#24	1.85mm(max)	Phosphor Bronze	Tin-plated	15,000pcs
C3030F-HPE-A	AWG#20-#24	1.85mm(max)	Phosphor Bronze	Gold-flash	15,000pcs
C3030F-HPE-A1	AWG#20-#24	1.85mm(max)	Phosphor Bronze	Gold-plated 15u"	15,000pcs

Note:E-Stamping before Tin-plated or Gold-plated
 Note:C3030F-TPE-TA Salt Spray 48 hours

						UNIT	SCALE	SHEET	TITLE:	
						mm	1 : 1	1 of 1		
						DRAWN BY	APPROVED BY		3.00mm PITCH CRIMP TERMINAL-FEMALE, MICRO-FIT	
						李勤	董正一			
						2007.03.08	2007.03.08		DRAW NO. : C3030F-XX-A	
						GENERAL TOLERANCE		ANGLE±		
A2	EN1704210003	2017.04.20	賴永強	REV.		X.X±0.25		REV. A2		
A1	EN1504240002	2015.04.27	郭木思			X.XX±0.15				
A0	NEW RELEASE	2007.03.08	李勤	X.XXX±0.05		DRAW NO. : C3030F-XX-A		REV. A2		
REV.	DESCRIPTION	DATE	NAME							