



REV.	ECN NO.	REVISED	DATE

NOTE:

1.MATERIAL:

a.HOUSING:PP BLACK

b.TERMINAL(-):BRASS

c.TERMINAL(+):BRASS

(SURFACE PLATING: Brass natural color)

SEE ORDERING INFORMATION





2.ELECTRIC:

a.DIELECTRIC VOLTAGE: 270V AC ONE MINUTE

b.OPERATING TEMPERATURE: -10°C~ +80°C

ORDERING INFORMATION

BH-2032-B1AW001-150



NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR
3	TERMINAL(+)	1	BRASS, T=0.15MM	Brass natural color
2	TERMINAL(-)	1	BRASS, T=0.15MM	Brass natural color
1	HOUSING	1	PP	BLACK

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美阳 www.meiyangdz.com			
DECIMALS: X :±0.30 X.X :±0.25 X.XX :±0.20 X.XXX :±0.10	ANGLES: X :±1° X.X :±0.5°	DSND	YangFeng	DATE	2023-07-28
		CHKD	ZhouRuicai	DATE	2023-07-28
		APVD	XueShunyong	DATE	2023-07-28
WEIGHT:		SCALE:	SIZE: A4	VIEW:	⊕ ⊖
SHEET 1 OF 1		UNIT: mm	REV.: A/1	OBJECT: MY	TITLE: 电池盒BH-2032-1J(26#红黑线长150mm)
		PART NO.:		BH-2032-B1AW001-150	
		DRAW NO.:		WD-CP-0325	

