


SEC:A-A



SEC:B-B

Ordering Information & Specifications

Part No	Wire Range	Insulation O.D.	Material	Finish	Qty/reel
C4255F-TPE-02	AWG#16-#24	3.10mm(max)	Phosphor Bronze	Tin-plated Ni: 50u"Min	5,000pcs
C4255F-TBE-HA	AWG#16-#24	3.10mm(max)	Brass	Tin-plated	5,000pcs
C4255F-TPE-HA	AWG#16-#24	3.10mm(max)	Phosphor Bronze	Tin-plated	5,000pcs
C4255F-HBE-HA	AWG#16-#24	3.10mm(max)	Brass	Gold-flash 1u"	5,000pcs
C4255F-HBE-HA1	AWG#16-#24	3.10mm(max)	Brass	Gold-plated 15u"	5,000pcs
C4255F-HPE-HA1	AWG#16-#24	3.10mm(max)	Phosphor Bronze	Gold-plated 15u"	5,000pcs

Note:E-Stamping before Tin-plated or Gold-plated

				燦達電子工業股份有限公司 JOINT TECH ELECTRONIC IND. CO., LTD.		
		UNIT	SCALE	SHEET		TITLE: 4.20mm PITCH CRIMP TERMINAL-FEMALE, MINI-FIT
		mm	1 : 1	1 of 1		
A4	EN1307240254	2013.08.01	劉包根	DRAWN BY	APPROVED BY	
A3	EN1203090052	2012.03.12	劉包根	歐陽小強	謝瑞清	
A2	EN110729323	2011.07.29	謝金發	GENERAL TOLERANCE		
A1	REVISE	2009.06.11	歐陽小強	X.X±0.25	ANGLE±	
A0	NEW RELEASE	2007.11.29	歐陽小強	X.XX±0.15		
REV.	DESCRIPTION	DATE	NAME	X.XXX±0.05		
				DRAW NO. : C4255F-XX-HA		REV. A4