




REV.	ECN NO.	REVISED	DATE

NOTE:
 1.MATERIAL:
 a.HOUSING:PP BLACK
 b.SPRING:CARBON STEEL
 (SURFACE PLATING: NI-PLATING)
 SEE ORDERING INFORMATION
 2.ELECTRIC:
 a.DIELECTNIC VOLTAGE: 270V AC ONE MINUTE
 b.OPERATING TEMPERATURE: -10° C~ +100° C



ORDERING INFORMATION

BH-23A-B1AJ002

电池盒

电池型号

SMT 180° TYPE

PLATING:
 A-Au1U"
 J-Ni-PLATING
 K-Sn-PLATING

MATERIAL:
 1A-PP BLACK
 1B-PA66 BLACK
 2A-PPA BROWN
 2B-PPA BLACK
 3A-PPS BROWN
 3B-PPS BLACK
 4A-LCP WHITE
 4B-LCP BLACK



UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美用 www.meiyangdz.com	
DECIMALS: X :±0.30 X.X :±0.25 X.XX :±0.20 X.XXX :±0.10	ANGLES: X :±1° X.X :±0.5°	DSND YangFeng	DATE 2023-06-02
WEIGHT:		CHKD ZhouRuicai	DATE 2023-06-02
SHEET 1 OF 1		APVD XueShunyong	DATE 2023-06-02
SCALE:		SIZE: A4	VIEW:
UNIT: mm		REV.: A/1	OBJECT: MY
TITLE:		PART NO.:	
		BH-23A-B1AJ002	
DRAW NO.:WD-CP-0312			

2	SPRING	2	CARBON STEEL,T=0.6MM	Ni-Plating
1	HOUSING	1	PP	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR