



CKT	DIM A	DIM B	DIM C
2	1.00	2.50	4.00
3	2.00	3.50	5.00
4	3.00	4.50	6.00
5	4.00	5.50	7.00
6	5.00	6.50	8.00
7	6.00	7.50	9.00
8	7.00	8.50	10.00
9	8.00	9.50	11.00
10	9.00	10.50	12.00
11	10.00	11.50	13.00
12	11.00	12.50	14.00
13	12.00	13.50	15.00
14	13.00	14.50	16.00
15	14.00	15.50	17.00
16	15.00	16.50	18.00
17	16.00	17.50	19.00
18	17.00	18.50	20.00
19	18.00	19.50	21.00
20	19.00	20.50	22.00
22	21.00	22.50	24.00
24	23.00	24.50	26.00
26	25.00	26.50	28.00

- 技术指标:
1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
 2. 温度范围: -40° C~85° C.
 3. 额定电压: 30V, AC/DC.
 4. 接触电阻: ≤0.02Ω.
 5. 绝缘电阻: ≥100MΩ.
 6. 额定电流:
- 适用电线型号: a. AWG#28: 1.0A (per pin)
 b. AWG#30: 1.0A (per pin)
 c. AWG#32: 0.8A (per pin)

深圳市连欣科技有限公司

品名 (ITEM) WAFER 1.00 Pitch卧式带扣
 料号 (DMG#) XDWFR-1015WT1-**P
 比例 (SCALE) 1:1
 单位 (UNITS) mm
 张数 (SHEET) 1
 图例 (DRAW) 1
 审核 (APP) 1
 尺寸 (SIZE) A4
 版本 (REV) A

一般公差 (TOLERANCE)
 X ±0.50
 X ±0.50
 ANGLES ±1°

序号	项目	描述	备注
1	塑胶	LCP	
2	端子	黄铜	
3	焊片	黄铜	