



Specifications:

规格:
 Voltage rating:50V AC/DC
 额定电压: 50V AC/DC
 Current rating:1A AC/DC
 额定电流: 1A AC/DC
 Withstanding voltage:500V AC/minute
 耐受电压: 500V AC/分钟
 Temperature range:-25℃~+85℃
 温度范围: -25℃~+85℃
 Insulation resistance:100MΩ min
 绝缘电阻: 100MΩ Min
 Contact resistance:30mΩ Max
 接触电阻: 30mΩ Max

X1010 W V S-XX -LP SN
 ① ② ③ ④ ⑤ ⑥ ⑦

- 1.Series No
- 2.Category:W-Wafer
- 3.Welding Board Angle:V-Stright 180°
- 4.Welding Way: S-SMT
- 5.Row No.Pin No:XX-02~15P
- 6.Material:LP-LCP UL94V-0
- 7.Plating:SN-Tin Plated
V01-Gold Flash

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	2.00	5.00	09	8.00	11.00
03	2.00	5.00	10	9.00	12.00
04	3.00	6.00	11	10.00	13.00
05	4.00	7.00	12	11.00	14.00
06	5.00	8.00	13	12.00	15.00
07	6.00	9.00	14	13.00	16.00
08	7.00	10.00	15	14.00	17.00

X1010WVS-XX-LPSN	LCP	Brass	X1010H
PART NO	Material	Material(Pin)	Suitable XKB Housing

Recommended P.C.B Layout

DSND		SCALE: N/A	MODEL TYPE: 1.0mm Crimp Style Connector
DWN		VIEW:	PART NO.: X1010WVS-XX-LPSN
CHKD		UNIT: mm/in	DWG NO.: X-X1010WVS-XX-LPSN
APPD		SIZE: A4	
			WEIGHT SHEET REVISION
			1/1 A0



XKB INDUSTRIAL PRECISION CO.,LIMITED

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5
UNSPECIFIED TOLERANCES	

MARK	DESCRIPTION	DATE	REVISED	APPROVED
ΔX				
ΔX				
ΔX				