


PTGL5SAS270K6B51B0

To be discontinued

RoHS

REACH

Appearance & Shape



Features

1. Useful protective threshold current range with a wide temperature range.
2. Small fluctuation in the circuit due to resistance tolerance +/- 10%.
3. Quick operating time due to small size compared with conventional products.
4. Best suited to meet the requirements of power supply and motor protector. Error-free operation is assured by rush current.
5. Circuit is protected until current is turned off.
6. Restores the original low resistance value automatically once the overload is removed.
7. Non-contact design leads to long life and no noise.
Durable and strong against mechanical vibration and shock because it is a solid element.
8. Lead (Pb) is not contained in the terminations.

Applications

Automotive Usage	Infotainment
Limited Usage	Automotive Grade

Packaging Information

Packaging	Specifications	Standard Packing Quantity
B0	Bulk(Bag)	500

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
2. This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

PTGL5SAS270K6B51B0



Specifications

Max. Voltage	140V
Hold Current(25°C)	134mA
Measure Condition of Hold Current	(at +25°C)
Hold Current (2)	80mA
Measure Condition of Hold Current (2)	(at +85°C)
Hold Current (3)	56mA
Measure Condition of Hold Current (3)	(at +105°C)
Trip Current(25°C)	178mA
Measure Condition of Trip Current	(at +25°C)
Trip Current(2)	227mA
Measure Condition of Trip Current(2)	(at -40°C)
Max. Current	1A
Resistance (25°C)	27Ω
Resistance Value Tolerance (at 25°C)	±10%
Curie Point(typ.)	130°C
Power Consumption(typ)	1.5W
Operating Temperature Range	-40°C to 125°C
D: Outer Dimension	5.5mm
Thickness	4.5mm
H: Height	10.5mm
F: Lead Space	5mm
d: Lead Diameter	0.6mm
Shape	Lead

Mass	0.5g
MSL	N

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.


Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

PTGL5SAS270K6B51B0


Product Data



Resistance-Temperature Charac.



Protective Threshold Current Range



Operating Time (Typical Curve)

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Murata:](#)

[PTGL5SAS270K6B51B0](#)