

1.5A Single-Channel High-Speed Power MOSFET Driver

Features

- High Peak Output Current: 1.5A
- Wide Supply Voltage Operating Range: 4.5V to 25V
- High Capacitive Load Drive Capability 1000pF in 11ns (typical)
- Short Delay Times: 35ns (typical)
- Matched Rise/Fall Times
- Low Output Impedance
- Low Supply Current
- **Over-temperature Protection**
- Under-voltage Lockout
- Non-overlapped Drive Tech
- ESD Protected: 2.0kV
- Input withstands negative inputs up to 5V
- Available in Small SOT23-5 Package

Applications

- Switch Mode Power Supplies
- **Power MOSFET Drivers**
- **Pulse Transformer Drivers**
- Line Drivers
- CCD Driver
- **Class D Switching Amplifiers**
- Level Translator


Rev1.0

KeV1.0 Copyright@2022 Cosine Nanoelectronics Inc. All rights reserved The information provided here is believed to be accurate and reliable. Cosine Nanoelectronics assumes no reliability for inaccuracies and omissions. Specifications described and contained here are subjected to change without notice on the purpose of improving the design and performance. All of this information described herein should not be implied or granted for any third party.

General Description

The COS44263 and COS44273 are single channel power MOSFET drivers. Unique circuit design enables high speed operation capable of delivering peak currents of 1.5A into 1000pF capacitive loads. Improved speed and drive capability are enhanced by matched rise and fall delay times. These matched delays maintain the integrity of input-to-output pulse-widths to reduce timing errors and clock skew problems. Dynamic switching losses are minimized with non-overlapped drive techni- ques. These devices are highly latch-up resistant within their power and voltage ratings. They are not subject to damage when up to 5V of noise spiking (of either polarity) occurs on the ground pin.

Pin Configuration



SOT23-5



1. Pin Configuration and Functions




Figure 1. Pin Diagram (SOT23-5)

Pin Descriptio	n
----------------	---

Pin	No.		
COS44263 COS44273	COS44263R COS44273R	Pin Name	Description
1	1	NC	No connection
2	5	VDD	Power Supply
3	3	IN	Control Input
4	2	GND	Ground
5	4	OUT/OUT	Output

1.1 Input (IN)

MOSFET driver input is a high-impedance, TTL/CMOS compatible input. The input also has 300 mV of hysteresis between the high and low thresholds that prevents output glitching even when the rise and fall time of the input signal is very slow.

1.2 Ground (GND)

Ground is the device return pin. The Ground pin(s) should have a low-impedance connection to the bias supply source return. High peak current flows out the Ground pin(s) when the capacitive load is being discharged.





1.3 Output (OUT)

MOSFET driver output is a low-impedance, CMOS push-pull style output. The pull-down and pull-up devices are of equal strength, making the rise and fall times equivalent.

1.4 Supply Input (V_{DD})

The VDD input is the bias supply for the MOSFET driver and is rated for 4.5V to 25V with respect to the Ground pin. The VDD input should be bypassed with local ceramic capacitors. The value of these capacitors should be chosen based on the capacitive load that is being driven. A value of 1.0 μ F is suggested.




Figure 2. Functional Block Diagram

Function Table	
----------------	--

	COS44263 COS44263R	COS44273 COS44273R
IN	OUT	OUT
L	н	L
н	L	н



2. Product Specification

2.1 Absolute Maximum Ratings ⁽¹⁾

Parameter	Min	Max	Unit
DC supply voltage Vs		26	V
Operating junction temperature	-40	125	°C
Storage temperature	-55	150	°C
Maximum input voltage	GND-5	V _{DD} +0.3	V
Peak output current		2	А

(1) Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only.

2.2 Thermal Data

Parameter	Rating	Unit	
Package Thermal Resistance	190 (SOT23-5)	°C/W	

2.3 Recommended Operating Conditions

Parameter	Rating	Unit
DC Supply Voltage	4.5V ~ 25V	V
Operating ambient temperature	-40 to +85	°C

2.4 Electrical Characteristics

(Typical values are tested at T_A=25 °C, V_{DD}=18V)

Parameter	Symbol	Conditions	Min.	Тур.	Max.	Unit
INPUT						
Input Signal High Threshold	VIH		1.8			V
Input Signal Low Threshold	VIL				0.7	V
Input Signal Hysteresis	V _{HYS}			0.3		V
Input Current	lin	$0V \leq V_{IN} \leq V_{DD}$			±1	μA




COS44263, COS44273

OUTPUT							
Pull-Up Resistance	Roh	Source Current = 10mA		2.0		Ω	
Pull-Down Resistance	R _{OL}	Sink Current = -10mA		2.0		Ω	
		Source Current, f=1kHz, C _L =1000pF		1.5			
Peak Output Current	I _{PK}	Sink Current, f=1kHz, C∟=1000pF		-1.5		- A	
Continuous Output Current	I _{DC}	Source / Sink Current		±200		mA	
POWER SUPPLY							
Davies Oversky Overset		V _{INA} =V _{INB} =3V		0.6		mA	
Power Supply Current	Icc	V _{INA} =V _{INB} =0V		0.4			
Operating Voltage Range	V _{DD}		4.5		25	V	
Under-Voltage Lockout ON Threshold				3.6	4	V	
Under-Voltage Lockout Hysteresis				0.5		V	
SWITCHING CHARACTERIST	ICS						
Rise Time	t _R	C _L =1000pF, See Figure 3.1		11		ns	
Fall Time	t⊧	C _L =1000pF, See Figure 3.1		11		ns	
	t _{D1}	Non-inverting Input		34		ns	
Turn-On Delay Time		Inverting Input		44		ns	
	t _{D2}	Non-inverting Input		34		ns	
Turn-Off Delay Time		Inverting Input		44		ns	
OVER-TEMPERATURE PROT	ECTION						
Thermal Shutdown Threshold				150		°C	
Thermal Shutdown Threshold Hysteresis				25		°C	



3. Application Information








Figure 3.2 COS44273/44273R Switching Time Test Circuit



4. Package and Ordering Information

Model	Order Number	Package	Package Option	Marking Information
COS44263	COS44263	SOT23-5	Tape and Reel, 3000	COS44263
COS44263R	COS44263R	SOT23-5	Tape and Reel, 3000	COS44263R
COS44273	COS44273	SOT23-5	Tape and Reel, 3000	COS44273
COS44273R	COS44273R	SOT23-5	Tape and Reel, 3000	COS44273R

0.20

5. Package Information

5.1 SOT23-5 (Package Outline Dimensions)

