





SURFACE MOUNT ULTRA FAST RECTIFIER

Features

- ◆ The plastic package carries Underwriters Laboratory Flammability Classification 94V-0
- ◆ For surface mounted applications
- ◆ Ultra fast switching for high efficiency
- ◆ Low reverse leakage
- ◆ Built-in strain relief, ideal for automated placement
- ◆ High forward surge current capability
- ◆ High temperature soldering guaranteed 250 °C/10 seconds at terminals

SMAF

ROHS COMPLIANT



Dimensions in inches and (millimeters)

Mechanical Data**Case :** JEDEC SMAF Molded plastic body**Terminals :** Solder plated, solderable per MIL-STD-750, Method 2026**Polarity :** Polarity symbol marking on body**Mounting Position :** Any**Weight :** 0.00095 ounce, 0.027 grams**Maximum Ratings And Electrical Characteristics**

Ratings at 25°C ambient temperature unless otherwise specified.

Single phase half-wave 60Hz, resistive or inductive load, for capacitive load current derate by 20%.

Parameter	SYMBOLS	MDD US2AF	MDD US2BF	MDD US2DF	MDD US2GF	MDD US2JF	MDD US2KF	MDD US2MF	UNITS
Marking Code									
Maximum repetitive peak reverse voltage	V _{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS voltage	V _{RMS}	35	70	140	280	420	560	700	V
Maximum DC blocking voltage	V _{DC}	50	100	200	400	600	800	1000	V
Maximum average forward rectified current at TL=125°C	I _(AV)					2.0			A
Peak forward surge current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method)	I _{FSM}					50			A
Maximum instantaneous forward voltage at 2.0A	V _F		1.0	1.30		1.65			V
Maximum DC reverse current TA=25°C at rated DC blocking voltage TA=125°C	I _R				5.0				uA
					100				
Maximum reverse recovery time (NOTE 1)	trr		50			75			ns
Typical junction capacitance (NOTE 2)	C _J		20.0						pF
Typical thermal resistance (NOTE 3)	R _{θJA} R _{θJC}		65.0						°C/W
Operating junction and storage temperature range	T _J , T _{STG}		-55 to +150						°C

Note: 1. Reverse recovery condition I_F=0.5A, I_R=1.0A, I_{rr}=0.25A

2. Measured at 1MHz and applied reverse voltage of 4.0V D.C.

3. P.C.B. mounted with 2.0"x2.0"(5.0x5.0cm) copper pad areas



Ratings And Characteristic Curves

Fig.1 Forward Current Derating Curve




Fig.2 Typical Reverse Characteristics




Fig.3 Typical Forward Characteristics





Fig.4 Maximum Non-Repetitive Peak Forward Surge Current




The curve above is for reference only.



US2AF THRU US2MF

Reverse Voltage - 50 to 1000 Volts Forward Current - 2.0 Ampere

Packing information




Item	Symbol	Tolerance	SMAF
Carrier width	A	0.1	2.80
Carrier length	B	0.1	4.75
Carrier depth	C	0.1	1.42
Sprocket hole	d	0.05	1.50
7" Reel outside diameter	D	2.0	178.00
7" Reel inner diameter	D ₁	min	54.40
Feed hole diameter	D ₂	0.5	13.00
Sprocket hole position	E	0.1	1.75
Punch hole position	F	0.1	5.05
Punch hole pitch	P	0.1	4.00
Sprocket hole pitch	P ₀	0.1	4.00
Embossment center	P ₁	0.1	2.00
Overall tape thickness	T	0.1	0.30
Tape width	W	0.3	8.00
Reel width	W ₁	1.0	12.30

Note: Devices are packed in accordance with EIA standard RS-481-A and specifications listed above.

Reel packing

PACKAGE	REEL SIZE	REEL (pcs)	COMPONENT SPACING (m/m)	BOX (pcs)	INNER BOX (m/m)	REEL DIA, (m/m)	CARTON SIZE (m/m)	CARTON (pcs)	APPROX. GROSS WEIGHT (kg)
SMAF	7"	3,000	4.0	6,000	210*208*203	178	400*265*400	120,000	10.0

Suggested Pad Layout



Symbol	Unit (mm)	Unit (inch)
A	1.8	0.071
B	1.6	0.063
C	3.8	0.150
D	2.2	0.087
E	5.4	0.213