


Dual N-Channel 30-V (D-S) MOSFET with Schottky Diode

| PRODUCT SUMMARY | | | | |
|-----------------|---------------------|----------------------------------|---------------------------------|-----------------------|
| | V _{DS} (V) | R _{DS(on)} (Ω) | I _D (A) ^a | Q _g (Typ.) |
| Channel-1 | 30 | 0.017 at V _{GS} = 10 V | 8.0 | 12.5 |
| | | 0.021 at V _{GS} = 4.5 V | 7.5 | |
| Channel-2 | 30 | 0.009 at V _{GS} = 10 V | 15.0 | 17 |
| | | 0.010 at V _{GS} = 4.5 V | 14.0 | |

| SCHOTTKY PRODUCT SUMMARY | | |
|--------------------------|--|---------------------------------|
| V _{DS} (V) | V _{SD} (V) Diode Forward Voltage | I _F (A) ^a |
| 30 | 0.43 V at 1.0 A | 3.8 |



FEATURES


- Halogen-free According to IEC 61249-2-21 Definition
- TrenchFET[®] Power MOSFET
- 100 % R_g and UIS Tested
- Compliant to RoHS Directive 2002/95/EC



RoHS
COMPLIANT

APPLICATIONS

- Notebook Logic dc-to-dc
- Low Current dc-to-dc



| ABSOLUTE MAXIMUM RATINGS T _A = 25 °C, unless otherwise noted | | | | |
|---|-----------------------------------|------------------------|----------------------|----------------------|
| Parameter | Symbol | Channel-1 | Channel-2 | Unit |
| Drain-Source Voltage | V _{DS} | 30 | 30 | V |
| Gate-Source Voltage | V _{GS} | ± 16 | ± 16 | |
| Continuous Drain Current (T _J = 150 °C) | I _D | T _C = 25 °C | 8.0 | 15.0 |
| | | T _C = 70 °C | 6.4 | 12.0 |
| | | T _A = 25 °C | 6.7 ^{b, c} | 11.4 ^{b, c} |
| | | T _A = 70 °C | 5.4 ^{b, c} | 9.1 ^{b, c} |
| Pulsed Drain Current (10 μs Pulse Width) | I _{DM} | 35 | 60 | A |
| Source-Drain Current Diode Current | I _S | T _C = 25 °C | 1.8 | 3.8 |
| | | T _A = 25 °C | 1.25 ^{b, c} | 2.4 ^{b, c} |
| Pulsed Source-Drain Current | I _{SM} | 35 | 35 | |
| Single Pulse Avalanche Current | I _{AS} | 15 | 15 | |
| Single Pulse Avalanche Energy | E _{AS} | 11.2 | 11.2 | mJ |
| Maximum Power Dissipation | P _D | T _C = 25 °C | 1.98 | 4.16 |
| | | T _C = 70 °C | 1.26 | 2.66 |
| | | T _A = 25 °C | 1.38 ^{b, c} | 2.35 ^{b, c} |
| | | T _A = 70 °C | 0.88 ^{b, c} | 1.5 ^{b, c} |
| Operating Junction and Storage Temperature Range | T _J , T _{stg} | - 55 to 150 | | °C |

| THERMAL RESISTANCE RATINGS | | | | | | | |
|---|--------------|-------------------|------|-----------|------|------|------|
| Parameter | Symbol | Channel-1 | | Channel-2 | | Unit | |
| | | Typ. | Max. | Typ. | Max. | | |
| Maximum Junction-to-Ambient ^{b, d} | t ≤ 10 s | R _{thJA} | 72 | 90 | 43 | 53 | °C/W |
| Maximum Junction-to-Foot (Drain) | Steady State | R _{thJF} | 51 | 63 | 25 | 30 | |

Notes:

- Based on T_C = 25 °C.
- Surface Mounted on 1" x 1" FR4 board.
- t = 10 s.
- Maximum under Steady State conditions is 125 °C/W (Channel-1) and 100 °C/W (Channel-2).

| SPECIFICATIONS $T_J = 25\text{ }^\circ\text{C}$, unless otherwise noted | | | | | | | |
|--|-------------------------|--|------|------|-------------------|-------|---------------|
| Parameter | Symbol | Test Conditions | | Min. | Typ. ^a | Max. | Unit |
| Static | | | | | | | |
| Drain-Source Breakdown Voltage | V_{DS} | $V_{GS} = 0\text{ V}, I_D = 1\text{ mA}$ | Ch-1 | 30 | | | V |
| | | $V_{GS} = 0\text{ V}, I_D = 1\text{ mA}$ | Ch-2 | 30 | | | |
| V_{DS} Temperature Coefficient | $\Delta V_{DS}/T_J$ | $I_D = 250\text{ }\mu\text{A}$ | Ch-1 | | 35 | | |
| $V_{GS(th)}$ Temperature Coefficient | $\Delta V_{GS(th)}/T_J$ | $I_D = 250\text{ }\mu\text{A}$ | Ch-1 | | - 6 | | |
| Gate Threshold Voltage | $V_{GS(th)}$ | $V_{DS} = V_{GS}, I_D = 1\text{ mA}$ | Ch-1 | 1 | | 2.5 | |
| | | $V_{DS} = V_{GS}, I_D = 1\text{ mA}$ | Ch-2 | 1 | | 2.5 | |
| Gate-Body Leakage | I_{GSS} | $V_{DS} = 0\text{ V}, V_{GS} = \pm 16\text{ V}$ | Ch-1 | | | 100 | μA |
| | | $V_{DS} = 0\text{ V}, V_{GS} = \pm 16\text{ V}$ | Ch-2 | | | 100 | |
| Zero Gate Voltage Drain Current | I_{DSS} | $V_{DS} = 30\text{ V}, V_{GS} = 0\text{ V}$ | Ch-1 | | | 0.001 | mA |
| | | $V_{DS} = 30\text{ V}, V_{GS} = 0\text{ V}$ | Ch-2 | | 0.05 | 0.5 | |
| | | $V_{DS} = 30\text{ V}, V_{GS} = 0\text{ V}, T_J = 100\text{ }^\circ\text{C}$ | Ch-1 | | | 0.025 | |
| | | $V_{DS} = 30\text{ V}, V_{GS} = 0\text{ V}, T_J = 100\text{ }^\circ\text{C}$ | Ch-2 | | 3 | 15 | |
| On-State Drain Current ^b | $I_{D(on)}$ | $V_{DS} = 5\text{ V}, V_{GS} = 10\text{ V}$ | Ch-1 | 20 | | | A |
| | | $V_{DS} = 5\text{ V}, V_{GS} = 10\text{ V}$ | Ch-2 | 20 | | | |
| Drain-Source On-State Resistance ^b | $R_{DS(on)}$ | $V_{GS} = 10\text{ V}, I_D = 8\text{ A}$ | Ch-1 | | 0.017 | | Ω |
| | | $V_{GS} = 10\text{ V}, I_D = 8\text{ A}$ | Ch-2 | | 0.009 | | |
| | | $V_{GS} = 4.5\text{ V}, I_D = 5\text{ A}$ | Ch-1 | | 0.021 | | |
| | | $V_{GS} = 4.5\text{ V}, I_D = 5\text{ A}$ | Ch-2 | | 0.010 | | |
| Forward Transconductance ^b | g_{fs} | $V_{DS} = 15\text{ V}, I_D = 8\text{ A}$ | Ch-1 | | 40 | | S |
| | | $V_{DS} = 15\text{ V}, I_D = 8\text{ A}$ | Ch-2 | | 47 | | |
| Dynamic^a | | | | | | | |
| Input Capacitance | C_{iss} | Channel-1 $V_{DS} = 15\text{ V}, V_{GS} = 0\text{ V}, f = 1\text{ MHz}$ | Ch-1 | | 1535 | | pF |
| Output Capacitance | C_{oss} | | Ch-2 | | 2290 | | |
| Reverse Transfer Capacitance | C_{rss} | Channel-2 $V_{DS} = 15\text{ V}, V_{GS} = 0\text{ V}, f = 1\text{ MHz}$ | Ch-1 | | 205 | | |
| | | | Ch-2 | | 360 | | |
| Total Gate Charge | Q_g | $V_{DS} = 15\text{ V}, V_{GS} = 10\text{ V}, I_D = 8\text{ A}$ | Ch-1 | | 29 | 44 | nC |
| | | | Ch-2 | | 39 | 59 | |
| | | Channel-1 $V_{DS} = 15\text{ V}, V_{GS} = 4.5\text{ V}, I_D = 8\text{ A}$ | Ch-1 | | 12.5 | 19 | |
| | | | Ch-2 | | 17 | 26 | |
| Gate-Source Charge | Q_{gs} | Channel-2 $V_{DS} = 15\text{ V}, V_{GS} = 4.5\text{ V}, I_D = 8\text{ A}$ | Ch-1 | | 4.1 | | |
| Gate-Drain Charge | Q_{gd} | | Ch-2 | | 5.6 | | |
| Gate Resistance | R_g | $f = 1\text{ MHz}$ | Ch-1 | | 1.8 | 3.0 | Ω |
| | | | Ch-2 | | 1.9 | 3.0 | |







| SPECIFICATIONS $T_J = 25\text{ }^\circ\text{C}$, unless otherwise noted | | | | | | | |
|--|--------------|---|------|-------------------|------|------|----|
| Parameter | Symbol | Test Conditions | Min. | Typ. ^a | Max. | Unit | |
| Dynamic^a | | | | | | | |
| Turn-On Delay Time | $t_{d(on)}$ | Channel-1 $V_{DD} = 15\text{ V}, R_L = 3\ \Omega$ $I_D \cong 5\text{ A}, V_{GEN} = 10\text{ V}, R_g = 1\ \Omega$ | Ch-1 | | 8 | 15 | ns |
| | | | Ch-2 | | 9 | 16 | |
| Rise Time | t_r | | Ch-1 | | 22 | 33 | |
| | | | Ch-2 | | 24 | 36 | |
| Turn-Off Delay Time | $t_{d(off)}$ | Channel-2 $V_{DD} = 15\text{ V}, R_L = 3\ \Omega$ $I_D \cong 5\text{ A}, V_{GEN} = 10\text{ V}, R_g = 1\ \Omega$ | Ch-1 | | 20 | 30 | |
| | | | Ch-2 | | 26 | 39 | |
| Fall Time | t_f | | Ch-1 | | 8 | 15 | |
| | | | Ch-2 | | 8 | 15 | |
| Turn-On Delay Time | $t_{d(on)}$ | Channel-1 $V_{DD} = 15\text{ V}, R_L = 3\ \Omega$ $I_D \cong 5\text{ A}, V_{GEN} = 4.5\text{ V}, R_g = 1\ \Omega$ | Ch-1 | | 24 | 36 | |
| | | | Ch-2 | | 24 | 36 | |
| Rise Time | t_r | | Ch-1 | | 87 | 130 | |
| | | | Ch-2 | | 97 | 145 | |
| Turn-Off Delay Time | $t_{d(off)}$ | Channel-2 $V_{DD} = 15\text{ V}, R_L = 3\ \Omega$ $I_D \cong 5\text{ A}, V_{GEN} = 4.5\text{ V}, R_g = 1\ \Omega$ | Ch-1 | | 30 | 45 | |
| | | | Ch-2 | | 35 | 53 | |
| Fall Time | t_f | | Ch-1 | | 34 | 51 | |
| | | | Ch-2 | | 45 | 68 | |
| Drain-Source Body Diode Characteristics | | | | | | | |
| Continuous Source-Drain Diode Current | I_S | $T_C = 25\text{ }^\circ\text{C}$ | Ch-1 | | | 1.8 | A |
| | | | Ch-2 | | | 3.8 | |
| Pulse Diode Forward Current ^a | I_{SM} | | Ch-1 | | | 35 | A |
| | | | Ch-2 | | | 35 | |
| Body Diode Voltage | V_{SD} | $I_S = 2\text{ A}$ | Ch-1 | | 0.77 | 1.1 | V |
| | | $I_S = 1\text{ A}$ | Ch-2 | | 0.37 | 0.43 | |
| Body Diode Reverse Recovery Time | t_{rr} | Channel-1 $I_F = 4\text{ A}, dI/dt = 100\text{ A}/\mu\text{s}, T_J = 25\text{ }^\circ\text{C}$ | Ch-1 | | 22 | 33 | ns |
| | | | Ch-2 | | 26 | 39 | |
| Body Diode Reverse Recovery Charge | Q_{rr} | Channel-2 $I_F = 4\text{ A}, dI/dt = 100\text{ A}/\mu\text{s}, T_J = 25\text{ }^\circ\text{C}$ | Ch-1 | | 15 | 23 | nC |
| | | | Ch-2 | | 15 | 23 | |
| Reverse Recovery Fall Time | t_a | | Ch-1 | | 13 | | ns |
| | | | Ch-2 | | 13 | | |
| Reverse Recovery Rise Time | t_b | | Ch-1 | | 9 | | ns |
| | | | Ch-2 | | 13 | | |

Notes:


- a. Guaranteed by design, not subject to production testing.
- b. Pulse test; pulse width $\leq 300\ \mu\text{s}$, duty cycle $\leq 2\%$.

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.


CHANNEL-1 TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted




CHANNEL-1 TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted




Source-Drain Diode Forward Voltage




On-Resistance vs. Gate-to-Source Voltage



Threshold Voltage






Single Pulse Power, Junction-to-Ambient



* $V_{GS} >$ minimum V_{GS} at which $R_{DS(on)}$ is specified


Safe Operating Area, Junction-to-Ambient

CHANNEL-1 TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted




* The power dissipation P_D is based on $T_{J(max)} = 150$ °C, using junction-to-case thermal resistance, and is more useful in settling the upper dissipation limit for cases where additional heatsinking is used. It is used to determine the current rating, when this rating falls below the package limit.

CHANNEL-1 TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted




Normalized Thermal Transient Impedance, Junction-to-Ambient




Normalized Thermal Transient Impedance, Junction-to-Foot


CHANNEL-2 TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted




Output Characteristics




Transfer Characteristics




On-Resistance vs. Drain Current



Capacitance




Gate Charge




On-Resistance vs. Junction Temperature


CHANNEL-2 TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted




Source-Drain Diode Forward Voltage




On-Resistance vs. Gate-to-Source Voltage



Reverse Current (Schottky)






Single Pulse Power, Junction-to-Ambient



* $V_{GS} >$ minimum V_{GS} at which $R_{DS(on)}$ is specified



Safe Operating Area, Junction-to-Ambient

CHANNEL-2 TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted




* The power dissipation P_D is based on $T_{J(max)} = 150$ °C, using junction-to-case thermal resistance, and is more useful in settling the upper dissipation limit for cases where additional heatsinking is used. It is used to determine the current rating, when this rating falls below the package limit.

CHANNEL-2 TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted




SOIC (NARROW): 8-LEAD
JEDEC Part Number: MS-012



| DIM | MILLIMETERS | | INCHES | |
|---|-------------|------|-----------|-------|
| | Min | Max | Min | Max |
| A | 1.35 | 1.75 | 0.053 | 0.069 |
| A ₁ | 0.10 | 0.20 | 0.004 | 0.008 |
| B | 0.35 | 0.51 | 0.014 | 0.020 |
| C | 0.19 | 0.25 | 0.0075 | 0.010 |
| D | 4.80 | 5.00 | 0.189 | 0.196 |
| E | 3.80 | 4.00 | 0.150 | 0.157 |
| e | 1.27 BSC | | 0.050 BSC | |
| H | 5.80 | 6.20 | 0.228 | 0.244 |
| h | 0.25 | 0.50 | 0.010 | 0.020 |
| L | 0.50 | 0.93 | 0.020 | 0.037 |
| q | 0° | 8° | 0° | 8° |
| S | 0.44 | 0.64 | 0.018 | 0.026 |
| ECN: C-06527-Rev. I, 11-Sep-06 DWG: 5498 | | | | |

RECOMMENDED MINIMUM PADS FOR SO-8



Recommended Minimum Pads
Dimensions in Inches/(mm)

Disclaimer

All products due to improve reliability, function or design or for other reasons, product specifications and data are subject to change without notice.

Taiwan VBsemi Electronics Co., Ltd., branches, agents, employees, and all persons acting on its or their representatives (collectively, the "Taiwan VBsemi"), assumes no responsibility for any errors, inaccuracies or incomplete data contained in the table or any other any disclosure of any information related to the product.(www.VBsemi.com)

Taiwan VBsemi makes no guarantee, representation or warranty on the product for any particular purpose of any goods or continuous production. To the maximum extent permitted by applicable law on Taiwan VBsemi relinquished: (1) any application and all liability arising out of or use of any products; (2) any and all liability, including but not limited to special, consequential damages or incidental ; (3) any and all implied warranties, including a particular purpose, non-infringement and merchantability guarantee.

Statement on certain types of applications are based on knowledge of the product is often used in a typical application of the general product VBsemi Taiwan demand that the Taiwan VBsemi of. Statement on whether the product is suitable for a particular application is non-binding. It is the customer's responsibility to verify specific product features in the products described in the specification is appropriate for use in a particular application. Parameter data sheets and technical specifications can be provided may vary depending on the application and performance over time. All operating parameters, including typical parameters must be made by customer's technical experts validated for each customer application. Product specifications do not expand or modify Taiwan VBsemi purchasing terms and conditions, including but not limited to warranty herein.

Unless expressly stated in writing, Taiwan VBsemi products are not intended for use in medical, life saving, or life sustaining applications or any other application. Wherein VBsemi product failure could lead to personal injury or death, use or sale of products used in Taiwan VBsemi such applications using client did not express their own risk. Contact your authorized Taiwan VBsemi people who are related to product design applications and other terms and conditions in writing.

The information provided in this document and the company's products without a license, express or implied, by estoppel or otherwise, to any intellectual property rights granted to the VBsemi act or document. Product names and trademarks referred to herein are trademarks of their respective representatives will be all.

Material Category Policy

Taiwan VBsemi Electronics Co., Ltd., hereby certify that all of the products are determined to be RoHS compliant and meets the definition of restrictions under Directive of the European Parliament 2011/65 / EU, 2011 Nian. 6. 8 Ri Yue restrict the use of certain hazardous substances in electrical and electronic equipment (EEE) - modification, unless otherwise specified as inconsistent.(www.VBsemi.com)

Please note that some documents may still refer to Taiwan VBsemi RoHS Directive 2002/95 / EC. We confirm that all products identified as consistent with the Directive 2002/95 / EC European Directive 2011/65 /.

Taiwan VBsemi Electronics Co., Ltd. hereby certify that all of its products comply identified as halogen-free halogen-free standards required by the JEDEC JS709A. Please note that some Taiwanese VBsemi documents still refer to the definition of IEC 61249-2-21, and we are sure that all products conform to confirm compliance with IEC 61249-2-21 standard level JS709A.